

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219647

Luminaire Tested: **LDSQA6A60950D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1219647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A60950D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6447.9 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219647

CATALOG NUMBER: LDSQA6A60950D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219647

CATALOG NUMBER: LDSQA6A60950D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	52033	52033	52033
5°	142812	47944	19561
10°	312956	39234	7454
15°	478039	29869	8741
20°	553849	22213	13585
25°	604176	18276	21929
30°	674676	16570	22392
35°	686450	11364	15353
40°	698507	5384	7768
45°	699643	2241	3392
50°	591484	978	1045
55°	190471	668	165
60°	37829	766	0
65°	3861	907	0
70°	415	1259	0
75°	0	1664	0
80°	0	2752	273
85°	0	5483	543

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219647

CATALOG NUMBER: LDSQA6A60950D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.0	2.5
10°-20°	848.4	13.2
20°-30°	1624.5	25.2
30°-40°	1913.9	29.7
40°-50°	1503.3	23.3
50°-60°	366.3	5.7
60°-70°	15.7	0.2
70°-80°	5.9	0.1
80°-90°	5.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2636.9	40.9
0°-40°	4550.8	70.6
0°-60°	6420.4	99.6
0°-90°	6447.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6447.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1208	1208	1208	1208	1208	
5°	3304	2391	1109	581	453	437
15°	10724	5508	670	192	196	2994
25°	12718	6698	385	402	462	5928
35°	13060	4234	216	279	292	8189
45°	11490	1309	37	51	56	8633
55°	2537	48	9	6	2	3020
65°	38	6	9	6	0	100
75°	0	6	10	7	0	0
85°	0	7	11	7	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219647

CATALOG NUMBER: LDSQA6A60950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5
2.5°	2071.3	2066.9	2036.7	2064.5	1979.8	1976.5	1938.7	1921.9	1872.9	1826.1	1759.1
5°	3304.3	3231.8	3172.7	3175.0	3012.2	2982.1	2897.4	2811.5	2680.0	2557.4	2391.3
7.5°	5036.6	4950.8	4825.9	4773.6	4462.5	4371.1	4196.1	3967.5	3681.0	3395.8	3088.0
10°	7158.2	7171.5	7009.9	6860.6	6390.1	6205.1	5921.9	5471.4	4928.5	4392.2	3847.2
12.5°	9293.0	9284.1	9091.3	8865.0	8285.3	8024.4	7647.6	7085.7	6366.7	5535.0	4682.2
15°	10724.5	10788.0	10706.6	10525.9	10031.0	9732.2	9307.5	8545.0	7668.8	6658.8	5508.3
17.5°	11622.9	11683.3	11654.2	11512.6	11075.6	10756.7	10402.3	9777.9	8764.6	7494.8	6159.3
20°	12087.8	12182.7	12169.1	12015.4	11685.4	11421.2	11029.9	10451.3	9573.9	8075.6	6580.7
22.5°	12397.7	12470.2	12490.3	12316.3	11975.2	11724.4	11437.9	10851.6	10026.5	8430.2	6747.8
25°	12717.7	12846.0	12719.9	12505.9	12192.6	11951.9	11646.4	11084.5	10242.9	8575.0	6697.7
27.5°	13110.1	13171.5	12886.0	12691.0	12343.1	12082.3	11757.9	11219.3	10280.7	8459.2	6411.3
30°	13570.5	13316.3	13116.8	12730.0	12335.3	12081.2	11751.2	11134.7	10081.1	8074.6	5856.1
32.5°	13494.7	13261.8	13035.5	12626.3	12236.0	11984.1	11616.2	10852.7	9609.6	7431.2	5090.2
35°	13060.0	13110.1	12866.0	12527.1	12085.6	11825.8	11424.6	10451.3	8809.2	6543.9	4233.9
37.5°	12693.2	12803.5	12644.2	12330.9	11882.7	11531.5	10989.8	9807.0	7764.5	5417.9	3422.4
40°	12427.8	12463.5	12377.7	12026.6	11488.2	10980.8	10354.3	8649.8	6495.9	4253.0	2701.1
42.5°	12016.6	12111.2	11959.7	11576.1	10760.2	10186.1	9278.5	7313.2	5045.6	3248.5	2033.4
45°	11490.3	11580.7	11393.3	10755.6	9620.7	8779.1	7672.1	5702.2	3732.4	2394.6	1308.8
47.5°	10631.9	10687.7	10325.3	9443.5	7793.7	7001.0	5866.1	3975.4	2404.6	1338.9	636.6
50°	8830.4	8803.6	8056.7	6972.1	5212.8	4381.1	3491.6	2154.9	1080.2	634.4	398.0
52.5°	5691.1	5629.7	4890.6	3904.1	2639.9	2014.5	1513.9	929.8	563.0	354.4	157.1
55°	2537.4	2513.9	2058.0	1598.6	1080.2	929.8	710.1	455.9	299.8	123.7	47.9
57.5°	940.9	919.8	810.5	680.1	521.7	433.7	344.4	218.5	76.9	41.2	25.7
60°	439.3	438.0	385.7	317.6	220.8	167.2	96.9	51.4	32.2	22.3	14.6
62.5°	140.4	137.2	95.8	70.3	50.1	43.5	34.6	25.7	16.7	12.2	8.9
65°	37.9	37.9	34.6	29.0	23.5	20.1	16.7	12.2	7.8	6.8	5.6
67.5°	14.6	14.6	13.3	12.2	8.9	7.8	6.8	5.6	4.4	5.6	5.6
70°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	4.4	4.4	5.6
72.5°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.4	5.6	5.6
75°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.4	5.6	5.6
77.5°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.4	5.6	5.6
80°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.4	5.6	5.6
82.5°	0.0	0.0	1.1	2.2	2.2	2.2	3.3	4.4	4.4	5.6	6.8
85°	0.0	0.0	1.1	2.2	2.2	3.3	3.3	4.4	4.4	5.6	6.8
87.5°	0.0	0.0	1.1	2.2	2.2	3.3	3.3	4.4	4.4	5.6	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219647

CATALOG NUMBER: LDSQA6A60950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5
2.5°	1710.1	1636.5	1535.0	1476.1	1461.5	1430.3	1375.7	1294.3	1227.4	1162.7	1124.9
5°	2250.9	2076.9	1881.9	1744.7	1689.0	1614.3	1481.5	1344.5	1218.5	1109.3	1023.5
7.5°	2823.8	2537.4	2221.8	1967.7	1876.2	1758.0	1541.8	1337.8	1165.0	1013.4	898.5
10°	3393.4	2931.9	2503.8	2136.0	1986.6	1826.1	1540.7	1276.4	1073.5	897.4	770.3
12.5°	3963.1	3299.8	2711.2	2237.4	2043.4	1840.5	1495.0	1182.8	957.6	778.1	656.7
15°	4489.4	3593.0	2851.7	2272.0	2037.9	1798.3	1402.4	1069.1	836.2	670.1	557.3
17.5°	4881.7	3746.9	2884.0	2219.6	1949.8	1684.4	1260.8	935.3	720.2	574.1	459.4
20°	5074.6	3771.4	2807.1	2070.2	1798.3	1522.9	1105.9	807.0	620.9	484.8	387.9
22.5°	5074.6	3655.5	2639.9	1882.9	1608.7	1336.7	956.6	701.3	543.0	422.6	341.1
25°	4881.7	3424.7	2415.7	1666.6	1400.3	1152.7	827.2	622.0	482.7	384.7	316.6
27.5°	4507.2	3105.9	2128.2	1425.8	1195.1	988.8	724.6	549.5	437.0	346.7	347.9
30°	3992.1	2714.6	1798.3	1171.7	984.5	812.7	609.8	460.4	350.1	333.3	343.3
32.5°	3396.8	2246.3	1424.7	908.5	762.6	639.9	463.7	325.5	278.7	280.9	292.1
35°	2786.0	1768.0	1072.4	673.4	567.4	463.7	304.3	214.0	211.8	216.2	224.0
37.5°	2199.5	1323.2	775.9	492.6	381.3	285.4	163.9	147.2	147.2	151.5	156.1
40°	1647.7	938.7	534.0	292.1	185.0	130.4	103.7	95.8	94.7	95.8	101.4
42.5°	1131.4	594.2	317.6	117.1	89.2	75.8	65.7	60.2	59.1	60.2	63.5
45°	635.4	365.7	123.7	62.5	53.6	47.9	41.2	37.9	36.8	36.8	39.0
47.5°	398.0	145.0	55.7	39.0	33.5	31.2	26.7	24.5	23.5	23.5	24.5
50°	152.8	56.8	34.6	25.7	22.3	20.1	17.9	15.6	14.6	14.6	15.6
52.5°	52.4	33.5	22.3	16.7	14.6	13.3	11.1	10.0	10.0	10.0	10.0
55°	29.0	20.1	13.3	10.0	8.9	8.9	8.9	8.9	8.9	8.9	8.9
57.5°	17.9	12.2	8.9	7.8	7.8	7.8	7.8	7.8	7.8	8.9	8.9
60°	10.0	7.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	8.9	8.9
62.5°	6.8	6.8	6.8	6.8	6.8	6.8	7.8	7.8	8.9	8.9	8.9
65°	5.6	5.6	5.6	6.8	6.8	6.8	7.8	7.8	8.9	8.9	8.9
67.5°	5.6	5.6	6.8	6.8	6.8	7.8	7.8	8.9	8.9	8.9	8.9
70°	5.6	6.8	6.8	7.8	7.8	7.8	8.9	8.9	8.9	10.0	10.0
72.5°	5.6	6.8	6.8	7.8	7.8	7.8	8.9	8.9	10.0	10.0	10.0
75°	6.8	6.8	6.8	7.8	7.8	7.8	8.9	10.0	10.0	10.0	10.0
77.5°	6.8	6.8	7.8	7.8	7.8	8.9	8.9	10.0	10.0	10.0	10.0
80°	6.8	6.8	7.8	7.8	8.9	8.9	10.0	10.0	10.0	11.1	11.1
82.5°	6.8	6.8	7.8	8.9	8.9	8.9	10.0	10.0	11.1	11.1	11.1
85°	6.8	7.8	7.8	8.9	8.9	8.9	10.0	10.0	11.1	11.1	11.1
87.5°	6.8	7.8	7.8	8.9	8.9	8.9	10.0	10.0	11.1	11.1	11.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219647

CATALOG NUMBER: LDSQA6A60950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5
2.5°	1074.6	1027.8	981.0	946.4	929.8	913.0	876.3	828.4	808.2	779.2	762.6
5°	936.4	857.3	794.9	753.7	729.1	696.7	654.4	607.6	580.8	550.8	530.6
7.5°	793.7	701.3	641.0	603.1	578.7	538.4	484.8	429.1	396.9	363.4	340.1
10°	668.8	580.8	512.9	469.4	438.0	391.2	337.9	298.7	270.8	241.9	218.5
12.5°	558.5	463.7	391.2	354.4	333.3	288.7	244.1	200.7	184.0	178.4	178.4
15°	452.6	366.8	305.4	274.2	251.9	204.0	195.1	192.9	191.8	190.6	192.9
17.5°	369.0	296.5	231.8	216.2	214.0	212.9	214.0	214.0	215.1	218.5	224.0
20°	310.0	242.9	238.6	239.7	239.7	244.1	249.7	254.3	258.6	264.3	274.2
22.5°	275.4	274.2	282.2	283.2	288.7	295.5	305.4	312.2	323.3	329.0	343.3
25°	317.6	325.5	340.1	344.4	353.4	364.5	380.1	389.1	402.5	409.1	425.9
27.5°	360.0	372.3	390.1	395.8	403.6	421.4	432.5	440.4	447.0	451.5	461.6
30°	356.8	368.0	385.7	386.9	398.0	410.2	416.9	423.7	428.1	426.9	432.5
32.5°	302.1	312.2	329.0	329.0	341.1	351.2	354.4	360.0	360.0	360.0	362.2
35°	231.8	238.6	249.7	253.0	263.0	269.8	272.0	278.7	278.7	276.4	276.4
37.5°	160.5	169.4	177.2	179.4	186.2	190.6	196.1	197.3	195.1	196.1	196.1
40°	104.7	110.3	116.0	117.1	122.6	126.0	131.6	131.6	132.6	131.6	133.7
42.5°	64.7	69.1	72.5	74.7	76.9	79.2	82.5	83.6	84.7	83.6	85.8
45°	40.0	42.4	44.6	45.8	46.8	47.9	51.4	51.4	51.4	51.4	52.4
47.5°	24.5	25.7	26.7	26.7	27.9	29.0	30.1	30.1	30.1	30.1	31.2
50°	14.6	15.6	15.6	15.6	16.7	16.7	17.9	17.9	17.9	16.7	17.9
52.5°	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	8.9	10.0
55°	8.9	8.9	7.8	7.8	7.8	7.8	7.8	6.8	5.6	5.6	4.4
57.5°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.6	5.6	4.4	3.3
60°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.6	4.4	4.4	3.3
62.5°	8.9	7.8	7.8	7.8	7.8	6.8	6.8	5.6	4.4	4.4	3.3
65°	8.9	8.9	7.8	7.8	7.8	6.8	6.8	5.6	5.6	4.4	3.3
67.5°	8.9	8.9	8.9	7.8	8.9	7.8	6.8	6.8	5.6	4.4	4.4
70°	10.0	8.9	8.9	8.9	8.9	7.8	7.8	6.8	5.6	4.4	4.4
72.5°	10.0	10.0	8.9	8.9	8.9	7.8	7.8	6.8	5.6	5.6	4.4
75°	10.0	10.0	8.9	8.9	8.9	7.8	7.8	6.8	6.8	5.6	4.4
77.5°	10.0	10.0	10.0	8.9	8.9	8.9	7.8	7.8	6.8	5.6	4.4
80°	10.0	10.0	10.0	10.0	10.0	8.9	8.9	7.8	6.8	5.6	4.4
82.5°	11.1	10.0	10.0	10.0	10.0	8.9	8.9	7.8	6.8	5.6	5.6
85°	11.1	11.1	10.0	10.0	10.0	8.9	8.9	7.8	6.8	6.8	5.6
87.5°	11.1	10.0	10.0	10.0	10.0	8.9	8.9	7.8	6.8	5.6	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219647

CATALOG NUMBER: LDSQA6A60950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5	1208.5
2.5°	745.9	736.9	736.9	721.2	719.1	706.9	716.9	710.1
5°	508.4	493.8	489.4	473.7	468.3	453.8	458.2	452.6
7.5°	320.0	305.4	301.1	289.8	283.2	272.0	273.2	269.8
10°	195.1	181.8	178.4	175.0	171.7	170.5	171.7	170.5
12.5°	177.2	176.2	173.9	175.0	172.8	173.9	175.0	173.9
15°	192.9	195.1	192.9	194.0	192.9	195.1	196.1	196.1
17.5°	226.2	230.8	228.6	231.8	230.8	236.4	236.4	236.4
20°	277.6	285.4	283.2	287.6	287.6	294.3	294.3	296.5
22.5°	348.9	359.0	357.9	368.0	365.7	373.4	373.4	375.8
25°	434.7	444.8	445.8	452.6	451.5	459.4	459.4	461.6
27.5°	470.5	476.1	474.9	478.3	479.3	483.8	487.2	484.8
30°	441.5	445.8	444.8	447.0	447.0	450.4	453.8	450.4
32.5°	371.2	374.6	374.6	379.1	375.8	376.8	382.3	379.1
35°	284.3	286.5	284.3	286.5	287.6	287.6	293.3	292.1
37.5°	202.9	204.0	204.0	207.3	204.0	204.0	209.7	210.7
40°	136.0	137.2	136.0	140.4	138.2	138.2	141.5	138.2
42.5°	86.9	88.1	86.9	90.4	88.1	90.4	91.4	92.6
45°	53.6	53.6	52.4	54.6	53.6	54.6	55.7	55.7
47.5°	31.2	31.2	30.1	32.2	31.2	31.2	31.2	32.2
50°	16.7	16.7	16.7	17.9	16.7	16.7	16.7	15.6
52.5°	8.9	8.9	7.8	8.9	7.8	7.8	7.8	7.8
55°	4.4	3.3	3.3	3.3	2.2	2.2	2.2	2.2
57.5°	3.3	2.2	2.2	1.1	1.1	1.1	0.0	0.0
60°	2.2	2.2	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.2	2.2	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.2	2.2	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.3	2.2	2.2	1.1	1.1	0.0	0.0	0.0
70°	3.3	2.2	2.2	1.1	1.1	0.0	0.0	0.0
72.5°	3.3	2.2	2.2	2.2	1.1	1.1	0.0	0.0
75°	3.3	3.3	2.2	2.2	1.1	1.1	0.0	0.0
77.5°	4.4	3.3	2.2	2.2	1.1	1.1	0.0	0.0
80°	4.4	3.3	2.2	2.2	2.2	1.1	1.1	1.1
82.5°	4.4	3.3	3.3	2.2	2.2	1.1	1.1	1.1
85°	4.4	3.3	3.3	2.2	2.2	1.1	1.1	1.1
87.5°	4.4	3.3	3.3	2.2	2.2	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)