

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979562

Luminaire Tested: PRLX-240-940-LL7-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-240-940-LL7-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 240 SHADE WITH FROSTED LENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4710.5 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.33
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979562
CATALOG NUMBER: PRLX-240-940-LL7-F-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P979562

CATALOG NUMBER: PRLX-240-940-LL7-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	112	109	106	103	110	106	104	101	102	100	98	99	97	95	95	94	92	90													90															
2	105	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	81													81															
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72													72															
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64													64															
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57													57															
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51													51															
7	73	61	54	48	71	61	53	48	59	53	48	58	52	48	57	51	47	46													46															
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41													41															
9	64	52	45	40	63	51	44	40	50	44	39	49	43	39	48	43	39	37													37															
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34													34															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24781
5°	24709
10°	24530
15°	24149
20°	23849
25°	23512
30°	23093
35°	22791
40°	22444
45°	21815
50°	18597
55°	9495
60°	1539
65°	198
70°	183
75°	241
80°	238
85°	243

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21815 cd/sqm

TEST NUMBER: P979562

CATALOG NUMBER: PRLX-240-940-LL7-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.9	4.9
10°-20°	653.8	13.9
20°-30°	974.1	20.7
30°-40°	1159.2	24.6
40°-50°	1157.2	24.6
50°-60°	507.5	10.8
60°-70°	17.6	0.4
70°-80°	6.3	0.1
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1859.8	39.5
0°-40°	3019.0	64.1
0°-60°	4683.8	99.4
0°-90°	4710.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4710.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2461	
5°	2445	232
15°	2317	654
25°	2116	974
35°	1854	1159
45°	1532	1157
55°	541	508
65°	8	18
75°	6	6
85°	2	3
90°	0	

TEST NUMBER: P979562

CATALOG NUMBER: PRLX-240-940-LL7-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	2461.1
2.5°	2459.1
5°	2444.6
7.5°	2424.0
10°	2399.2
12.5°	2364.1
15°	2316.6
17.5°	2269.1
20°	2225.7
22.5°	2174.1
25°	2116.3
27.5°	2050.2
30°	1986.2
32.5°	1920.2
35°	1854.1
37.5°	1781.8
40°	1707.5
42.5°	1629.0
45°	1532.0
47.5°	1395.7
50°	1187.2
52.5°	891.9
55°	540.9
57.5°	243.6
60°	76.4
62.5°	16.5
65°	8.3
67.5°	6.2
70°	6.2
72.5°	6.2
75°	6.2
77.5°	6.2
80°	4.1
82.5°	4.1
85°	2.1
87.5°	2.1
90°	0.0



TEST NUMBER: P979562
 CATALOG NUMBER: PRLX-240-940-LL7-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.45	14.80	13.82	15.11	15.43	13.45	14.80	13.82	15.11	15.43
	3H	13.33	14.51	13.71	14.84	15.21	13.33	14.51	13.71	14.84	15.21
	4H	13.27	14.36	13.67	14.71	15.09	13.27	14.36	13.67	14.71	15.09
	6H	13.20	14.20	13.61	14.57	14.96	13.20	14.20	13.61	14.57	14.96
	8H	13.16	14.11	13.59	14.50	14.90	13.16	14.11	13.59	14.50	14.90
	12H	13.12	14.02	13.55	14.41	14.84	13.12	14.02	13.55	14.41	14.84
4H	2H	13.26	14.35	13.66	14.70	15.09	13.26	14.35	13.66	14.70	15.09
	3H	13.14	14.01	13.55	14.42	14.82	13.14	14.01	13.55	14.42	14.82
	4H	13.06	13.84	13.50	14.26	14.70	13.06	13.84	13.50	14.26	14.70
	6H	12.99	13.66	13.46	14.11	14.57	12.99	13.66	13.46	14.11	14.57
	8H	12.94	13.56	13.41	14.01	14.48	12.94	13.56	13.41	14.01	14.48
	12H	12.90	13.45	13.38	13.93	14.41	12.90	13.45	13.38	13.93	14.41
8H	4H	12.92	13.55	13.39	14.00	14.47	12.92	13.55	13.39	14.00	14.47
	6H	12.83	13.35	13.33	13.84	14.32	12.83	13.35	13.33	13.84	14.32
	8H	12.77	13.24	13.29	13.76	14.25	12.77	13.24	13.29	13.76	14.25
	12H	12.73	13.15	13.24	13.65	14.22	12.73	13.15	13.24	13.65	14.22
12H	4H	12.87	13.43	13.36	13.91	14.38	12.87	13.43	13.36	13.91	14.38
	6H	12.76	13.23	13.29	13.75	14.24	12.76	13.23	13.29	13.75	14.24
	8H	12.72	13.15	13.24	13.64	14.21	12.72	13.15	13.24	13.64	14.21