

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219651

Luminaire Tested: **LDSQA6A65950D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1219651
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A65950D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6626.3 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.46 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 66.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219651

CATALOG NUMBER: LDSQA6A65950D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219651

CATALOG NUMBER: LDSQA6A65950D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	102		103	100	98		99	97	95		95	94	93
2	105	99	94	90	103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	79	96	89	83	78		86	81	77		83	79	76		81	77	74
4	91	82	75	70	89	81	74	69		78	73	68		76	71	67		74	70	67
5	85	74	67	62	83	73	67	61		71	65	61		70	64	60		68	63	60
6	79	68	60	55	77	67	60	55		65	59	54		64	58	54		62	57	54
7	74	62	55	49	72	61	54	49		60	53	49		59	53	49		57	52	48
8	69	57	49	44	67	56	49	44		55	49	44		54	48	44		53	47	43
9	64	52	45	40	63	52	45	40		51	44	40		50	44	40		49	43	39
10	60	48	41	36	59	48	41	36		47	40	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	51464	51464	51464
5°	132012	46820	14582
10°	257326	35981	7004
15°	461934	24436	9401
20°	685826	18552	15510
25°	779551	15283	24323
30°	845039	16710	22884
35°	890099	10828	14186
40°	909349	4811	6908
45°	821326	1833	2563
50°	540651	723	723
55°	148066	631	0
60°	29571	723	0
65°	2089	988	0
70°	302	1221	0
75°	0	1797	0
80°	0	2678	298
85°	0	5335	593



TEST NUMBER: P1219651

CATALOG NUMBER: LDSQA6A65950D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.4	2.2
10°-20°	777.8	11.7
20°-30°	1763.0	26.6
30°-40°	2116.2	31.9
40°-50°	1491.4	22.5
50°-60°	307.7	4.6
60°-70°	10.9	0.2
70°-80°	6.5	0.1
80°-90°	6.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2687.2	40.6
0°-40°	4803.4	72.5
0°-60°	6602.5	99.6
0°-90°	6626.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6626.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1195	1195	1195	1195	1195	
5°	3054	2225	1083	451	337	376
15°	10363	4559	548	195	211	3075
25°	16409	5515	322	451	512	7573
35°	16934	3862	206	270	270	10528
45°	13489	1324	30	41	42	9921
55°	1972	26	8	6	0	2599
65°	20	6	10	6	0	61
75°	0	6	11	7	0	0
85°	0	7	11	7	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1219651

CATALOG NUMBER: LDSQA6A65950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3
2.5°	2037.5	1975.9	2000.1	1929.0	1913.4	1900.1	1913.4	1836.2	1792.9	1737.4	1692.8
5°	3054.4	2980.8	2997.8	2873.7	2817.0	2778.5	2771.3	2612.2	2492.9	2361.5	2225.4
7.5°	4252.0	4182.2	4172.5	3979.7	3862.8	3796.6	3769.0	3541.1	3335.2	3101.3	2845.9
10°	5885.8	5726.8	5677.4	5397.9	5174.9	5034.0	4860.4	4496.6	4135.1	3782.2	3456.9
12.5°	7787.1	7700.4	7577.4	7084.7	6694.3	6494.4	6235.2	5666.5	5119.5	4536.4	3991.7
15°	10363.2	10054.7	9845.1	9133.0	8504.0	8195.6	7817.3	6947.4	6120.7	5382.2	4559.4
17.5°	12880.1	12718.7	12391.0	11466.8	10498.1	10011.4	9447.5	8265.4	7097.9	6047.3	5042.4
20°	14968.2	14816.4	14442.9	13571.7	12497.1	11778.8	11069.2	9447.5	7922.1	6577.4	5365.4
22.5°	15968.3	15871.9	15567.0	14821.1	13905.4	13222.4	12459.7	10453.6	8531.7	6924.4	5512.3
25°	16409.3	16364.6	16168.3	15580.2	14717.7	14138.0	13417.6	11165.6	8911.2	7085.9	5514.7
27.5°	16856.3	16864.7	16431.0	15965.9	15147.7	14591.0	13897.0	11481.3	8980.0	6995.6	5334.0
30°	16997.2	16908.1	16716.4	16049.0	15271.8	14680.2	13935.7	11335.6	8698.0	6624.5	4973.7
32.5°	16939.3	16904.5	16693.6	15987.5	15061.1	14409.2	13563.3	10757.1	8141.3	6094.3	4463.0
35°	16934.5	16869.5	16386.3	15780.3	14639.2	13834.5	12719.9	9822.2	7353.3	5395.4	3861.6
37.5°	16628.5	16467.0	16104.4	15287.6	13783.7	12763.3	11513.8	8679.9	6389.6	4611.0	3265.2
40°	16179.1	15962.1	15485.1	14248.8	12301.8	11125.9	9906.5	7382.2	5369.0	3837.5	2631.4
42.5°	15240.5	14912.8	14238.0	12537.9	10327.1	9266.7	8252.2	6067.8	4378.5	3126.7	2008.6
45°	13488.7	13040.5	12128.4	10262.0	8342.6	7477.4	6661.7	4882.2	3505.0	2319.4	1324.2
47.5°	10841.5	10425.8	9595.7	8169.0	6542.5	5811.2	5160.5	3631.5	2376.0	1343.5	632.6
50°	8071.5	7714.8	7066.7	5677.4	4391.8	3817.1	3260.4	2062.7	1113.3	638.7	262.6
52.5°	4815.9	4638.8	4064.0	3148.4	2168.7	1868.7	1500.0	873.6	561.5	231.3	71.1
55°	1972.5	1820.5	1604.8	1287.9	943.4	800.1	684.3	431.4	174.6	48.2	26.5
57.5°	891.6	857.9	760.3	597.6	433.8	363.9	245.8	82.0	38.5	24.0	15.6
60°	343.4	309.7	265.0	143.3	61.4	51.9	42.1	27.7	19.2	13.2	9.7
62.5°	49.5	46.9	42.1	33.7	26.5	24.0	20.5	14.5	10.8	8.4	7.2
65°	20.5	20.5	18.1	14.5	12.1	10.8	9.7	7.2	6.0	6.0	6.0
67.5°	8.4	8.4	7.2	6.0	4.8	4.8	4.8	3.6	4.8	4.8	6.0
70°	2.4	2.4	2.4	2.4	2.4	2.4	3.6	3.6	4.8	4.8	6.0
72.5°	0.0	0.0	1.2	1.2	2.4	2.4	2.4	3.6	4.8	6.0	6.0
75°	0.0	0.0	1.2	1.2	2.4	2.4	2.4	3.6	4.8	6.0	6.0
77.5°	0.0	0.0	1.2	1.2	2.4	2.4	3.6	3.6	4.8	6.0	6.0
80°	0.0	0.0	1.2	1.2	2.4	2.4	3.6	3.6	4.8	6.0	7.2
82.5°	0.0	0.0	1.2	1.2	2.4	2.4	3.6	3.6	4.8	6.0	7.2
85°	0.0	0.0	1.2	1.2	2.4	2.4	3.6	3.6	4.8	6.0	7.2
87.5°	0.0	0.0	1.2	1.2	2.4	2.4	3.6	3.6	4.8	6.0	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219651

CATALOG NUMBER: LDSQA6A65950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3
2.5°	1654.3	1577.2	1555.5	1488.0	1431.5	1403.8	1368.7	1290.3	1231.4	1153.0	1106.1
5°	2130.2	1984.5	1868.7	1727.8	1635.1	1574.8	1480.8	1337.4	1221.8	1083.3	984.5
7.5°	2644.6	2378.4	2170.0	1937.4	1803.7	1698.8	1538.7	1332.7	1162.7	978.4	825.3
10°	3141.1	2743.5	2415.7	2082.0	1906.1	1760.4	1539.8	1280.8	1055.4	823.0	661.5
12.5°	3578.5	3065.2	2603.7	2174.7	1956.7	1774.9	1498.8	1188.1	915.7	677.1	535.0
15°	3943.6	3314.6	2736.2	2209.8	1960.3	1743.6	1413.4	1055.4	760.3	548.2	448.2
17.5°	4220.6	3446.0	2777.3	2167.6	1890.5	1654.3	1281.9	888.1	616.8	465.1	377.1
20°	4364.2	3471.3	2718.1	2053.1	1761.6	1519.4	1109.7	720.5	522.9	404.9	315.7
22.5°	4382.1	3400.2	2577.2	1889.3	1598.9	1355.5	919.3	601.2	466.2	357.9	278.4
25°	4274.9	3245.9	2376.0	1703.7	1420.6	1167.5	748.3	538.6	424.1	321.7	320.5
27.5°	4046.0	2980.8	2135.0	1488.0	1204.9	949.4	635.0	486.7	378.2	341.0	362.6
30°	3723.1	2641.1	1838.6	1215.8	941.0	730.1	535.0	401.1	332.6	336.1	354.2
32.5°	3285.7	2219.5	1490.4	890.4	673.5	549.4	401.1	273.4	276.0	277.1	292.9
35°	2736.2	1779.6	1113.3	598.8	473.5	386.7	226.5	201.2	204.9	206.0	216.8
37.5°	2192.8	1367.5	739.9	398.7	297.6	203.6	140.9	134.9	137.4	136.1	148.2
40°	1679.6	953.2	443.4	197.6	114.5	95.2	86.7	83.2	84.3	85.6	92.8
42.5°	1189.1	517.0	219.3	74.8	60.3	55.3	51.9	49.5	50.5	50.5	55.3
45°	603.6	244.6	74.8	41.0	37.3	33.7	31.3	30.1	30.1	30.1	32.6
47.5°	261.5	80.8	34.9	25.3	22.9	21.6	19.2	18.1	18.1	18.1	19.2
50°	82.0	32.6	21.6	16.8	14.5	13.2	12.1	12.1	12.1	10.8	12.1
52.5°	30.1	20.5	14.5	10.8	9.7	9.7	9.7	8.4	9.7	8.4	9.7
55°	18.1	13.2	9.7	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
57.5°	12.1	9.7	8.4	8.4	7.2	7.2	8.4	8.4	8.4	8.4	8.4
60°	8.4	8.4	7.2	7.2	7.2	7.2	8.4	8.4	8.4	8.4	8.4
62.5°	7.2	7.2	7.2	7.2	7.2	7.2	8.4	8.4	8.4	8.4	9.7
65°	6.0	7.2	7.2	7.2	7.2	7.2	8.4	8.4	9.7	9.7	9.7
67.5°	6.0	7.2	7.2	8.4	8.4	8.4	8.4	9.7	9.7	9.7	9.7
70°	7.2	7.2	8.4	8.4	8.4	8.4	9.7	9.7	9.7	9.7	10.8
72.5°	7.2	7.2	8.4	8.4	8.4	8.4	9.7	9.7	10.8	10.8	10.8
75°	7.2	8.4	8.4	8.4	8.4	9.7	9.7	9.7	10.8	10.8	10.8
77.5°	7.2	8.4	8.4	9.7	9.7	9.7	9.7	10.8	10.8	10.8	10.8
80°	7.2	8.4	8.4	9.7	9.7	9.7	10.8	10.8	10.8	10.8	12.1
82.5°	7.2	8.4	8.4	9.7	9.7	9.7	10.8	10.8	10.8	10.8	12.1
85°	8.4	8.4	9.7	9.7	9.7	9.7	10.8	10.8	10.8	10.8	12.1
87.5°	8.4	8.4	9.7	9.7	9.7	9.7	10.8	10.8	12.1	10.8	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219651

CATALOG NUMBER: LDSQA6A65950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3
2.5°	1043.4	973.5	925.3	907.3	872.4	816.9	784.4	754.3	697.6	685.6	654.3
5°	871.1	759.1	679.5	649.5	609.6	562.6	517.0	486.7	450.6	436.2	414.5
7.5°	686.8	574.7	506.0	481.9	454.3	415.7	374.7	344.6	307.3	287.9	269.9
10°	539.8	456.7	398.7	374.7	345.8	304.8	262.6	222.9	190.4	169.9	166.2
12.5°	438.6	369.8	308.5	283.1	249.4	208.4	178.4	177.0	174.6	173.6	176.0
15°	359.0	292.9	227.8	200.0	190.4	189.2	192.8	196.5	195.2	198.8	201.2
17.5°	295.3	224.1	209.7	210.9	212.1	215.7	221.7	231.3	232.5	238.6	243.4
20°	241.0	237.3	243.4	248.1	251.8	259.1	272.3	284.4	287.9	296.4	306.1
22.5°	273.4	284.4	297.6	303.7	308.5	321.7	336.1	355.5	362.6	373.5	386.7
25°	330.1	348.2	368.7	375.9	383.1	404.9	421.7	444.6	450.6	463.8	477.2
27.5°	377.1	396.4	418.1	427.8	433.8	455.4	469.9	484.3	484.3	491.5	501.2
30°	369.8	385.5	403.7	410.9	413.3	429.0	443.4	448.2	445.8	449.4	456.7
32.5°	307.3	319.3	333.7	339.8	342.2	353.0	365.0	365.0	363.9	363.9	368.7
35°	227.8	236.2	243.4	249.4	253.0	260.2	271.0	269.9	269.9	267.5	271.0
37.5°	153.0	157.8	166.2	168.6	169.9	174.6	183.1	183.1	180.8	182.0	184.4
40°	92.8	98.8	103.6	104.8	107.2	110.9	116.9	116.9	116.9	116.9	118.0
42.5°	55.3	59.0	62.7	62.7	63.8	68.7	71.1	71.1	71.1	71.1	72.3
45°	32.6	33.7	36.1	37.3	37.3	39.7	41.0	41.0	41.0	41.0	42.1
47.5°	19.2	20.5	20.5	21.6	21.6	22.9	24.0	24.0	22.9	22.9	22.9
50°	12.1	12.1	12.1	12.1	13.2	13.2	13.2	13.2	13.2	13.2	12.1
52.5°	9.7	9.7	9.7	9.7	8.4	8.4	8.4	8.4	7.2	7.2	6.0
55°	8.4	8.4	8.4	8.4	8.4	7.2	7.2	7.2	6.0	4.8	3.6
57.5°	8.4	8.4	8.4	8.4	8.4	7.2	7.2	6.0	4.8	4.8	3.6
60°	8.4	8.4	8.4	8.4	8.4	7.2	7.2	6.0	4.8	4.8	3.6
62.5°	9.7	9.7	8.4	8.4	8.4	7.2	7.2	6.0	6.0	4.8	3.6
65°	9.7	9.7	8.4	8.4	8.4	8.4	7.2	7.2	6.0	4.8	3.6
67.5°	9.7	9.7	9.7	9.7	8.4	8.4	8.4	7.2	6.0	4.8	3.6
70°	10.8	10.8	9.7	9.7	9.7	8.4	8.4	7.2	6.0	6.0	4.8
72.5°	10.8	10.8	9.7	9.7	9.7	9.7	8.4	7.2	7.2	6.0	4.8
75°	10.8	10.8	10.8	10.8	9.7	9.7	8.4	8.4	7.2	6.0	4.8
77.5°	10.8	10.8	10.8	10.8	9.7	9.7	9.7	8.4	7.2	6.0	4.8
80°	10.8	10.8	10.8	10.8	10.8	9.7	9.7	8.4	7.2	6.0	4.8
82.5°	12.1	12.1	10.8	10.8	10.8	9.7	9.7	8.4	7.2	6.0	6.0
85°	12.1	12.1	10.8	10.8	10.8	9.7	9.7	8.4	7.2	7.2	6.0
87.5°	12.1	12.1	10.8	10.8	10.8	9.7	9.7	8.4	7.2	7.2	6.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219651

CATALOG NUMBER: LDSQA6A65950D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3	1195.3
2.5°	635.0	598.8	586.8	595.2	585.5	578.3	568.7	563.9
5°	397.7	371.1	362.6	365.0	356.6	349.4	339.8	337.4
7.5°	244.6	219.3	209.7	209.7	200.0	191.6	185.6	182.0
10°	163.8	159.0	160.2	161.4	160.2	161.4	157.8	160.2
12.5°	176.0	173.6	176.0	177.0	177.0	179.6	174.6	178.4
15°	204.9	202.5	206.0	208.4	208.4	212.1	207.3	210.9
17.5°	250.6	249.4	255.4	257.8	259.1	265.0	259.1	263.8
20°	316.9	315.7	324.2	327.7	326.6	338.5	330.1	338.5
22.5°	402.5	400.1	412.2	415.7	416.9	432.5	425.4	431.4
25°	488.0	490.4	496.4	502.5	503.6	517.0	506.0	512.0
27.5°	506.0	502.5	506.0	513.3	514.4	520.5	511.0	515.7
30°	457.8	451.9	453.0	461.4	463.8	466.2	457.8	460.3
32.5°	372.3	362.6	362.6	371.1	373.5	377.1	362.6	368.7
35°	274.7	266.2	266.2	272.3	273.4	276.0	265.0	269.9
37.5°	188.0	180.8	183.1	185.6	186.8	189.2	188.0	186.8
40°	120.4	115.6	119.3	119.3	120.4	121.7	121.7	122.9
42.5°	73.5	69.9	72.3	72.3	73.5	73.5	73.5	74.8
45°	42.1	41.0	41.0	42.1	42.1	42.1	41.0	42.1
47.5°	22.9	21.6	22.9	22.9	22.9	22.9	22.9	22.9
50°	12.1	10.8	10.8	10.8	10.8	10.8	10.8	10.8
52.5°	6.0	4.8	4.8	4.8	3.6	4.8	3.6	3.6
55°	3.6	2.4	2.4	2.4	1.2	1.2	0.0	0.0
57.5°	2.4	1.2	1.2	1.2	0.0	0.0	0.0	0.0
60°	2.4	1.2	1.2	1.2	0.0	0.0	0.0	0.0
62.5°	2.4	1.2	1.2	1.2	0.0	0.0	0.0	0.0
65°	2.4	1.2	1.2	1.2	0.0	0.0	0.0	0.0
67.5°	3.6	2.4	1.2	1.2	1.2	0.0	0.0	0.0
70°	3.6	2.4	2.4	1.2	1.2	0.0	0.0	0.0
72.5°	3.6	2.4	2.4	2.4	1.2	1.2	0.0	0.0
75°	3.6	2.4	2.4	2.4	1.2	1.2	0.0	0.0
77.5°	3.6	3.6	2.4	2.4	1.2	1.2	1.2	0.0
80°	4.8	3.6	2.4	2.4	2.4	1.2	1.2	1.2
82.5°	4.8	3.6	2.4	2.4	2.4	1.2	1.2	1.2
85°	4.8	3.6	3.6	2.4	2.4	1.2	1.2	1.2
87.5°	4.8	3.6	3.6	2.4	2.4	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)