

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212692

Luminaire Tested: **LDSQA6A70930D010TE LARH20SP 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212692
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A70930D010TE LARH20SP 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4868.0 lumens
Efficiency: N/A
Efficacy: 62.3 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212692

CATALOG NUMBER: LDSQA6A70930D010TE LARH20SP 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212692

CATALOG NUMBER: LDSQA6A70930D010TE LARH20SP 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	45	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	59167	59167	59167
5°	114654	56385	19017
10°	194789	49347	8543
15°	300160	39359	13577
20°	434519	25613	23615
25°	637516	24718	30366
30°	741257	23416	23272
35°	750280	12404	12299
40°	621180	4676	5165
45°	469144	1589	1881
50°	320974	583	583
55°	44649	510	68
60°	1163	508	0
65°	295	693	0
70°	113	856	0
75°	0	1131	0
80°	0	1934	223
85°	0	3853	0

TEST NUMBER: P1212692

CATALOG NUMBER: LDSQA6A70930D010TE LARH20SP 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	3.0
10°-20°	609.4	12.5
20°-30°	1390.2	28.6
30°-40°	1608.8	33.0
40°-50°	970.3	19.9
50°-60°	131.8	2.7
60°-70°	4.3	0.1
70°-80°	4.6	0.1
80°-90°	4.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2143.8	44.0
0°-40°	3752.7	77.1
0°-60°	4854.8	99.7
0°-90°	4868.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4868.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1374	1374	1374	1374	1374	
5°	2653	2172	1305	714	440	309
15°	6734	3785	883	272	305	1994
25°	13420	4485	520	626	639	6073
35°	14274	3420	236	241	234	8602
45°	7705	931	26	32	31	6025
55°	595	7	7	5	1	1166
65°	3	4	7	4	0	4
75°	0	5	7	5	0	0
85°	0	5	8	5	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P1212692

CATALOG NUMBER: LDSQA6A70930D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2
2.5°	1987.4	1969.0	1976.8	1956.5	1905.2	1894.5	1893.6	1880.1	1836.5	1802.7	1762.0
5°	2652.8	2651.7	2656.7	2613.1	2523.2	2495.1	2481.6	2448.7	2343.2	2262.0	2172.0
7.5°	3483.5	3477.6	3471.9	3392.6	3251.4	3197.2	3162.4	3043.4	2898.4	2754.3	2593.8
10°	4455.4	4452.5	4430.3	4291.0	4064.7	3965.1	3897.4	3708.8	3475.8	3270.7	2998.1
12.5°	5584.0	5557.9	5518.2	5314.1	5003.7	4895.4	4746.6	4447.7	4089.8	3775.6	3394.6
15°	6733.9	6696.2	6625.6	6363.5	5978.6	5793.8	5609.1	5215.6	4730.0	4273.6	3785.2
17.5°	7858.6	7817.0	7651.7	7206.8	6830.6	6605.3	6400.3	5859.6	5289.0	4702.0	4083.0
20°	9483.4	9332.4	9044.4	8343.1	7644.0	7237.8	6997.9	6426.4	5720.4	5036.6	4294.9
22.5°	11653.6	11319.0	10704.8	9565.5	8566.6	7980.4	7587.8	6827.7	6030.8	5255.2	4425.5
25°	13419.5	13267.7	12569.3	10948.5	9389.5	8699.1	8152.7	7146.9	6257.2	5401.2	4485.4
27.5°	14557.7	14520.0	13722.2	12093.5	10061.7	9155.5	8545.3	7357.7	6366.4	5432.2	4456.4
30°	14909.7	14968.7	14202.8	12482.3	10256.1	9247.4	8580.1	7360.6	6282.2	5291.9	4270.8
32.5°	14883.6	14886.6	13947.4	12146.8	9939.8	8980.5	8290.0	7115.9	5971.8	4940.9	3917.7
35°	14274.4	14124.5	13062.5	11115.8	9203.9	8357.7	7715.5	6642.1	5460.3	4412.8	3419.6
37.5°	12936.8	12740.5	11502.7	9795.8	8332.5	7550.1	7031.8	6020.2	4851.0	3849.0	2905.1
40°	11052.0	10773.5	9752.2	8568.4	7378.9	6790.9	6355.8	5324.8	4199.1	3295.9	2422.6
42.5°	9165.1	9028.8	8353.8	7391.5	6577.2	6024.1	5569.5	4596.7	3572.4	2750.4	1812.3
45°	7704.8	7587.8	7134.3	6499.9	5701.0	5196.2	4758.1	3837.5	2775.6	1845.2	931.3
47.5°	6641.0	6546.3	6112.1	5445.7	4569.5	4017.3	3565.6	2516.4	1572.5	796.9	233.1
50°	4791.9	4695.2	4269.7	3498.0	2706.9	2244.6	1919.7	1123.7	445.8	161.5	24.2
52.5°	2349.1	2269.8	1980.7	1482.5	995.2	715.6	523.2	210.9	51.2	17.4	11.6
55°	594.8	546.4	455.5	286.3	140.3	84.1	54.2	19.4	12.6	9.6	6.8
57.5°	33.8	32.9	30.0	22.2	16.4	14.6	12.6	9.6	6.8	5.9	4.8
60°	13.5	12.6	11.6	9.6	7.8	6.8	6.8	4.8	3.9	3.9	3.9
62.5°	5.9	5.9	5.9	4.8	3.9	3.9	3.9	2.9	3.9	3.9	3.9
65°	2.9	2.9	2.9	2.0	2.0	2.0	2.9	2.9	2.9	3.9	3.9
67.5°	2.0	0.9	0.9	0.9	2.0	2.0	2.0	2.9	2.9	3.9	3.9
70°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.9	2.9	3.9	4.8
72.5°	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.9	2.9	3.9	4.8
75°	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.9	3.9	3.9	4.8
77.5°	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.9	3.9	3.9	4.8
80°	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.9	3.9	3.9	4.8
82.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	3.9	3.9	4.8
85°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	3.9	3.9	4.8
87.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	2.9	3.9	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212692

CATALOG NUMBER: LDSQA6A70930D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2
2.5°	1709.9	1675.0	1623.7	1589.9	1557.0	1526.1	1474.9	1445.9	1393.6	1345.2	1303.6
5°	2063.8	1976.8	1871.4	1781.4	1723.4	1666.3	1562.9	1486.4	1390.7	1304.6	1225.2
7.5°	2421.6	2267.8	2094.7	1946.8	1856.8	1768.8	1614.1	1490.3	1354.9	1232.1	1115.0
10°	2746.5	2515.4	2270.7	2058.9	1937.1	1823.0	1618.9	1454.6	1280.5	1128.7	981.6
12.5°	3048.2	2732.1	2412.9	2136.3	1985.5	1848.1	1598.6	1397.5	1190.5	1010.6	839.4
15°	3317.1	2911.0	2516.4	2180.8	2003.8	1841.3	1551.2	1317.2	1084.1	883.0	666.4
17.5°	3521.2	3022.2	2561.8	2174.0	1970.9	1790.1	1470.0	1216.7	971.0	727.2	482.6
20°	3644.9	3069.6	2552.2	2121.9	1900.3	1708.8	1373.3	1107.3	834.6	559.0	425.5
22.5°	3697.2	3065.7	2506.7	2043.5	1813.4	1619.9	1280.5	1001.0	691.5	505.8	444.0
25°	3705.9	3026.0	2442.8	1957.4	1727.2	1534.8	1186.6	880.1	600.6	520.3	497.1
27.5°	3639.2	2933.2	2323.0	1833.6	1606.4	1407.1	1046.4	699.3	563.8	518.3	533.8
30°	3441.9	2721.4	2111.2	1616.0	1396.5	1197.3	747.6	548.3	468.1	471.0	474.9
32.5°	3094.6	2369.4	1770.7	1297.8	1057.9	789.1	465.1	366.5	355.9	355.9	354.0
35°	2631.5	1939.1	1389.7	821.1	526.1	379.1	240.8	241.8	237.0	236.0	235.0
37.5°	2152.8	1530.0	880.1	339.4	228.3	158.6	142.2	144.0	142.2	145.1	143.1
40°	1697.3	944.8	321.1	108.3	80.2	77.4	79.3	81.2	81.2	83.2	83.2
42.5°	986.4	313.3	84.1	43.6	43.6	41.6	42.5	44.5	45.5	46.4	45.5
45°	293.0	64.7	27.0	24.2	24.2	23.3	23.3	24.2	25.1	26.1	26.1
47.5°	46.4	18.3	15.5	13.5	13.5	13.5	13.5	13.5	14.6	14.6	15.5
50°	14.6	11.6	9.6	8.7	8.7	7.8	7.8	8.7	8.7	8.7	9.6
52.5°	8.7	6.8	6.8	5.9	6.8	6.8	5.9	6.8	6.8	6.8	7.8
55°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.8	6.8	6.8
57.5°	4.8	4.8	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
60°	4.8	4.8	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.8
62.5°	4.8	4.8	5.9	5.9	5.9	5.9	5.9	5.9	6.8	6.8	6.8
65°	4.8	4.8	5.9	5.9	5.9	5.9	5.9	6.8	6.8	6.8	6.8
67.5°	4.8	5.9	5.9	5.9	5.9	6.8	6.8	6.8	6.8	6.8	6.8
70°	4.8	5.9	5.9	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
72.5°	4.8	5.9	5.9	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
75°	5.9	5.9	5.9	6.8	6.8	6.8	6.8	6.8	6.8	6.8	7.8
77.5°	5.9	5.9	6.8	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8
80°	5.9	5.9	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8
82.5°	5.9	5.9	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8
85°	5.9	5.9	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8
87.5°	5.9	5.9	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212692

CATALOG NUMBER: LDSQA6A70930D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2
2.5°	1267.9	1223.4	1202.1	1172.1	1150.9	1103.4	1084.1	1051.2	1024.1	979.7	982.5
5°	1157.6	1073.5	1016.5	971.9	940.9	865.5	815.2	762.1	713.7	653.8	631.5
7.5°	1004.8	901.3	814.3	761.2	721.5	620.9	509.6	422.6	356.8	309.5	291.1
10°	852.0	717.6	579.3	497.1	440.0	343.3	294.1	270.8	249.5	223.3	206.0
12.5°	674.1	482.6	356.8	324.0	300.8	268.8	237.0	211.8	216.6	217.6	224.4
15°	460.3	347.2	307.6	285.4	260.1	241.8	252.5	259.2	271.7	272.7	281.4
17.5°	374.3	325.9	294.1	293.0	295.0	305.6	322.0	330.7	347.2	351.0	363.6
20°	374.3	346.2	373.4	373.4	378.2	392.6	413.9	426.5	444.9	451.6	467.1
22.5°	426.5	445.8	479.7	483.6	485.4	501.0	528.1	540.7	561.9	565.8	582.1
25°	520.3	537.7	568.6	571.6	572.5	584.1	604.5	611.3	625.7	618.0	627.6
27.5°	550.3	558.0	577.3	579.3	574.5	579.3	587.1	587.1	591.9	576.4	579.3
30°	483.6	485.4	495.2	496.1	485.4	487.4	488.4	487.4	486.5	470.0	470.0
32.5°	358.8	358.8	371.4	368.4	356.8	359.7	359.7	359.7	358.8	345.3	343.3
35°	237.9	238.8	249.5	247.5	238.8	240.8	240.8	243.8	240.8	233.1	231.1
37.5°	145.1	146.0	150.9	151.8	149.0	149.9	150.9	149.9	151.8	147.9	146.0
40°	84.1	86.1	90.0	90.9	90.0	90.0	90.9	91.9	95.7	90.9	88.9
42.5°	49.3	50.3	52.3	52.3	52.3	52.3	53.2	54.2	55.1	54.2	53.2
45°	28.1	29.0	30.0	30.0	30.9	30.0	30.9	30.9	31.8	30.9	30.9
47.5°	16.4	16.4	17.4	17.4	18.3	17.4	18.3	18.3	18.3	17.4	17.4
50°	9.6	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	9.6	9.6
52.5°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	6.8	6.8	5.9	5.9
55°	6.8	6.8	6.8	6.8	6.8	6.8	5.9	4.8	4.8	3.9	3.9
57.5°	5.9	6.8	6.8	6.8	6.8	5.9	5.9	4.8	3.9	2.9	2.9
60°	6.8	6.8	6.8	6.8	5.9	5.9	5.9	4.8	3.9	2.9	2.9
62.5°	6.8	6.8	6.8	6.8	6.8	5.9	5.9	4.8	3.9	2.9	2.9
65°	6.8	6.8	6.8	6.8	6.8	5.9	5.9	4.8	3.9	2.9	2.9
67.5°	6.8	6.8	6.8	6.8	6.8	5.9	5.9	4.8	3.9	3.9	2.9
70°	6.8	7.8	7.8	6.8	6.8	6.8	5.9	4.8	4.8	3.9	2.9
72.5°	6.8	7.8	7.8	6.8	6.8	6.8	5.9	4.8	4.8	3.9	2.9
75°	7.8	7.8	7.8	7.8	6.8	6.8	5.9	5.9	4.8	3.9	2.9
77.5°	7.8	7.8	7.8	7.8	6.8	6.8	5.9	5.9	4.8	3.9	2.9
80°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.9	4.8	3.9	3.9
82.5°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.9	4.8	3.9	3.9
85°	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.9	4.8	3.9	2.9
87.5°	7.8	7.8	7.8	7.8	6.8	6.8	5.9	5.9	4.8	3.9	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212692

CATALOG NUMBER: LDSQA6A70930D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2	1374.2
2.5°	946.8	924.6	914.8	930.4	922.6	899.3	904.3	889.7
5°	564.7	530.9	509.6	519.4	488.4	460.3	460.3	440.0
7.5°	272.7	262.1	256.2	258.2	251.4	242.7	237.9	237.9
10°	191.5	187.6	188.6	188.6	194.4	193.4	196.3	195.4
12.5°	227.2	229.2	230.2	234.0	238.8	238.8	241.8	239.8
15°	291.1	289.1	295.0	295.9	303.7	304.6	308.5	304.6
17.5°	370.4	374.3	380.1	379.1	394.6	395.6	395.6	394.6
20°	476.8	479.7	485.4	487.4	505.8	507.8	514.5	515.4
22.5°	592.8	592.8	595.8	599.6	617.0	618.0	620.9	620.9
25°	632.4	626.7	627.6	632.4	642.2	638.3	641.2	639.2
27.5°	581.2	572.5	570.6	577.3	584.1	573.4	577.3	577.3
30°	471.9	464.2	462.3	469.0	473.8	462.3	466.2	468.1
32.5°	345.3	340.5	339.4	344.2	348.1	338.5	342.3	345.3
35°	233.1	231.1	229.2	230.2	236.0	228.3	232.0	234.0
37.5°	147.9	144.0	145.1	147.0	150.9	146.0	149.9	149.9
40°	90.9	88.9	88.9	90.9	92.8	88.9	90.9	91.9
42.5°	53.2	53.2	53.2	54.2	55.1	53.2	53.2	54.2
45°	30.9	30.0	30.0	30.9	31.8	30.0	30.9	30.9
47.5°	17.4	16.4	16.4	17.4	17.4	16.4	17.4	17.4
50°	9.6	8.7	8.7	9.6	9.6	8.7	8.7	8.7
52.5°	4.8	4.8	4.8	4.8	4.8	4.8	3.9	3.9
55°	2.9	2.9	2.0	2.0	2.0	2.0	2.0	0.9
57.5°	2.0	2.0	0.9	0.9	0.9	0.9	0.0	0.0
60°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
62.5°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
65°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
67.5°	2.0	2.0	0.9	0.9	0.9	0.0	0.0	0.0
70°	2.9	2.0	2.0	0.9	0.9	0.9	0.0	0.0
72.5°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
75°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
77.5°	2.9	2.0	2.0	2.0	0.9	0.9	0.9	0.0
80°	2.9	2.0	2.0	2.0	0.9	0.9	0.9	0.9
82.5°	2.9	2.0	2.0	2.0	0.9	0.9	0.9	0.9
85°	2.9	2.0	2.0	2.0	0.9	0.9	0.9	0.0
87.5°	2.9	2.0	2.0	2.0	0.9	0.9	0.9	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)