

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979582

Luminaire Tested: PRLX-241-927-LL1-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979582
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-927-LL1-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 241 SHADE WITH FROSTED LENS
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 502.3 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.07
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct


Input Watts (W): 7.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979582

CATALOG NUMBER: PRLX-241-927-LL1-F-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P979582

CATALOG NUMBER: PRLX-241-927-LL1-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		93
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		86
3	102	95	90	86	100	93	89	85	91	87	83		88	85	82		79
4	96	88	82	78	94	87	82	77	85	80	77		83	79	76		73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		68
6	86	77	70	66	84	76	70	65	74	69	65		73	68	65		63
7	81	71	65	61	80	71	65	61	69	64	60		68	63	60		58
8	77	67	61	56	76	66	60	56	65	60	56		64	59	56		54
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		50
10	69	59	53	49	68	58	53	49	58	52	49		57	52	48		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3343
5°	3288
10°	3199
15°	3118
20°	3078
25°	3035
30°	2982
35°	2622
40°	1164
45°	146
50°	34
55°	38
60°	39
65°	38
70°	32
75°	33
80°	31
85°	35

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 146 cd/sqm

TEST NUMBER: P979582

CATALOG NUMBER: PRLX-241-927-LL1-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.0	8.0
10°-20°	110.4	22.0
20°-30°	164.4	32.7
30°-40°	158.6	31.6
40°-50°	23.1	4.6
50°-60°	2.4	0.5
60°-70°	2.0	0.4
70°-80°	1.1	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	314.8	62.7
0°-40°	473.4	94.2
0°-60°	498.9	99.3
0°-90°	502.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	502.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	434	
5°	425	40
15°	391	110
25°	357	164
35°	279	159
45°	13	23
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P979582

CATALOG NUMBER: PRLX-241-927-LL1-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	433.7
2.5°	431.6
5°	424.9
7.5°	416.1
10°	408.7
12.5°	398.8
15°	390.7
17.5°	382.9
20°	375.2
22.5°	367.1
25°	356.8
27.5°	346.3
30°	335.0
32.5°	317.0
35°	278.6
37.5°	206.3
40°	115.7
42.5°	48.0
45°	13.4
47.5°	4.2
50°	2.8
52.5°	2.8
55°	2.8
57.5°	2.5
60°	2.5
62.5°	2.1
65°	2.1
67.5°	1.8
70°	1.4
72.5°	1.4
75°	1.1
77.5°	0.7
80°	0.7
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

TEST NUMBER: P979582

CATALOG NUMBER: PRLX-241-927-LL1-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT