

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212698

Luminaire Tested: **LDSQA6A70935D010TE LARH20SP 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212698
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A70935D010TE LARH20SP 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5196.4 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212698

CATALOG NUMBER: LDSQA6A70935D010TE LARH20SP 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212698

CATALOG NUMBER: LDSQA6A70935D010TE LARH20SP 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	45	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	63158	63158	63158
5°	122386	60193	20300
10°	207932	52669	9116
15°	320410	42011	14491
20°	463834	27340	25214
25°	680523	26385	32419
30°	791266	24992	24838
35°	800897	13240	13135
40°	663086	4991	5508
45°	500801	1693	2009
50°	342630	616	616
55°	47659	548	75
60°	1240	534	0
65°	316	744	0
70°	126	919	0
75°	0	1214	0
80°	0	2058	248
85°	0	4100	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212698

CATALOG NUMBER: LDSQA6A70935D010TE LARH20SP 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.9	3.0
10°-20°	650.5	12.5
20°-30°	1484.0	28.6
30°-40°	1717.4	33.0
40°-50°	1035.7	19.9
50°-60°	140.7	2.7
60°-70°	4.6	0.1
70°-80°	5.0	0.1
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2288.5	44.0
0°-40°	4005.8	77.1
0°-60°	5182.3	99.7
0°-90°	5196.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5196.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1467	1467	1467	1467	1467	
5°	2832	2319	1393	762	470	330
15°	7188	4041	942	290	325	2128
25°	14325	4788	555	668	682	6483
35°	15237	3650	252	257	250	9183
45°	8225	994	28	34	33	6431
55°	635	7	7	5	1	1245
65°	3	4	7	4	0	5
75°	0	5	7	5	0	0
85°	0	5	8	5	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212698

CATALOG NUMBER: LDSQA6A70935D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9
2.5°	2121.5	2101.8	2110.2	2088.5	2033.7	2022.4	2021.4	2006.9	1960.4	1924.3	1881.0
5°	2831.7	2830.8	2835.8	2789.4	2693.3	2663.4	2649.0	2613.9	2501.3	2414.6	2318.7
7.5°	3718.5	3712.3	3706.2	3621.4	3470.7	3412.9	3375.7	3248.8	3094.0	2940.1	2768.7
10°	4756.0	4752.9	4729.1	4580.6	4338.9	4232.7	4160.4	3959.0	3710.2	3491.4	3200.2
12.5°	5960.8	5932.9	5890.6	5672.7	5341.3	5225.7	5066.8	4747.7	4365.8	4030.3	3623.5
15°	7188.2	7147.9	7072.6	6792.9	6382.0	6184.8	5987.5	5567.4	5049.2	4562.0	4040.7
17.5°	8388.8	8344.4	8167.9	7693.0	7291.4	7050.9	6832.0	6255.0	5645.9	5019.3	4358.5
20°	10123.2	9962.2	9654.4	8906.0	8159.7	7726.0	7470.1	6860.0	6106.4	5376.4	4584.6
22.5°	12439.7	12082.6	11427.0	10211.0	9144.5	8518.9	8099.8	7288.3	6437.7	5609.8	4724.1
25°	14324.8	14162.7	13417.4	11687.1	10023.0	9285.9	8702.7	7629.0	6679.3	5765.6	4788.0
27.5°	15539.9	15499.6	14647.9	12909.5	10740.5	9773.1	9121.8	7854.1	6795.9	5798.7	4757.1
30°	15915.6	15978.7	15161.0	13324.5	10948.0	9871.3	9159.0	7857.2	6706.0	5649.0	4558.8
32.5°	15887.8	15890.9	14888.5	12966.2	10610.5	9586.3	8849.2	7596.0	6374.7	5274.2	4182.0
35°	15237.4	15077.4	13943.9	11865.8	9824.9	8921.5	8236.0	7090.2	5828.7	4710.6	3650.4
37.5°	13809.6	13600.1	12278.8	10456.7	8894.7	8059.5	7506.2	6426.3	5178.3	4108.8	3101.2
40°	11797.6	11500.3	10410.1	9146.5	7876.8	7249.1	6784.6	5684.1	4482.4	3518.2	2586.0
42.5°	9783.5	9637.9	8917.4	7890.2	7020.9	6430.4	5945.3	4906.7	3813.4	2936.0	1934.7
45°	8224.7	8099.8	7615.7	6938.4	6085.7	5546.8	5079.1	4096.3	2962.8	1969.8	994.1
47.5°	7089.2	6987.9	6524.4	5813.1	4877.9	4288.3	3806.3	2686.2	1678.6	850.6	248.8
50°	5115.2	5012.0	4557.8	3734.0	2889.5	2396.0	2049.2	1199.6	475.9	172.4	25.9
52.5°	2507.6	2422.9	2114.2	1582.6	1062.2	763.9	558.5	225.0	54.7	18.6	12.4
55°	634.9	583.3	486.2	305.6	149.6	89.8	57.8	20.7	13.4	10.3	7.3
57.5°	36.1	35.1	32.0	23.8	17.6	15.5	13.4	10.3	7.3	6.2	5.2
60°	14.4	13.4	12.4	10.3	8.3	7.3	7.3	5.2	4.2	4.2	4.2
62.5°	6.2	6.2	6.2	5.2	4.2	4.2	4.2	3.1	4.2	4.2	4.2
65°	3.1	3.1	3.1	2.1	2.1	2.1	3.1	3.1	3.1	4.2	4.2
67.5°	2.1	1.0	1.0	1.0	2.1	2.1	2.1	3.1	3.1	4.2	4.2
70°	1.0	1.0	1.0	1.0	2.1	2.1	2.1	3.1	3.1	4.2	5.2
72.5°	0.0	1.0	1.0	1.0	2.1	2.1	2.1	3.1	3.1	4.2	5.2
75°	0.0	1.0	1.0	1.0	2.1	2.1	2.1	3.1	4.2	4.2	5.2
77.5°	0.0	1.0	1.0	1.0	2.1	2.1	2.1	3.1	4.2	4.2	5.2
80°	0.0	1.0	1.0	1.0	2.1	2.1	2.1	3.1	4.2	4.2	5.2
82.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.1	4.2	4.2	5.2
85°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.1	4.2	4.2	5.2
87.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.1	3.1	4.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212698

CATALOG NUMBER: LDSQA6A70935D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9
2.5°	1825.2	1788.0	1733.3	1697.2	1662.0	1629.0	1574.3	1543.4	1487.6	1436.0	1391.6
5°	2203.0	2110.2	1997.6	1901.6	1839.6	1778.8	1668.3	1586.6	1484.5	1392.7	1307.9
7.5°	2585.0	2420.9	2236.0	2078.0	1982.1	1888.1	1723.0	1590.8	1446.2	1315.2	1190.3
10°	2931.9	2685.2	2424.0	2197.9	2067.8	1946.0	1728.1	1552.6	1366.8	1204.7	1047.8
12.5°	3253.9	2916.4	2575.7	2280.5	2119.4	1972.8	1706.5	1491.8	1270.9	1078.7	896.1
15°	3540.9	3107.4	2686.2	2327.9	2139.0	1965.6	1655.9	1406.1	1157.3	942.5	711.2
17.5°	3758.8	3226.1	2734.7	2320.8	2103.9	1910.9	1569.1	1298.7	1036.5	776.4	515.2
20°	3890.9	3276.6	2724.4	2265.0	2028.5	1824.2	1465.9	1182.1	890.9	596.7	454.2
22.5°	3946.7	3272.5	2675.8	2181.4	1935.7	1729.1	1366.8	1068.5	738.1	539.9	473.8
25°	3955.9	3230.2	2607.7	2089.5	1843.8	1638.4	1266.7	939.4	641.0	555.4	530.7
27.5°	3884.7	3131.0	2479.8	1957.3	1714.7	1502.0	1117.0	746.3	601.9	553.3	569.8
30°	3674.1	2905.0	2253.6	1725.1	1490.7	1278.0	797.9	585.4	499.6	502.7	506.9
32.5°	3303.6	2529.3	1890.2	1385.4	1129.4	842.4	496.6	391.3	379.9	379.9	377.8
35°	2809.0	2069.9	1483.4	876.5	561.6	404.7	257.0	258.0	253.0	251.9	250.9
37.5°	2298.0	1633.2	939.4	362.3	243.6	169.3	151.7	153.8	151.7	154.8	152.8
40°	1811.8	1008.5	342.7	115.6	85.7	82.6	84.6	86.7	86.7	88.8	88.8
42.5°	1053.0	334.5	89.8	46.4	46.4	44.3	45.4	47.4	48.5	49.5	48.5
45°	312.8	69.2	28.9	25.9	25.9	24.8	24.8	25.9	26.8	27.8	27.8
47.5°	49.5	19.6	16.5	14.4	14.4	14.4	14.4	14.4	15.5	15.5	16.5
50°	15.5	12.4	10.3	9.2	9.2	8.3	8.3	9.2	9.2	9.2	10.3
52.5°	9.2	7.3	7.3	6.2	7.3	7.3	6.2	7.3	7.3	7.3	8.3
55°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3
57.5°	5.2	5.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
60°	5.2	5.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	7.3
62.5°	5.2	5.2	6.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3
65°	5.2	5.2	6.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3
67.5°	5.2	6.2	6.2	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3
70°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
72.5°	5.2	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
75°	6.2	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	8.3
77.5°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3	8.3	8.3	8.3
80°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3
82.5°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3
85°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3
87.5°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	8.3	8.3	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212698

CATALOG NUMBER: LDSQA6A70935D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9
2.5°	1353.4	1306.0	1283.2	1251.2	1228.5	1177.9	1157.3	1122.2	1093.3	1045.7	1048.8
5°	1235.8	1146.0	1085.0	1037.5	1004.5	923.9	870.2	813.5	761.9	697.8	674.2
7.5°	1072.6	962.1	869.2	812.5	770.1	662.7	544.1	451.1	380.9	330.3	310.7
10°	909.5	766.0	618.4	530.7	469.7	366.5	313.8	289.1	266.4	238.4	219.8
12.5°	719.6	515.2	380.9	345.8	321.1	287.0	253.0	226.1	231.3	232.3	239.5
15°	491.4	370.6	328.2	304.6	277.7	258.0	269.5	276.6	290.0	291.1	300.4
17.5°	399.5	347.9	313.8	312.8	314.9	326.2	343.7	353.1	370.6	374.8	388.2
20°	399.5	369.6	398.4	398.4	403.7	419.1	441.9	455.3	474.9	482.0	498.7
22.5°	455.3	475.9	512.1	516.2	518.2	534.7	563.7	577.1	599.8	604.0	621.5
25°	555.4	574.0	607.0	610.1	611.1	623.5	645.2	652.5	667.9	659.6	670.0
27.5°	587.3	595.7	616.3	618.4	613.2	618.4	626.6	626.6	631.8	615.3	618.4
30°	516.2	518.2	528.6	529.6	518.2	520.3	521.3	520.3	519.2	501.7	501.7
32.5°	383.0	383.0	396.4	393.4	380.9	384.0	384.0	384.0	383.0	368.6	366.5
35°	254.0	254.9	266.4	264.3	254.9	257.0	257.0	260.1	257.0	248.8	246.7
37.5°	154.8	155.9	161.1	162.1	159.0	160.0	161.1	160.0	162.1	158.0	155.9
40°	89.8	91.9	96.1	97.0	96.1	96.1	97.0	98.0	102.2	97.0	95.0
42.5°	52.6	53.7	55.8	55.8	55.8	55.8	56.8	57.8	58.9	57.8	56.8
45°	29.9	30.9	32.0	32.0	33.0	32.0	33.0	33.0	34.1	33.0	33.0
47.5°	17.6	17.6	18.6	18.6	19.6	18.6	19.6	19.6	19.6	18.6	18.6
50°	10.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	10.3	10.3
52.5°	8.3	8.3	8.3	8.3	8.3	7.3	7.3	7.3	7.3	6.2	6.2
55°	7.3	7.3	7.3	7.3	7.3	7.3	6.2	5.2	5.2	4.2	4.2
57.5°	6.2	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.2	3.1	3.1
60°	7.3	7.3	7.3	7.3	6.2	6.2	6.2	5.2	4.2	3.1	3.1
62.5°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.2	3.1	3.1
65°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.2	3.1	3.1
67.5°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	5.2	4.2	4.2	3.1
70°	7.3	8.3	8.3	7.3	7.3	7.3	6.2	5.2	5.2	4.2	3.1
72.5°	7.3	8.3	8.3	7.3	7.3	7.3	6.2	5.2	5.2	4.2	3.1
75°	8.3	8.3	8.3	8.3	7.3	7.3	6.2	6.2	5.2	4.2	3.1
77.5°	8.3	8.3	8.3	8.3	7.3	7.3	6.2	6.2	5.2	4.2	3.1
80°	8.3	8.3	8.3	8.3	8.3	7.3	7.3	6.2	5.2	4.2	4.2
82.5°	8.3	8.3	8.3	8.3	8.3	7.3	7.3	6.2	5.2	4.2	4.2
85°	8.3	8.3	8.3	8.3	8.3	7.3	7.3	6.2	5.2	4.2	3.1
87.5°	8.3	8.3	8.3	8.3	7.3	7.3	6.2	6.2	5.2	4.2	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212698

CATALOG NUMBER: LDSQA6A70935D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9	1466.9
2.5°	1010.6	987.0	976.6	993.1	984.9	960.0	965.2	949.8
5°	602.9	566.8	544.1	554.3	521.3	491.4	491.4	469.7
7.5°	291.1	279.8	273.5	275.6	268.4	259.1	254.0	254.0
10°	204.4	200.3	201.4	201.4	207.5	206.4	209.6	208.5
12.5°	242.6	244.7	245.7	249.9	254.9	254.9	258.0	256.0
15°	310.7	308.6	314.9	315.9	324.2	325.1	329.3	325.1
17.5°	395.3	399.5	405.7	404.7	421.2	422.2	422.2	421.2
20°	509.0	512.1	518.2	520.3	539.9	542.0	549.2	550.3
22.5°	632.8	632.8	636.0	640.0	658.6	659.6	662.7	662.7
25°	675.1	669.0	670.0	675.1	685.5	681.3	684.4	682.4
27.5°	620.5	611.1	609.1	616.3	623.5	612.2	616.3	616.3
30°	503.8	495.6	493.5	500.6	505.8	493.5	497.6	499.6
32.5°	368.6	363.4	362.3	367.5	371.7	361.3	365.4	368.6
35°	248.8	246.7	244.7	245.7	251.9	243.6	247.8	249.9
37.5°	158.0	153.8	154.8	156.9	161.1	155.9	160.0	160.0
40°	97.0	95.0	95.0	97.0	99.1	95.0	97.0	98.0
42.5°	56.8	56.8	56.8	57.8	58.9	56.8	56.8	57.8
45°	33.0	32.0	32.0	33.0	34.1	32.0	33.0	33.0
47.5°	18.6	17.6	17.6	18.6	18.6	17.6	18.6	18.6
50°	10.3	9.2	9.2	10.3	10.3	9.2	9.2	9.2
52.5°	5.2	5.2	5.2	5.2	5.2	5.2	4.2	4.2
55°	3.1	3.1	2.1	2.1	2.1	2.1	2.1	1.0
57.5°	2.1	2.1	1.0	1.0	1.0	1.0	0.0	0.0
60°	2.1	2.1	1.0	1.0	1.0	0.0	0.0	0.0
62.5°	2.1	2.1	1.0	1.0	1.0	0.0	0.0	0.0
65°	2.1	2.1	1.0	1.0	1.0	0.0	0.0	0.0
67.5°	2.1	2.1	1.0	1.0	1.0	0.0	0.0	0.0
70°	3.1	2.1	2.1	1.0	1.0	1.0	0.0	0.0
72.5°	3.1	2.1	2.1	2.1	1.0	1.0	0.0	0.0
75°	3.1	2.1	2.1	2.1	1.0	1.0	0.0	0.0
77.5°	3.1	2.1	2.1	2.1	1.0	1.0	1.0	0.0
80°	3.1	2.1	2.1	2.1	1.0	1.0	1.0	1.0
82.5°	3.1	2.1	2.1	2.1	1.0	1.0	1.0	1.0
85°	3.1	2.1	2.1	2.1	1.0	1.0	1.0	0.0
87.5°	3.1	2.1	2.1	2.1	1.0	1.0	1.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)