

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979593

Luminaire Tested: PRLX-241-927-LL2-F-U-S-WHTE-X

Issue Date: 4/3/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P979593  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/3/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-241-927-LL2-F-U-S-WHTE-X  
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE 241 SHADE WITH FROSTED LENS  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1372.5 lumens  
Efficiency: N/A  
Efficacy: 124.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.12  
Luminous Opening: Circular (Dia: 1.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 11  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P979593  
CATALOG NUMBER: PRLX-241-927-LL2-F-U-S-WHTE-X

### Luminous Intensity Polar Plot





TEST NUMBER: P979593

CATALOG NUMBER: PRLX-241-927-LL2-F-U-S-WHTE-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88													88															
2	103	96	90	85	100	94	89	84	90	86	82	87	84	81	84	81	79	77													77															
3	95	86	80	74	93	85	79	73	82	77	72	79	75	71	77	73	70	68													68															
4	89	78	71	65	87	77	70	65	75	69	64	73	67	63	71	66	62	61													61															
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54													54															
6	77	66	58	52	76	65	58	52	63	57	52	62	56	51	60	55	51	49													49															
7	72	61	53	48	71	60	53	47	58	52	47	57	51	47	56	51	47	45													45															
8	68	56	49	43	67	55	48	43	54	48	43	53	47	43	52	47	43	41													41															
9	64	52	45	40	63	52	45	40	51	44	40	50	44	39	49	43	39	38													38															
10	60	49	42	37	59	48	41	37	47	41	37	46	41	36	46	40	36	35													35															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	6238
5°	6158
10°	6016
15°	5916
20°	5890
25°	5879
30°	5845
35°	5452
40°	3356
45°	1764
50°	1638
55°	1711
60°	1772
65°	1758
70°	1709
75°	1626
80°	1532
85°	1415

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 62.5°  
 Luminance: 1773 cd/sqm

TEST NUMBER: P979593

CATALOG NUMBER: PRLX-241-927-LL2-F-U-S-WHTE-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.1	5.5
10°-20°	209.7	15.3
20°-30°	318.4	23.2
30°-40°	339.3	24.7
40°-50°	145.0	10.6
50°-60°	113.7	8.3
60°-70°	95.1	6.9
70°-80°	57.9	4.2
80°-90°	18.3	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	603.3	44.0
0°-40°	942.6	68.7
0°-60°	1201.2	87.5
0°-90°	1372.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1372.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	809	
5°	796	75
15°	741	210
25°	691	318
35°	579	339
45°	162	145
55°	127	114
65°	96	95
75°	55	58
85°	16	18
90°	0	

TEST NUMBER: P979593

CATALOG NUMBER: PRLX-241-927-LL2-F-U-S-WHTE-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	809.2
2.5°	806.6
5°	795.8
7.5°	781.9
10°	768.5
12.5°	755.1
15°	741.2
17.5°	730.4
20°	718.0
22.5°	706.6
25°	691.2
27.5°	674.2
30°	656.6
32.5°	631.9
35°	579.3
37.5°	478.8
40°	333.5
42.5°	220.1
45°	161.8
47.5°	141.7
50°	136.6
52.5°	132.5
55°	127.3
57.5°	122.2
60°	114.9
62.5°	106.2
65°	96.4
67.5°	86.1
70°	75.8
72.5°	64.9
75°	54.6
77.5°	44.8
80°	34.5
82.5°	25.3
85°	16.0
87.5°	8.8
90°	0.0



TEST NUMBER: P979593  
 CATALOG NUMBER: PRLX-241-927-LL2-F-U-S-WHTE-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.37	13.71	12.73	14.02	14.34	12.37	13.71	12.73	14.02	14.34
	3H	14.37	15.57	14.75	15.90	16.27	14.37	15.57	14.75	15.90	16.27
	4H	15.13	16.25	15.53	16.60	16.99	15.13	16.25	15.53	16.60	16.99
	6H	15.71	16.75	16.13	17.12	17.51	15.71	16.75	16.13	17.12	17.51
	8H	15.91	16.90	16.34	17.29	17.69	15.91	16.90	16.34	17.29	17.69
	12H	16.05	16.99	16.48	17.38	17.81	16.05	16.99	16.48	17.38	17.81
4H	2H	13.04	14.16	13.44	14.51	14.90	13.04	14.16	13.44	14.51	14.90
	3H	15.24	16.17	15.65	16.58	16.98	15.24	16.17	15.65	16.58	16.98
	4H	16.12	16.96	16.55	17.38	17.82	16.12	16.96	16.55	17.38	17.82
	6H	16.83	17.57	17.29	18.01	18.48	16.83	17.57	17.29	18.01	18.48
	8H	17.08	17.77	17.55	18.22	18.69	17.08	17.77	17.55	18.22	18.69
	12H	17.27	17.88	17.76	18.36	18.83	17.27	17.88	17.76	18.36	18.83
8H	4H	16.44	17.12	16.91	17.57	18.04	16.44	17.12	16.91	17.57	18.04
	6H	17.29	17.85	17.79	18.35	18.83	17.29	17.85	17.79	18.35	18.83
	8H	17.63	18.14	18.15	18.65	19.14	17.63	18.14	18.15	18.65	19.14
	12H	17.91	18.35	18.43	18.85	19.42	17.91	18.35	18.43	18.85	19.42
12H	4H	16.47	17.07	16.95	17.56	18.03	16.47	17.07	16.95	17.56	18.03
	6H	17.36	17.86	17.88	18.37	18.86	17.36	17.86	17.88	18.37	18.86
	8H	17.76	18.20	18.28	18.70	19.27	17.76	18.20	18.28	18.70	19.27