

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208997

Luminaire Tested: **LDSQA6A75830D010TE LARH40FL 6LSQA1H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P208997  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26677)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDSQA6A75830D010TE LARH40FL 6LSQA1H  
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,  
SELF-FLANGED, 40° FLOOD  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6922.2 lumens  
Efficiency: N/A  
Efficacy: 87.1 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.61  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 79.45  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P208997

CATALOG NUMBER: LDSQA6A75830D010TE LARH40FL 6LSQA1H

### Luminous Intensity Polar Plot





TEST NUMBER: P208997

CATALOG NUMBER: LDSQA6A75830D010TE LARH40FL 6LSQA1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 115 | 112 | 110 | 109 |  | 112 | 110 | 108 | 107 |  | 106 | 105 | 104 |  | 103 | 101 | 100 |  | 99  | 98  | 98  |
| 2   | 110 | 107 | 103 | 101 |  | 108 | 105 | 102 | 100 |  | 102 | 99  | 97  |  | 99  | 97  | 95  |  | 96  | 95  | 93  |
| 3   | 107 | 101 | 98  | 94  |  | 105 | 100 | 97  | 94  |  | 98  | 95  | 92  |  | 95  | 93  | 91  |  | 93  | 91  | 89  |
| 4   | 103 | 97  | 93  | 89  |  | 101 | 96  | 92  | 89  |  | 94  | 90  | 88  |  | 92  | 89  | 87  |  | 90  | 88  | 86  |
| 5   | 99  | 93  | 88  | 85  |  | 98  | 92  | 88  | 84  |  | 90  | 87  | 84  |  | 89  | 85  | 83  |  | 87  | 85  | 82  |
| 6   | 96  | 89  | 84  | 81  |  | 94  | 88  | 84  | 81  |  | 87  | 83  | 80  |  | 85  | 82  | 80  |  | 84  | 81  | 79  |
| 7   | 92  | 85  | 81  | 77  |  | 91  | 85  | 80  | 77  |  | 84  | 80  | 77  |  | 82  | 79  | 76  |  | 81  | 78  | 76  |
| 8   | 89  | 82  | 77  | 74  |  | 88  | 82  | 77  | 74  |  | 81  | 77  | 74  |  | 80  | 76  | 74  |  | 79  | 76  | 73  |
| 9   | 86  | 79  | 74  | 71  |  | 85  | 79  | 74  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 71  |  | 76  | 73  | 71  |
| 10  | 84  | 76  | 72  | 69  |  | 83  | 76  | 71  | 69  |  | 75  | 71  | 68  |  | 74  | 71  | 68  |  | 74  | 70  | 68  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 771372 |
| 5°  | 671554 |
| 10° | 606775 |
| 15° | 554427 |
| 20° | 405983 |
| 25° | 200336 |
| 30° | 44481  |
| 35° | 9009   |
| 40° | 1501   |
| 45° | 444    |
| 50° | 80     |
| 55° | 90     |
| 60° | 103    |
| 65° | 122    |
| 70° | 151    |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P208997

CATALOG NUMBER: LDSQA6A75830D010TE LARH40FL 6LSQA1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1440.3 | 20.8      |
| 10°-20°   | 3342.1 | 48.3      |
| 20°-30°   | 1960.4 | 28.3      |
| 30°-40°   | 169.6  | 2.5       |
| 40°-50°   | 7.4    | 0.1       |
| 50°-60°   | 1.1    | 0.0       |
| 60°-70°   | 1.2    | 0.0       |
| 70°-80°   | 0.2    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 6742.8 | 97.4      |
| 0°-40°    | 6912.4 | 99.9      |
| 0°-60°    | 6920.8 | 100.0     |
| 0°-90°    | 6922.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 6922.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 17916 |      |
| 5°  | 15538 | ###  |
| 15° | 12438 | 3342 |
| 25° | 4217  | 1960 |
| 35° | 171   | 170  |
| 45° | 7     | 7    |
| 55° | 1     | 1    |
| 65° | 1     | 1    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P208997

CATALOG NUMBER: LDSQA6A75830D010TE LARH40FL 6LSQA1H

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 17915.7 |
| 2.5°  | 16835.0 |
| 5°    | 15538.0 |
| 7.5°  | 14674.9 |
| 10°   | 13878.7 |
| 12.5° | 13216.2 |
| 15°   | 12438.2 |
| 17.5° | 11093.7 |
| 20°   | 8860.6  |
| 22.5° | 6407.5  |
| 25°   | 4217.0  |
| 27.5° | 2376.5  |
| 30°   | 894.7   |
| 32.5° | 461.9   |
| 35°   | 171.4   |
| 37.5° | 52.3    |
| 40°   | 26.7    |
| 42.5° | 14.6    |
| 45°   | 7.3     |
| 47.5° | 3.6     |
| 50°   | 1.2     |
| 52.5° | 1.2     |
| 55°   | 1.2     |
| 57.5° | 1.2     |
| 60°   | 1.2     |
| 62.5° | 1.2     |
| 65°   | 1.2     |
| 67.5° | 1.2     |
| 70°   | 1.2     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)