

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979700

Luminaire Tested: PRLX-241-930-LL5-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-930-LL5-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 241 SHADE WITH CLEAR LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2058.0 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.05
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 29.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979700
CATALOG NUMBER: PRLX-241-930-LL5-C-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979700

CATALOG NUMBER: PRLX-241-930-LL5-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93
2	108	103	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64
7	82	72	66	62	81	72	66	62	70	65	61	69	65	61	68	64	61	59
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	57	55
9	74	64	58	54	73	63	57	53	62	57	53	61	57	53	61	56	53	51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	14923
5°	14230
10°	13553
15°	13245
20°	13158
25°	13067
30°	12930
35°	12158
40°	1871
45°	304
50°	143
55°	142
60°	163
65°	170
70°	149
75°	158
80°	120
85°	115

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 304 cd/sqm

TEST NUMBER: P979700

CATALOG NUMBER: PRLX-241-930-LL5-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.1	8.4
10°-20°	469.6	22.8
20°-30°	707.7	34.4
30°-40°	645.4	31.4
40°-50°	37.9	1.8
50°-60°	9.6	0.5
60°-70°	8.7	0.4
70°-80°	5.1	0.2
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1349.3	65.6
0°-40°	1994.8	96.9
0°-60°	2042.4	99.2
0°-90°	2058.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2058.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1936	
5°	1839	172
15°	1660	470
25°	1536	708
35°	1292	645
45°	28	38
55°	11	10
65°	9	9
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P979700

CATALOG NUMBER: PRLX-241-930-LL5-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1935.8
2.5°	1910.6
5°	1838.9
7.5°	1773.8
10°	1731.3
12.5°	1692.8
15°	1659.6
17.5°	1631.8
20°	1603.9
22.5°	1577.3
25°	1536.2
27.5°	1492.3
30°	1452.5
32.5°	1406.0
35°	1291.9
37.5°	695.7
40°	185.9
42.5°	62.4
45°	27.9
47.5°	14.6
50°	11.9
52.5°	10.6
55°	10.6
57.5°	10.6
60°	10.6
62.5°	9.3
65°	9.3
67.5°	8.0
70°	6.6
72.5°	5.3
75°	5.3
77.5°	4.0
80°	2.7
82.5°	2.7
85°	1.3
87.5°	1.3
90°	0.0



TEST NUMBER: P979700
 CATALOG NUMBER: PRLX-241-930-LL5-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.33	0.00	0.00	0.00	0.00	0.33
	8H	0.00	0.00	0.00	0.11	0.58	0.00	0.00	0.00	0.11	0.58
	12H	0.00	0.00	0.00	0.26	0.74	0.00	0.00	0.00	0.26	0.74
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.16	0.65	0.00	0.00	0.00	0.16	0.65
	8H	0.00	0.03	0.27	0.56	1.05	0.00	0.03	0.27	0.56	1.05
	12H	0.01	0.26	0.53	0.76	1.35	0.01	0.26	0.53	0.76	1.35
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.20	0.69	0.00	0.00	0.00	0.20	0.69
	8H	0.00	0.11	0.38	0.61	1.20	0.00	0.11	0.38	0.61	1.20