

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979770

Luminaire Tested: PRLX-241-935-31L-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P979770
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-935-31L-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 241 SHADE WITH CLEAR LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1550.0 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.05
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979770

CATALOG NUMBER: PRLX-241-935-31L-C-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P979770

CATALOG NUMBER: PRLX-241-935-31L-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97
2	108	103	98	95	105	101	97	94	98	94	92		95	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	83	79	95	88	82	78	85	81	77		83	80	76		82
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	72	66	62	81	72	66	62	70	65	61		69	65	61		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	57	53	62	57	53		61	57	53		61
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	11240
5°	10718
10°	10208
15°	9976
20°	9910
25°	9841
30°	9738
35°	9157
40°	1409
45°	229
50°	108
55°	108
60°	123
65°	128
70°	113
75°	119
80°	89
85°	88

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 229 cd/sqm

TEST NUMBER: P979770

CATALOG NUMBER: PRLX-241-935-31L-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.6	8.4
10°-20°	353.7	22.8
20°-30°	533.0	34.4
30°-40°	486.1	31.4
40°-50°	28.6	1.8
50°-60°	7.3	0.5
60°-70°	6.6	0.4
70°-80°	3.8	0.2
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1016.3	65.6
0°-40°	1502.4	96.9
0°-60°	1538.3	99.2
0°-90°	1550.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1550.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1458	
5°	1385	130
15°	1250	354
25°	1157	533
35°	973	486
45°	21	29
55°	8	7
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P979770

CATALOG NUMBER: PRLX-241-935-31L-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1458
2.5°	1439
5°	1385
7.5°	1336
10°	1304
12.5°	1275
15°	1250
17.5°	1229
20°	1208
22.5°	1188
25°	1157
27.5°	1124
30°	1094
32.5°	1059
35°	973
37.5°	524
40°	140
42.5°	47
45°	21
47.5°	11
50°	9
52.5°	8
55°	8
57.5°	8
60°	8
62.5°	7
65°	7
67.5°	6
70°	5
72.5°	4
75°	4
77.5°	3
80°	2
82.5°	2
85°	1
87.5°	1
90°	0

TEST NUMBER: P979770

CATALOG NUMBER: PRLX-241-935-31L-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.05	0.00	0.00	0.00	0.00	0.05
	12H	0.00	0.00	0.00	0.00	0.34	0.00	0.00	0.00	0.00	0.34
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.19	0.00	0.00	0.00	0.00	0.19

END OF REPORT