

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979781

Luminaire Tested: PRLX-241-935-LL5-C-U-S-WHTE-X

Issue Date: 4/3/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P979781  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/3/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-241-935-LL5-C-U-S-WHTE-X  
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE 241 SHADE WITH CLEAR LENS  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3826.8 lumens  
Efficiency: N/A  
Efficacy: 129.7 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.09  
Luminous Opening: Circular (Dia: 1.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 29.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P979781  
CATALOG NUMBER: PRLX-241-935-LL5-C-U-S-WHTE-X

### Luminous Intensity Polar Plot





TEST NUMBER: P979781

CATALOG NUMBER: PRLX-241-935-LL5-C-U-S-WHTE-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68
4	89	79	71	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61
5	83	72	64	59	81	71	64	59	69	63	58	67	62	57	65	61	57	55
6	78	66	59	53	76	65	58	53	64	57	52	62	56	52	61	56	52	50
7	73	61	54	48	71	60	53	48	59	53	48	58	52	48	56	51	47	45
8	69	57	49	44	67	56	49	44	55	48	44	54	48	44	53	47	43	42
9	65	53	46	41	63	52	45	41	51	45	40	50	44	40	49	44	40	38
10	61	49	42	38	60	49	42	37	48	42	37	47	41	37	46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	18284
5°	17854
10°	17212
15°	16991
20°	17048
25°	17129
30°	17180
35°	16588
40°	6405
45°	4502
50°	4409
55°	4664
60°	4906
65°	5055
70°	4884
75°	4617
80°	4324
85°	4007

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 65°  
 Luminance: 5055 cd/sqm

TEST NUMBER: P979781

CATALOG NUMBER: PRLX-241-935-LL5-C-U-S-WHTE-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	216.6	5.7
10°-20°	603.3	15.8
20°-30°	928.4	24.3
30°-40°	944.4	24.7
40°-50°	338.3	8.8
50°-60°	309.4	8.1
60°-70°	270.3	7.1
70°-80°	164.4	4.3
80°-90°	51.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1748.3	45.7
0°-40°	2692.7	70.4
0°-60°	3340.3	87.3
0°-90°	3826.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3826.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2372	
5°	2307	217
15°	2129	603
25°	2014	928
35°	1763	944
45°	413	338
55°	347	309
65°	277	270
75°	155	164
85°	45	52
90°	0	

TEST NUMBER: P979781

CATALOG NUMBER: PRLX-241-935-LL5-C-U-S-WHTE-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2371.7
2.5°	2363.4
5°	2307.2
7.5°	2244.1
10°	2198.8
12.5°	2164.5
15°	2128.9
17.5°	2105.6
20°	2078.1
22.5°	2050.7
25°	2013.7
27.5°	1972.5
30°	1930.0
32.5°	1876.5
35°	1762.6
37.5°	1193.4
40°	636.5
42.5°	463.6
45°	412.9
47.5°	381.3
50°	367.6
52.5°	358.0
55°	347.0
57.5°	333.3
60°	318.2
62.5°	300.4
65°	277.1
67.5°	246.9
70°	216.7
72.5°	185.2
75°	155.0
77.5°	126.2
80°	97.4
82.5°	71.3
85°	45.3
87.5°	24.7
90°	0.0



TEST NUMBER: P979781  
 CATALOG NUMBER: PRLX-241-935-LL5-C-U-S-WHTE-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.81	17.13	16.17	17.44	17.76	15.81	17.13	16.17	17.44	17.76
	3H	17.97	19.15	18.34	19.48	19.85	17.97	19.15	18.34	19.48	19.85
	4H	18.75	19.86	19.15	20.21	20.59	18.75	19.86	19.15	20.21	20.59
	6H	19.34	20.36	19.75	20.73	21.13	19.34	20.36	19.75	20.73	21.13
	8H	19.54	20.51	19.97	20.90	21.31	19.54	20.51	19.97	20.90	21.31
	12H	19.68	20.61	20.11	20.99	21.42	19.68	20.61	20.11	20.99	21.42
4H	2H	16.55	17.67	16.96	18.02	18.40	16.55	17.67	16.96	18.02	18.40
	3H	18.87	19.80	19.28	20.20	20.61	18.87	19.80	19.28	20.20	20.61
	4H	19.77	20.60	20.20	21.02	21.47	19.77	20.60	20.20	21.02	21.47
	6H	20.48	21.21	20.94	21.65	22.12	20.48	21.21	20.94	21.65	22.12
	8H	20.73	21.41	21.20	21.86	22.33	20.73	21.41	21.20	21.86	22.33
	12H	20.92	21.52	21.41	22.00	22.48	20.92	21.52	21.41	22.00	22.48
8H	4H	20.09	20.77	20.56	21.21	21.68	20.09	20.77	20.56	21.21	21.68
	6H	20.95	21.50	21.45	22.00	22.48	20.95	21.50	21.45	22.00	22.48
	8H	21.29	21.78	21.81	22.29	22.79	21.29	21.78	21.81	22.29	22.79
	12H	21.57	22.00	22.08	22.49	23.06	21.57	22.00	22.08	22.49	23.06
12H	4H	20.12	20.72	20.60	21.20	21.67	20.12	20.72	20.60	21.20	21.67
	6H	21.01	21.50	21.53	22.02	22.51	21.01	21.50	21.53	22.02	22.51
	8H	21.42	21.85	21.93	22.34	22.91	21.42	21.85	21.93	22.34	22.91