

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844300

Luminaire Tested: **LD6C30DE010B2750 EU6C30B30 6LBWLI**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P844300
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C30DE010B2750 EU6C30B30 6LBWLI
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2820.7 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844300

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B30 6LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P844300

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B30 6LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92				92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76				76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69				69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63				63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57				57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52				52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48				48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44				44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41				41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96599
5°	97496
10°	100226
15°	102730
20°	104292
25°	102139
30°	95755
35°	85615
40°	69344
45°	45865
50°	23180
55°	9787
60°	3158
65°	1232
70°	1042
75°	678
80°	0
85°	0



TEST NUMBER: P844300

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B30 6LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.0	6.0
10°-20°	511.0	18.1
20°-30°	770.2	27.3
30°-40°	788.4	27.9
40°-50°	459.3	16.3
50°-60°	105.5	3.7
60°-70°	12.9	0.5
70°-80°	3.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1451.2	51.4
0°-40°	2239.5	79.4
0°-60°	2804.4	99.4
0°-90°	2820.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2820.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1762	
5°	1772	170
15°	1810	511
25°	1689	770
35°	1279	788
45°	592	459
55°	102	106
65°	10	13
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P844300

CATALOG NUMBER: LD6C30DE010B2750 EU6C30B30 6LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1762.1
2.5°	1759.0
5°	1771.7
7.5°	1784.4
10°	1800.5
12.5°	1803.7
15°	1810.1
17.5°	1803.7
20°	1787.7
22.5°	1736.5
25°	1688.6
27.5°	1611.8
30°	1512.7
32.5°	1410.4
35°	1279.3
37.5°	1132.1
40°	969.0
42.5°	786.8
45°	591.6
47.5°	412.5
50°	271.8
52.5°	172.7
55°	102.4
57.5°	54.4
60°	28.8
62.5°	16.0
65°	9.5
67.5°	9.5
70°	6.5
72.5°	3.2
75°	3.2
77.5°	3.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)