

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843986

Luminaire Tested: **LD6C10DE010B40 EU6C10B40 6LBMH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843986
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C10DE010B40 EU6C10B40 6LBMH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 869.5 lumens
Efficiency: N/A
Efficacy: 65.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843986

CATALOG NUMBER: LD6C10DE010B40 EU6C10B40 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P843986

CATALOG NUMBER: LD6C10DE010B40 EU6C10B40 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	93	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	60	55	75	65	59	55	64	59	55		63	58	55		62
9	72	62	56	51	71	61	55	51	60	55	51		60	55	51		59
10	69	58	52	48	68	58	52	48	57	52	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47167
5°	46324
10°	43954
15°	41220
20°	38387
25°	35373
30°	29473
35°	20773
40°	13239
45°	7900
50°	4665
55°	2963
60°	2039
65°	1453
70°	994
75°	784
80°	410
85°	0



TEST NUMBER: P843986

CATALOG NUMBER: LD6C10DE010B40 EU6C10B40 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.7	9.0
10°-20°	203.5	23.4
20°-30°	263.7	30.3
30°-40°	195.8	22.5
40°-50°	82.7	9.5
50°-60°	29.3	3.4
60°-70°	11.3	1.3
70°-80°	3.9	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	545.9	62.8
0°-40°	741.7	85.3
0°-60°	853.7	98.2
0°-90°	869.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	869.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	860	
5°	842	79
15°	726	204
25°	585	264
35°	310	196
45°	102	83
55°	31	29
65°	11	11
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P843986

CATALOG NUMBER: LD6C10DE010B40 EU6C10B40 6LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	860.4
2.5°	857.8
5°	841.8
7.5°	818.2
10°	789.6
12.5°	758.5
15°	726.3
17.5°	690.3
20°	658.0
22.5°	624.5
25°	584.8
27.5°	530.1
30°	465.6
32.5°	389.8
35°	310.4
37.5°	243.4
40°	185.0
42.5°	137.8
45°	101.9
47.5°	74.5
50°	54.7
52.5°	40.9
55°	31.0
57.5°	23.6
60°	18.6
62.5°	13.6
65°	11.2
67.5°	8.7
70°	6.2
72.5°	5.0
75°	3.7
77.5°	2.5
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)