

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979812

Luminaire Tested: PRLX-241-935-LL8-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-935-LL8-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 241 SHADE WITH FROSTED LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3363.3 lumens
Efficiency: N/A
Efficacy: 54.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.07
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 61.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979812
CATALOG NUMBER: PRLX-241-935-LL8-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979812

CATALOG NUMBER: PRLX-241-935-LL8-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86
3	102	95	90	86	100	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68
6	86	77	70	66	84	76	70	65	74	69	65	73	68	65	71	67	64	63
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50
10	69	59	53	49	68	58	53	49	58	52	49	57	52	48	56	52	48	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22390
5°	22018
10°	21423
15°	20881
20°	20611
25°	20326
30°	19968
35°	17555
40°	7794
45°	978
50°	227
55°	254
60°	254
65°	259
70°	212
75°	211
80°	209
85°	212

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 978 cd/sqm

TEST NUMBER: P979812

CATALOG NUMBER: PRLX-241-935-LL8-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.9	8.0
10°-20°	739.2	22.0
20°-30°	1100.7	32.7
30°-40°	1062.3	31.6
40°-50°	154.5	4.6
50°-60°	16.1	0.5
60°-70°	13.2	0.4
70°-80°	7.4	0.2
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2107.9	62.7
0°-40°	3170.2	94.3
0°-60°	3340.8	99.3
0°-90°	3363.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3363.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2904	
5°	2845	268
15°	2616	739
25°	2390	1101
35°	1865	1062
45°	90	154
55°	19	16
65°	14	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P979812

CATALOG NUMBER: PRLX-241-935-LL8-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	2904.4
2.5°	2890.2
5°	2845.3
7.5°	2786.3
10°	2736.7
12.5°	2670.6
15°	2616.3
17.5°	2564.4
20°	2512.4
22.5°	2458.1
25°	2389.6
27.5°	2318.8
30°	2243.2
32.5°	2122.8
35°	1865.4
37.5°	1381.4
40°	774.5
42.5°	321.1
45°	89.7
47.5°	28.3
50°	18.9
52.5°	18.9
55°	18.9
57.5°	16.5
60°	16.5
62.5°	14.2
65°	14.2
67.5°	11.8
70°	9.4
72.5°	9.4
75°	7.1
77.5°	4.7
80°	4.7
82.5°	2.4
85°	2.4
87.5°	0.0
90°	0.0



TEST NUMBER: P979812
 CATALOG NUMBER: PRLX-241-935-LL8-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.35	0.00	0.00	0.00	0.00	0.35
	8H	0.00	0.00	0.00	0.05	0.46	0.00	0.00	0.00	0.05	0.46
	12H	0.00	0.00	0.00	0.11	0.54	0.00	0.00	0.00	0.11	0.54
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.02	0.00	0.00	0.00	0.00	0.02
	4H	0.00	0.00	0.00	0.38	0.83	0.00	0.00	0.00	0.38	0.83
	6H	0.00	0.39	0.38	0.84	1.32	0.00	0.39	0.38	0.84	1.32
	8H	0.05	0.49	0.52	0.94	1.42	0.05	0.49	0.52	0.94	1.42
	12H	0.19	0.58	0.69	1.07	1.55	0.19	0.58	0.69	1.07	1.55
8H	4H	0.00	0.03	0.06	0.48	0.96	0.00	0.03	0.06	0.48	0.96
	6H	0.26	0.61	0.77	1.11	1.60	0.26	0.61	0.77	1.11	1.60
	8H	0.45	0.77	0.99	1.29	1.79	0.45	0.77	0.99	1.29	1.79
	12H	0.71	0.98	1.23	1.48	2.06	0.71	0.98	1.23	1.48	2.06
12H	4H	0.00	0.00	0.07	0.46	0.93	0.00	0.00	0.07	0.46	0.93
	6H	0.28	0.59	0.81	1.12	1.61	0.28	0.59	0.81	1.12	1.61
	8H	0.53	0.80	1.05	1.30	1.88	0.53	0.80	1.05	1.30	1.88