

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979892

Luminaire Tested: PRLX-241-940-74L-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P979892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-940-74L-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 241 SHADE WITH FROSTED LENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3488.3 lumens
Efficiency: N/A
Efficacy: 56.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.07
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 61.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979892

CATALOG NUMBER: PRLX-241-940-74L-F-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P979892

CATALOG NUMBER: PRLX-241-940-74L-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		93
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		86
3	102	95	90	86	100	93	89	85	91	87	83		88	85	82		79
4	96	88	82	78	94	87	82	77	85	80	77		83	79	76		73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		68
6	86	77	70	66	84	76	70	65	74	69	65		73	68	65		63
7	81	71	65	61	80	71	65	61	69	64	60		68	63	60		58
8	77	67	61	56	76	66	60	56	65	60	56		64	59	56		54
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		50
10	69	59	53	49	68	58	53	49	58	52	49		57	52	48		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23222
5°	22837
10°	22219
15°	21657
20°	21378
25°	21081
30°	20711
35°	18208
40°	8084
45°	1015
50°	235
55°	263
60°	264
65°	268
70°	221
75°	217
80°	218
85°	212

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1015 cd/sqm

TEST NUMBER: P979892

CATALOG NUMBER: PRLX-241-940-74L-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.9	8.0
10°-20°	766.7	22.0
20°-30°	1141.7	32.7
30°-40°	1101.7	31.6
40°-50°	160.3	4.6
50°-60°	16.7	0.5
60°-70°	13.6	0.4
70°-80°	7.7	0.2
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2186.2	62.7
0°-40°	3288.0	94.3
0°-60°	3465.0	99.3
0°-90°	3488.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3488.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3012	
5°	2951	278
15°	2714	767
25°	2478	1142
35°	1935	1102
45°	93	160
55°	20	17
65°	15	14
75°	7	8
85°	2	2
90°	0	

TEST NUMBER: P979892

CATALOG NUMBER: PRLX-241-940-74L-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	3012.3
2.5°	2997.6
5°	2951.1
7.5°	2889.9
10°	2838.4
12.5°	2769.9
15°	2713.5
17.5°	2659.7
20°	2605.8
22.5°	2549.5
25°	2478.4
27.5°	2405.0
30°	2326.6
32.5°	2201.7
35°	1934.7
37.5°	1432.7
40°	803.3
42.5°	333.1
45°	93.1
47.5°	29.4
50°	19.6
52.5°	19.6
55°	19.6
57.5°	17.1
60°	17.1
62.5°	14.7
65°	14.7
67.5°	12.2
70°	9.8
72.5°	9.8
75°	7.3
77.5°	4.9
80°	4.9
82.5°	2.4
85°	2.4
87.5°	0.0
90°	0.0

TEST NUMBER: P979892

CATALOG NUMBER: PRLX-241-940-74L-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.11	0.00	0.00	0.00	0.00	0.11
	6H	0.00	0.00	0.00	0.08	0.48	0.00	0.00	0.00	0.08	0.48
	8H	0.00	0.00	0.00	0.17	0.58	0.00	0.00	0.00	0.17	0.58
	12H	0.00	0.00	0.00	0.22	0.65	0.00	0.00	0.00	0.22	0.65
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.15	0.00	0.00	0.00	0.00	0.15
	4H	0.00	0.07	0.00	0.50	0.95	0.00	0.07	0.00	0.50	0.95
	6H	0.04	0.52	0.51	0.97	1.44	0.04	0.52	0.51	0.97	1.44
	8H	0.17	0.61	0.64	1.06	1.54	0.17	0.61	0.64	1.06	1.54
	12H	0.30	0.68	0.79	1.17	1.65	0.30	0.68	0.79	1.17	1.65
8H	4H	0.00	0.15	0.18	0.60	1.08	0.00	0.15	0.18	0.60	1.08
	6H	0.39	0.74	0.90	1.24	1.73	0.39	0.74	0.90	1.24	1.73
	8H	0.57	0.88	1.10	1.41	1.90	0.57	0.88	1.10	1.41	1.90
	12H	0.81	1.07	1.33	1.57	2.15	0.81	1.07	1.33	1.57	2.15
12H	4H	0.00	0.09	0.20	0.58	1.05	0.00	0.09	0.20	0.58	1.05
	6H	0.41	0.72	0.94	1.24	1.74	0.41	0.72	0.94	1.24	1.74
	8H	0.64	0.91	1.16	1.41	1.99	0.64	0.91	1.16	1.41	1.99

END OF REPORT