

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979910

Luminaire Tested: PRLX-242-927-LL2-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979910
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-26)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-242-927-LL2-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 242 SHADE WITH CLEAR LENS
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1723.0 lumens
Efficiency: N/A
Efficacy: 156.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.39
Luminous Opening: Circular (Dia: 1.75' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979910
CATALOG NUMBER: PRLX-242-927-LL2-C-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979910

CATALOG NUMBER: PRLX-242-927-LL2-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76				76
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65				65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56				56
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49				49
6	73	61	52	46	71	60	52	46	58	51	46	56	50	45	55	49	45	43				43
7	68	55	47	41	66	54	46	41	53	46	40	51	45	40	50	44	40	38				38
8	63	50	42	36	62	49	42	36	48	41	36	47	41	36	46	40	36	34				34
9	59	46	38	33	58	45	38	33	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	35	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3077
5°	3079
10°	3075
15°	3037
20°	3019
25°	3006
30°	2991
35°	2991
40°	2996
45°	2991
50°	2985
55°	2936
60°	2750
65°	1282
70°	432
75°	133
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2991 cd/sqm



TEST NUMBER: P979910

CATALOG NUMBER: PRLX-242-927-LL2-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.2	3.8
10°-20°	185.4	10.8
20°-30°	280.5	16.3
30°-40°	342.8	19.9
40°-50°	364.7	21.2
50°-60°	334.7	19.4
60°-70°	137.3	8.0
70°-80°	12.4	0.7
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	531.0	30.8
0°-40°	873.8	50.7
0°-60°	1573.3	91.3
0°-90°	1723.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1723.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	688	
5°	686	65
15°	656	185
25°	609	280
35°	547	343
45°	473	365
55°	376	335
65°	121	137
75°	8	12
85°	0	0
90°	0	

TEST NUMBER: P979910

CATALOG NUMBER: PRLX-242-927-LL2-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	687.6
2.5°	687.1
5°	685.5
7.5°	682.4
10°	676.7
12.5°	669.0
15°	655.6
17.5°	644.8
20°	634.0
22.5°	621.6
25°	608.7
27.5°	593.8
30°	578.8
32.5°	563.9
35°	547.4
37.5°	530.9
40°	512.8
42.5°	493.3
45°	472.6
47.5°	451.5
50°	428.8
52.5°	403.6
55°	376.3
57.5°	348.9
60°	307.2
62.5°	221.6
65°	121.1
67.5°	48.4
70°	33.0
72.5°	22.7
75°	7.7
77.5°	0.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



TEST NUMBER: P979910
 CATALOG NUMBER: PRLX-242-927-LL2-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.69	18.23	17.06	18.55	18.86	16.69	18.23	17.06	18.55	18.86
	3H	16.68	18.04	17.06	18.37	18.73	16.68	18.04	17.06	18.37	18.73
	4H	16.63	17.90	17.03	18.25	18.63	16.63	17.90	17.03	18.25	18.63
	6H	16.57	17.74	16.98	18.10	18.49	16.57	17.74	16.98	18.10	18.49
	8H	16.53	17.64	16.96	18.03	18.43	16.53	17.64	16.96	18.03	18.43
	12H	16.50	17.56	16.93	17.94	18.37	16.50	17.56	16.93	17.94	18.37
4H	2H	16.75	18.02	17.15	18.37	18.75	16.75	18.02	17.15	18.37	18.75
	3H	16.76	17.80	17.17	18.20	18.60	16.76	17.80	17.17	18.20	18.60
	4H	16.70	17.62	17.14	18.04	18.48	16.70	17.62	17.14	18.04	18.48
	6H	16.64	17.44	17.10	17.88	18.34	16.64	17.44	17.10	17.88	18.34
	8H	16.60	17.34	17.06	17.78	18.25	16.60	17.34	17.06	17.78	18.25
	12H	16.56	17.22	17.05	17.70	18.17	16.56	17.22	17.05	17.70	18.17
8H	4H	16.60	17.34	17.07	17.79	18.26	16.60	17.34	17.07	17.79	18.26
	6H	16.52	17.13	17.02	17.62	18.10	16.52	17.13	17.02	17.62	18.10
	8H	16.46	17.01	16.98	17.52	18.01	16.46	17.01	16.98	17.52	18.01
	12H	16.43	16.91	16.94	17.41	17.97	16.43	16.91	16.94	17.41	17.97
12H	4H	16.57	17.23	17.05	17.71	18.18	16.57	17.23	17.05	17.71	18.18
	6H	16.46	17.01	16.98	17.52	18.01	16.46	17.01	16.98	17.52	18.01
	8H	16.43	16.91	16.94	17.41	17.97	16.43	16.91	16.94	17.41	17.97