

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600694

Luminaire Tested: PRLX-215-90-30K-LL7-UNV-STD-X-X-WHHR-BR-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600694
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-215-90-30K-LL7-UNV-STD-X-X-WHHR-BR-X
Description: Prenalux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4851.0 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.85
Luminous Opening: Circular (Dia: 1' x H: 0')
CIE Type: Direct


Input Watts (W): 55.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600694

CATALOG NUMBER: PRLX-215-90-30K-LL7-UNV-STD-X-X-WHHR-BR-X

Luminous Intensity Polar Plot





TEST NUMBER: P600694

CATALOG NUMBER: PRLX-215-90-30K-LL7-UNV-STD-X-X-WHHR-BR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95	93	92	90
2	104	98	93	89	102	96	92	87	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52		61	56	52		60	55	51	50
8	71	60	53	48	70	60	53	48	58	52	48		57	52	48		56	51	47	46
9	68	56	49	45	66	56	49	45	55	49	45		54	48	44		53	48	44	43
10	64	53	46	42	63	52	46	42	51	46	42		51	45	41		50	45	41	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64830
5°	52922
10°	48521
15°	47465
20°	47136
25°	46826
30°	37446
35°	18079
40°	15844
45°	14387
50°	12771
55°	11223
60°	9818
65°	8584
70°	7497
75°	6322
80°	4396
85°	1572

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14387 cd/sqm



TEST NUMBER: P600694

CATALOG NUMBER: PRLX-215-90-30K-LL7-UNV-STD-X-X-WHHR-BR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	360.1	7.4
10°-20°	945.8	19.5
20°-30°	1385.4	28.6
30°-40°	753.0	15.5
40°-50°	571.5	11.8
50°-60°	422.6	8.7
60°-70°	265.6	5.5
70°-80°	126.9	2.6
80°-90°	20.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2691.4	55.5
0°-40°	3444.4	71.0
0°-60°	4438.5	91.5
0°-90°	4851.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4851.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4730	
5°	3847	360
15°	3345	946
25°	3097	1385
35°	1081	753
45°	742	571
55°	470	423
65°	265	266
75°	119	127
85°	10	20
90°	0	



TEST NUMBER: P600694

CATALOG NUMBER: PRLX-215-90-30K-LL7-UNV-STD-X-X-WHHR-BR-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	4730.4
2.5°	4437.9
5°	3846.8
7.5°	3588.1
10°	3486.6
12.5°	3413.0
15°	3345.3
17.5°	3281.7
20°	3231.9
22.5°	3184.1
25°	3096.6
27.5°	2973.2
30°	2366.2
32.5°	1194.1
35°	1080.6
37.5°	977.1
40°	885.6
42.5°	812.0
45°	742.3
47.5°	670.7
50°	599.0
52.5°	533.3
55°	469.7
57.5°	411.9
60°	358.2
62.5°	310.5
65°	264.7
67.5°	226.9
70°	187.1
72.5°	153.2
75°	119.4
77.5°	87.6
80°	55.7
82.5°	31.8
85°	10.0
87.5°	4.0
90°	0.0

(END OF REPORT)