

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979943

Luminaire Tested: PRLX-242-927-LL5-F-U-S-WHTE-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979943
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-22)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-242-927-LL5-F-U-S-WHTE-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE 242 SHADE WITH FROSTED LENS
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4133.2 lumens
Efficiency: N/A
Efficacy: 140.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.34
Luminous Opening: Circular (Dia: 1.75' x H: 0')
CIE Type: Direct

Input Watts (W): 29.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979943
CATALOG NUMBER: PRLX-242-927-LL5-F-U-S-WHTE-X

Luminous Intensity Polar Plot



TEST NUMBER: P979943

CATALOG NUMBER: PRLX-242-927-LL5-F-U-S-WHTE-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	101	98	107	103	100	96	99	96	93	95	93	90	91	90	88	86
2	100	92	86	80	98	90	85	79	87	82	78	84	80	76	81	77	74	72
3	91	81	73	67	89	80	72	67	77	71	65	74	69	64	71	67	63	61
4	84	72	64	57	81	71	63	57	68	61	56	66	60	55	64	59	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	37	49	42	37	47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7012
5°	7004
10°	6972
15°	6887
20°	6805
25°	6728
30°	6601
35°	6520
40°	6424
45°	6325
50°	6217
55°	6078
60°	5907
65°	5689
70°	5375
75°	2230
80°	484
85°	770

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6325 cd/sqm

TEST NUMBER: P979943

CATALOG NUMBER: PRLX-242-927-LL5-F-U-S-WHTE-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.0	3.6
10°-20°	419.5	10.1
20°-30°	627.0	15.2
30°-40°	746.8	18.1
40°-50°	771.0	18.7
50°-60°	696.0	16.8
60°-70°	531.6	12.9
70°-80°	179.6	4.3
80°-90°	13.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1194.4	28.9
0°-40°	1941.2	47.0
0°-60°	3408.2	82.5
0°-90°	4133.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4133.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1567	
5°	1559	148
15°	1487	420
25°	1363	627
35°	1194	747
45°	999	771
55°	779	696
65°	537	532
75°	129	180
85°	15	14
90°	0	

TEST NUMBER: P979943

CATALOG NUMBER: PRLX-242-927-LL5-F-U-S-WHTE-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1566.8
2.5°	1565.5
5°	1559.2
7.5°	1546.7
10°	1534.2
12.5°	1514.2
15°	1486.6
17.5°	1459.1
20°	1429.0
22.5°	1398.9
25°	1362.6
27.5°	1321.3
30°	1277.5
32.5°	1238.6
35°	1193.5
37.5°	1148.5
40°	1099.6
42.5°	1050.8
45°	999.4
47.5°	946.8
50°	893.0
52.5°	836.6
55°	779.0
57.5°	720.1
60°	660.0
62.5°	599.9
65°	537.3
67.5°	475.9
70°	410.8
72.5°	314.4
75°	129.0
77.5°	27.6
80°	18.8
82.5°	17.5
85°	15.0
87.5°	8.8
90°	0.0



TEST NUMBER: P979943
 CATALOG NUMBER: PRLX-242-927-LL5-F-U-S-WHTE-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.62	20.23	18.99	20.54	20.85	18.62	20.23	18.99	20.54	20.85
	3H	20.45	21.89	20.83	22.22	22.58	20.45	21.89	20.83	22.22	22.58
	4H	20.68	22.03	21.08	22.38	22.76	20.68	22.03	21.08	22.38	22.76
	6H	20.63	21.88	21.04	22.25	22.64	20.63	21.88	21.04	22.25	22.64
	8H	20.60	21.79	21.03	22.18	22.58	20.60	21.79	21.03	22.18	22.58
	12H	20.58	21.72	21.01	22.10	22.53	20.58	21.72	21.01	22.10	22.53
4H	2H	19.27	20.63	19.67	20.97	21.35	19.27	20.63	19.67	20.97	21.35
	3H	21.28	22.40	21.69	22.80	23.20	21.28	22.40	21.69	22.80	23.20
	4H	21.50	22.50	21.93	22.92	23.36	21.50	22.50	21.93	22.92	23.36
	6H	21.46	22.33	21.91	22.77	23.23	21.46	22.33	21.91	22.77	23.23
	8H	21.42	22.24	21.89	22.68	23.15	21.42	22.24	21.89	22.68	23.15
	12H	21.41	22.14	21.89	22.61	23.08	21.41	22.14	21.89	22.61	23.08
8H	4H	21.55	22.36	22.01	22.81	23.27	21.55	22.36	22.01	22.81	23.27
	6H	21.50	22.16	21.99	22.65	23.13	21.50	22.16	21.99	22.65	23.13
	8H	21.46	22.06	21.98	22.57	23.06	21.46	22.06	21.98	22.57	23.06
	12H	21.45	21.98	21.96	22.47	23.03	21.45	21.98	21.96	22.47	23.03
12H	4H	21.52	22.25	22.01	22.73	23.20	21.52	22.25	22.01	22.73	23.20
	6H	21.45	22.05	21.97	22.56	23.05	21.45	22.05	21.97	22.56	23.05
	8H	21.44	21.97	21.95	22.46	23.02	21.44	21.97	21.95	22.46	23.02