

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980001

Luminaire Tested: PRLX-242-930-23L-C-U-S-WHTE-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P980001
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-242-930-23L-C-U-S-WHTE-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE 242 SHADE WITH CLEAR LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2480.5 lumens
Efficiency: N/A
Efficacy: 165.4 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.4
Luminous Opening: Circular (Dia: 1.75' x H: 0')
CIE Type: Direct

Input Watts (W): 15
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P980001

CATALOG NUMBER: PRLX-242-930-23L-C-U-S-WHTE-X

Luminous Intensity Polar Plot



TEST NUMBER: P980001

CATALOG NUMBER: PRLX-242-930-23L-C-U-S-WHTE-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	104	101	98		100	98	95		96	94	92		93	91	90
2	102	95	89	84		99	93	87	83		89	85	81		86	82	79		83	80	77
3	93	84	76	71		91	82	75	70		79	74	69		77	72	68		74	70	66
4	86	75	67	60		83	73	66	60		71	64	59		69	63	58		67	62	58
5	79	67	58	52		77	66	58	52		64	57	51		62	56	51		60	55	50
6	73	60	52	46		71	59	51	45		57	50	45		56	49	45		54	49	44
7	68	55	46	40		66	54	46	40		52	45	40		51	44	40		49	44	39
8	63	50	42	36		61	49	41	36		48	41	36		47	40	35		45	40	35
9	59	46	38	32		57	45	37	32		44	37	32		43	36	32		42	36	32
10	55	42	34	29		54	42	34	29		41	34	29		40	33	29		39	33	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4332
5°	4339
10°	4341
15°	4282
20°	4272
25°	4267
30°	4254
35°	4255
40°	4269
45°	4271
50°	4264
55°	4213
60°	3960
65°	2028
70°	816
75°	384
80°	75
85°	113

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4271 cd/sqm

TEST NUMBER: P980001

CATALOG NUMBER: PRLX-242-930-23L-C-U-S-WHTE-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.8	3.7
10°-20°	261.6	10.5
20°-30°	397.9	16.0
30°-40°	487.6	19.7
40°-50°	520.3	21.0
50°-60°	479.7	19.3
60°-70°	211.2	8.5
70°-80°	28.3	1.1
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	751.2	30.3
0°-40°	1238.8	49.9
0°-60°	2238.9	90.3
0°-90°	2480.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2480.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	968	
5°	966	92
15°	924	262
25°	864	398
35°	779	488
45°	675	520
55°	540	480
65°	192	211
75°	22	28
85°	2	2
90°	0	

TEST NUMBER: P980001

CATALOG NUMBER: PRLX-242-930-23L-C-U-S-WHTE-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	968.1
2.5°	966.6
5°	965.9
7.5°	959.5
10°	955.2
12.5°	940.8
15°	924.3
17.5°	911.4
20°	897.1
22.5°	880.6
25°	864.1
27.5°	842.6
30°	823.2
32.5°	801.0
35°	778.8
37.5°	755.1
40°	730.7
42.5°	702.8
45°	674.8
47.5°	644.7
50°	612.4
52.5°	576.5
55°	540.0
57.5°	501.2
60°	442.4
62.5°	329.1
65°	191.5
67.5°	88.9
70°	62.4
72.5°	46.6
75°	22.2
77.5°	6.5
80°	2.9
82.5°	2.9
85°	2.2
87.5°	1.4
90°	0.0

TEST NUMBER: P980001

CATALOG NUMBER: PRLX-242-930-23L-C-U-S-WHTE-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.93	19.48	18.30	19.79	20.11	17.93	19.48	18.30	19.79	20.11
	3H	17.98	19.35	18.36	19.68	20.04	17.98	19.35	18.36	19.68	20.04
	4H	17.94	19.23	18.34	19.58	19.96	17.94	19.23	18.34	19.58	19.96
	6H	17.88	19.07	18.30	19.43	19.82	17.88	19.07	18.30	19.43	19.82
	8H	17.85	18.97	18.28	19.36	19.76	17.85	18.97	18.28	19.36	19.76
	12H	17.82	18.89	18.25	19.27	19.70	17.82	18.89	18.25	19.27	19.70
4H	2H	18.03	19.31	18.43	19.66	20.04	18.03	19.31	18.43	19.66	20.04
	3H	18.12	19.16	18.53	19.56	19.97	18.12	19.16	18.53	19.56	19.97
	4H	18.08	19.01	18.51	19.43	19.87	18.08	19.01	18.51	19.43	19.87
	6H	18.02	18.83	18.48	19.27	19.73	18.02	18.83	18.48	19.27	19.73
	8H	17.98	18.73	18.44	19.18	19.64	17.98	18.73	18.44	19.18	19.64
	12H	17.95	18.62	18.43	19.09	19.57	17.95	18.62	18.43	19.09	19.57
8H	4H	17.99	18.74	18.46	19.19	19.66	17.99	18.74	18.46	19.19	19.66
	6H	17.91	18.53	18.41	19.02	19.50	17.91	18.53	18.41	19.02	19.50
	8H	17.86	18.42	18.38	18.93	19.42	17.86	18.42	18.38	18.93	19.42
	12H	17.83	18.32	18.34	18.81	19.38	17.83	18.32	18.34	18.81	19.38
12H	4H	17.96	18.63	18.44	19.11	19.58	17.96	18.63	18.44	19.11	19.58
	6H	17.86	18.41	18.37	18.92	19.41	17.86	18.41	18.37	18.92	19.41
	8H	17.82	18.32	18.34	18.81	19.38	17.82	18.32	18.34	18.81	19.38