

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600562

Luminaire Tested: PRLX-225-90-27K-LL3-UNV-STD-X-X-WHHR-BR-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PentaLux
Catalog Number: PRLX-225-90-27K-LL3-UNV-STD-X-X-WHHR-BR-X
Description: PentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2009.2 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct


Input Watts (W): 17.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600562

CATALOG NUMBER: PRLX-225-90-27K-LL3-UNV-STD-X-X-WHHR-BR-X

Luminous Intensity Polar Plot





TEST NUMBER: P600562

CATALOG NUMBER: PRLX-225-90-27K-LL3-UNV-STD-X-X-WHHR-BR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95		97	95	93		93	91	90	88
2	103	96	90	86	100	94	89	85	91	86	83		88	84	81		85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72		80	75	71		77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64		73	68	63		71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47		57	51	46		56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43		53	47	42		52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36		46	40	36		45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	10197
5°	9055
10°	8366
15°	8161
20°	8073
25°	8054
30°	7999
35°	7930
40°	7028
45°	2861
50°	2519
55°	2437
60°	2385
65°	2286
70°	2193
75°	2106
80°	2020
85°	1981

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2861 cd/sqm



TEST NUMBER: P600562

CATALOG NUMBER: PRLX-225-90-27K-LL3-UNV-STD-X-X-WHHR-BR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.0	5.4
10°-20°	289.1	14.4
20°-30°	436.3	21.7
30°-40°	520.2	25.9
40°-50°	269.0	13.4
50°-60°	162.3	8.1
60°-70°	124.4	6.2
70°-80°	74.6	3.7
80°-90°	24.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	834.3	41.5
0°-40°	1354.5	67.4
0°-60°	1785.8	88.9
0°-90°	2009.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2009.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1323	
5°	1170	109
15°	1022	289
25°	947	436
35°	843	520
45°	262	269
55°	181	162
65°	125	124
75°	71	75
85°	22	24
90°	0	



TEST NUMBER: P600562

CATALOG NUMBER: PRLX-225-90-27K-LL3-UNV-STD-X-X-WHHR-BR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1322.7
2.5°	1280.7
5°	1170.1
7.5°	1103.0
10°	1068.7
12.5°	1044.2
15°	1022.5
17.5°	1002.9
20°	984.0
22.5°	966.5
25°	946.9
27.5°	925.2
30°	898.6
32.5°	867.1
35°	842.6
37.5°	816.7
40°	698.4
42.5°	465.4
45°	262.4
47.5°	233.7
50°	210.0
52.5°	193.2
55°	181.3
57.5°	168.7
60°	154.7
62.5°	140.0
65°	125.3
67.5°	111.3
70°	97.3
72.5°	83.3
75°	70.7
77.5°	57.4
80°	45.5
82.5°	33.6
85°	22.4
87.5°	11.2
90°	0.0

(END OF REPORT)