

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600575

Luminaire Tested: PRLX-225-90-27K-LL7-UNV-STD-X-X-WHHR-FL-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PentaLux
Catalog Number: PRLX-225-90-27K-LL7-UNV-STD-X-X-WHHR-FL-X
Description: PentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5344.4 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 55.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600575
CATALOG NUMBER: PRLX-225-90-27K-LL7-UNV-STD-X-X-WHHR-FL-X

Luminous Intensity Polar Plot





TEST NUMBER: P600575

CATALOG NUMBER: PRLX-225-90-27K-LL7-UNV-STD-X-X-WHHR-FL-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95		97	95	93		93	91	90	88
2	103	96	90	86	100	94	89	85	91	86	83		88	84	81		85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72		80	75	71		77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64		73	68	63		71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47		57	51	46		56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43		53	47	42		52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36		46	40	36		45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27124
5°	24087
10°	22253
15°	21707
20°	21473
25°	21424
30°	21278
35°	21094
40°	18697
45°	7611
50°	6698
55°	6481
60°	6343
65°	6078
70°	5833
75°	5600
80°	5372
85°	5272

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7611 cd/sqm



TEST NUMBER: P600575

CATALOG NUMBER: PRLX-225-90-27K-LL7-UNV-STD-X-X-WHHR-FL-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.8	5.4
10°-20°	768.9	14.4
20°-30°	1160.4	21.7
30°-40°	1383.8	25.9
40°-50°	715.6	13.4
50°-60°	431.6	8.1
60°-70°	330.7	6.2
70°-80°	198.4	3.7
80°-90°	65.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2219.1	41.5
0°-40°	3603.0	67.4
0°-60°	4750.1	88.9
0°-90°	5344.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5344.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3518	
5°	3113	290
15°	2720	769
25°	2519	1160
35°	2241	1384
45°	698	716
55°	482	432
65°	333	331
75°	188	198
85°	60	65
90°	0	



TEST NUMBER: P600575

CATALOG NUMBER: PRLX-225-90-27K-LL7-UNV-STD-X-X-WHHR-FL-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	3518.4
2.5°	3406.7
5°	3112.6
7.5°	2933.9
10°	2842.7
12.5°	2777.5
15°	2719.8
17.5°	2667.7
20°	2617.4
22.5°	2570.9
25°	2518.7
27.5°	2461.0
30°	2390.3
32.5°	2306.5
35°	2241.4
37.5°	2172.5
40°	1857.9
42.5°	1238.0
45°	698.1
47.5°	621.8
50°	558.5
52.5°	513.8
55°	482.2
57.5°	448.6
60°	411.4
62.5°	372.3
65°	333.2
67.5°	296.0
70°	258.8
72.5°	221.5
75°	188.0
77.5°	152.7
80°	121.0
82.5°	89.4
85°	59.6
87.5°	29.8
90°	0.0

(END OF REPORT)