

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600627

Luminaire Tested: PRLX-225-90-35K-LL8-UNV-STD-X-X-WHHR-SR-X

Issue Date: 7/6/2022

**Test Information**

Test Method: LM-79-2019  
Report Number: P600627  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/6/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PentaLux  
Catalog Number: PRLX-225-90-35K-LL8-UNV-STD-X-X-WHHR-SR-X  
Description: PentaLux 200 SERIES 3D PRINTED LUMINAIRE  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6807.4 lumens  
Efficiency: N/A  
Efficacy: 94.3 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17  
Luminous Opening: Circular (Dia: 1.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P600627

CATALOG NUMBER: PRLX-225-90-35K-LL8-UNV-STD-X-X-WHHR-SR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P600627

CATALOG NUMBER: PRLX-225-90-35K-LL8-UNV-STD-X-X-WHHR-SR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	88				88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77				77
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68				68
4	89	79	71	65	87	77	70	65	75	69	64	73	68	63	71	66	63	61				61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54				54
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49				49
7	72	60	53	47	71	60	52	47	58	52	47	57	51	46	56	50	46	44				44
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	52	46	42	41				41
9	64	52	44	39	62	51	44	39	50	44	39	49	43	39	48	43	39	37				37
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34				34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	34549
5°	30681
10°	28345
15°	27650
20°	27352
25°	27290
30°	27103
35°	26869
40°	23815
45°	9694
50°	8532
55°	8255
60°	8079
65°	7743
70°	7429
75°	7134
80°	6841
85°	6714

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9694 cd/sqm



TEST NUMBER: P600627

CATALOG NUMBER: PRLX-225-90-35K-LL8-UNV-STD-X-X-WHHR-SR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	369.2	5.4
10°-20°	979.4	14.4
20°-30°	1478.1	21.7
30°-40°	1762.7	25.9
40°-50°	911.5	13.4
50°-60°	549.7	8.1
60°-70°	421.3	6.2
70°-80°	252.7	3.7
80°-90°	82.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2826.7	41.5
0°-40°	4589.3	67.4
0°-60°	6050.6	88.9
0°-90°	6807.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6807.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4482	
5°	3965	369
15°	3464	979
25°	3208	1478
35°	2855	1763
45°	889	912
55°	614	550
65°	424	421
75°	240	253
85°	76	83
90°	0	



TEST NUMBER: P600627

CATALOG NUMBER: PRLX-225-90-35K-LL8-UNV-STD-X-X-WHHR-SR-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4481.6
2.5°	4339.4
5°	3964.7
7.5°	3737.1
10°	3620.9
12.5°	3537.9
15°	3464.4
17.5°	3398.0
20°	3334.0
22.5°	3274.7
25°	3208.3
27.5°	3134.8
30°	3044.7
32.5°	2938.0
35°	2855.0
37.5°	2767.2
40°	2366.5
42.5°	1576.9
45°	889.2
47.5°	792.0
50°	711.4
52.5°	654.5
55°	614.2
57.5°	571.5
60°	524.0
62.5°	474.2
65°	424.5
67.5°	377.0
70°	329.6
72.5°	282.2
75°	239.5
77.5°	194.4
80°	154.1
82.5°	113.8
85°	75.9
87.5°	37.9
90°	0.0

(END OF REPORT)