

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980160

Luminaire Tested: PRLX-242-940-23L-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P980160
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-26)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-242-940-23L-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 242 SHADE WITH CLEAR LENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2568.6 lumens
Efficiency: N/A
Efficacy: 171.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.39
Luminous Opening: Circular (Dia: 1.75' x H: 0')
CIE Type: Direct

Input Watts (W): 15
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P980160

CATALOG NUMBER: PRLX-242-940-23L-C-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P980160

CATALOG NUMBER: PRLX-242-940-23L-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	103	100	108	105	102	99	101	98	96		97	95	93		93
2	102	95	89	84	100	93	88	83	90	85	81		86	83	79		84
3	94	84	77	71	91	83	76	71	80	74	69		77	72	68		75
4	86	75	67	61	84	74	66	61	71	65	60		69	63	59		67
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	73	61	52	46	71	60	52	46	58	51	46		56	50	45		55
7	68	55	47	41	66	54	46	41	53	46	40		51	45	40		50
8	63	50	42	36	62	49	42	36	48	41	36		47	41	36		46
9	59	46	38	33	58	45	38	33	44	37	32		43	37	32		42
10	55	42	35	30	54	42	35	30	41	34	29		40	34	29		39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4587
5°	4591
10°	4585
15°	4528
20°	4501
25°	4481
30°	4459
35°	4458
40°	4466
45°	4459
50°	4451
55°	4376
60°	4099
65°	1912
70°	644
75°	199
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4459 cd/sqm

TEST NUMBER: P980160

CATALOG NUMBER: PRLX-242-940-23L-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.2	3.8
10°-20°	276.3	10.8
20°-30°	418.2	16.3
30°-40°	511.0	19.9
40°-50°	543.7	21.2
50°-60°	499.0	19.4
60°-70°	204.8	8.0
70°-80°	18.5	0.7
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	791.7	30.8
0°-40°	1302.7	50.7
0°-60°	2345.4	91.3
0°-90°	2568.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2568.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1025	
5°	1022	97
15°	977	276
25°	908	418
35°	816	511
45°	705	544
55°	561	499
65°	181	205
75°	12	18
85°	0	0
90°	0	

TEST NUMBER: P980160

CATALOG NUMBER: PRLX-242-940-23L-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1025.0
2.5°	1024.3
5°	1022.0
7.5°	1017.3
10°	1008.9
12.5°	997.4
15°	977.4
17.5°	961.3
20°	945.1
22.5°	926.7
25°	907.5
27.5°	885.2
30°	862.9
32.5°	840.6
35°	816.0
37.5°	791.4
40°	764.5
42.5°	735.3
45°	704.6
47.5°	673.1
50°	639.3
52.5°	601.6
55°	560.9
57.5°	520.2
60°	458.0
62.5°	330.4
65°	180.6
67.5°	72.2
70°	49.2
72.5°	33.8
75°	11.5
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

TEST NUMBER: P980160

CATALOG NUMBER: PRLX-242-940-23L-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.08	19.62	18.45	19.93	20.25	18.08	19.62	18.45	19.93	20.25
	3H	18.07	19.43	18.45	19.76	20.12	18.07	19.43	18.45	19.76	20.12
	4H	18.02	19.29	18.42	19.64	20.02	18.02	19.29	18.42	19.64	20.02
	6H	17.95	19.12	18.37	19.49	19.88	17.95	19.12	18.37	19.49	19.88
	8H	17.92	19.03	18.35	19.42	19.82	17.92	19.03	18.35	19.42	19.82
	12H	17.89	18.95	18.32	19.33	19.76	17.89	18.95	18.32	19.33	19.76
4H	2H	18.14	19.41	18.54	19.76	20.14	18.14	19.41	18.54	19.76	20.14
	3H	18.15	19.18	18.56	19.59	19.99	18.15	19.18	18.56	19.59	19.99
	4H	18.09	19.01	18.52	19.43	19.87	18.09	19.01	18.52	19.43	19.87
	6H	18.03	18.83	18.49	19.27	19.73	18.03	18.83	18.49	19.27	19.73
	8H	17.99	18.73	18.45	19.17	19.64	17.99	18.73	18.45	19.17	19.64
	12H	17.95	18.61	18.43	19.09	19.56	17.95	18.61	18.43	19.09	19.56
8H	4H	17.99	18.73	18.46	19.18	19.65	17.99	18.73	18.46	19.18	19.65
	6H	17.91	18.52	18.41	19.01	19.49	17.91	18.52	18.41	19.01	19.49
	8H	17.85	18.40	18.37	18.91	19.40	17.85	18.40	18.37	18.91	19.40
	12H	17.82	18.30	18.33	18.79	19.36	17.82	18.30	18.33	18.79	19.36
12H	4H	17.96	18.62	18.44	19.10	19.57	17.96	18.62	18.44	19.10	19.57
	6H	17.85	18.40	18.37	18.91	19.40	17.85	18.40	18.37	18.91	19.40
	8H	17.82	18.30	18.33	18.79	19.36	17.82	18.30	18.33	18.79	19.36