

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979280

Luminaire Tested: PRLX-240-927-LL3-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979280
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-240-927-LL3-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 240 SHADE WITH CLEAR LENS
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1696.6 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.39
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 15
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979280
CATALOG NUMBER: PRLX-240-927-LL3-C-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979280

CATALOG NUMBER: PRLX-240-927-LL3-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	99	99	97	96	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	44	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39
10	61	49	42	38	60	49	42	38	48	42	37	47	41	37	46	41	37	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9147
5°	9134
10°	9095
15°	8934
20°	8871
25°	8860
30°	8808
35°	8838
40°	8864
45°	8794
50°	6018
55°	937
60°	232
65°	48
70°	59
75°	78
80°	116
85°	81

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8794 cd/sqm

TEST NUMBER: P979280

CATALOG NUMBER: PRLX-240-927-LL3-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	5.1
10°-20°	242.3	14.3
20°-30°	367.0	21.6
30°-40°	449.9	26.5
40°-50°	445.4	26.3
50°-60°	99.3	5.9
60°-70°	3.6	0.2
70°-80°	2.1	0.1
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	695.1	41.0
0°-40°	1145.0	67.5
0°-60°	1689.8	99.6
0°-90°	1696.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1696.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	908	
5°	904	86
15°	857	242
25°	798	367
35°	719	450
45°	618	445
55°	53	99
65°	2	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P979280

CATALOG NUMBER: PRLX-240-927-LL3-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	908.4
2.5°	909.1
5°	903.7
7.5°	896.9
10°	889.5
12.5°	872.6
15°	857.0
17.5°	843.5
20°	827.9
22.5°	813.1
25°	797.5
27.5°	776.5
30°	757.6
32.5°	738.0
35°	719.0
37.5°	698.1
40°	674.4
42.5°	650.0
45°	617.6
47.5°	518.8
50°	384.2
52.5°	179.3
55°	53.4
57.5°	25.7
60°	11.5
62.5°	4.1
65°	2.0
67.5°	2.0
70°	2.0
72.5°	2.0
75°	2.0
77.5°	2.0
80°	2.0
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0



TEST NUMBER: P979280
 CATALOG NUMBER: PRLX-240-927-LL3-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.51	2.81	1.87	3.12	3.44	1.51	2.81	1.87	3.12	3.44
	3H	1.42	2.55	1.80	2.89	3.25	1.42	2.55	1.80	2.89	3.25
	4H	1.39	2.45	1.80	2.80	3.18	1.39	2.45	1.80	2.80	3.18
	6H	1.41	2.37	1.83	2.75	3.14	1.41	2.37	1.83	2.75	3.14
	8H	1.42	2.33	1.85	2.72	3.13	1.42	2.33	1.85	2.72	3.13
	12H	1.41	2.28	1.84	2.66	3.09	1.41	2.28	1.84	2.66	3.09
4H	2H	1.31	2.36	1.72	2.72	3.10	1.31	2.36	1.72	2.72	3.10
	3H	1.24	2.09	1.66	2.49	2.90	1.24	2.09	1.66	2.49	2.90
	4H	1.24	1.99	1.67	2.41	2.85	1.24	1.99	1.67	2.41	2.85
	6H	1.33	1.97	1.79	2.42	2.88	1.33	1.97	1.79	2.42	2.88
	8H	1.36	1.96	1.83	2.41	2.88	1.36	1.96	1.83	2.41	2.88
	12H	1.36	1.89	1.85	2.38	2.85	1.36	1.89	1.85	2.38	2.85
8H	4H	1.15	1.75	1.62	2.20	2.67	1.15	1.75	1.62	2.20	2.67
	6H	1.28	1.78	1.79	2.28	2.76	1.28	1.78	1.79	2.28	2.76
	8H	1.35	1.80	1.87	2.32	2.81	1.35	1.80	1.87	2.32	2.81
	12H	1.39	1.79	1.90	2.29	2.86	1.39	1.79	1.90	2.29	2.86
12H	4H	1.11	1.64	1.60	2.13	2.60	1.11	1.64	1.60	2.13	2.60
	6H	1.25	1.70	1.78	2.22	2.71	1.25	1.70	1.78	2.22	2.71
	8H	1.35	1.76	1.87	2.25	2.82	1.35	1.76	1.87	2.25	2.82