

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979342

Luminaire Tested: PRLX-240-930-12L-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P979342
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-240-930-12L-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 240 SHADE WITH FROSTED LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 852.8 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.33
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979342

CATALOG NUMBER: PRLX-240-930-12L-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979342

CATALOG NUMBER: PRLX-240-930-12L-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	106	104	101	102	100	98	99	97	95	95	94	92	90		
2	105	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	81		
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72		
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64		
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57		
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51		
7	73	61	54	48	71	61	53	48	59	53	48	58	52	48	57	51	47	46		
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	51	44	40	50	44	39	49	43	39	48	43	39	37		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4487
5°	4474
10°	4441
15°	4372
20°	4318
25°	4257
30°	4181
35°	4126
40°	4063
45°	3950
50°	3366
55°	1719
60°	278
65°	36
70°	32
75°	43
80°	41
85°	46

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3950 cd/sqm

TEST NUMBER: P979342

CATALOG NUMBER: PRLX-240-930-12L-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.0	4.9
10°-20°	118.4	13.9
20°-30°	176.4	20.7
30°-40°	209.9	24.6
40°-50°	209.5	24.6
50°-60°	91.9	10.8
60°-70°	3.2	0.4
70°-80°	1.1	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	336.7	39.5
0°-40°	546.6	64.1
0°-60°	848.0	99.4
0°-90°	852.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	446	
5°	443	42
15°	419	118
25°	383	176
35°	336	210
45°	277	210
55°	98	92
65°	2	3
75°	1	1
85°	0	1
90°	0	

TEST NUMBER: P979342

CATALOG NUMBER: PRLX-240-930-12L-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	445.6
2.5°	445.2
5°	442.6
7.5°	438.8
10°	434.4
12.5°	428.0
15°	419.4
17.5°	410.8
20°	403.0
22.5°	393.6
25°	383.2
27.5°	371.2
30°	359.6
32.5°	347.6
35°	335.7
37.5°	322.6
40°	309.1
42.5°	294.9
45°	277.4
47.5°	252.7
50°	214.9
52.5°	161.5
55°	97.9
57.5°	44.1
60°	13.8
62.5°	3.0
65°	1.5
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	0.7
82.5°	0.7
85°	0.4
87.5°	0.4
90°	0.0

TEST NUMBER: P979342

CATALOG NUMBER: PRLX-240-930-12L-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.52	8.86	7.88	9.18	9.49	7.52	8.86	7.88	9.18	9.49
	3H	7.39	8.57	7.77	8.90	9.27	7.39	8.57	7.77	8.90	9.27
	4H	7.33	8.42	7.73	8.77	9.16	7.33	8.42	7.73	8.77	9.16
	6H	7.26	8.26	7.67	8.63	9.02	7.26	8.26	7.67	8.63	9.02
	8H	7.22	8.17	7.65	8.56	8.96	7.22	8.17	7.65	8.56	8.96
	12H	7.18	8.08	7.61	8.47	8.90	7.18	8.08	7.61	8.47	8.90
4H	2H	7.32	8.41	7.72	8.76	9.15	7.32	8.41	7.72	8.76	9.15
	3H	7.20	8.08	7.61	8.48	8.88	7.20	8.08	7.61	8.48	8.88
	4H	7.12	7.90	7.56	8.32	8.76	7.12	7.90	7.56	8.32	8.76
	6H	7.05	7.72	7.52	8.17	8.63	7.05	7.72	7.52	8.17	8.63
	8H	7.00	7.62	7.47	8.07	8.54	7.00	7.62	7.47	8.07	8.54
	12H	6.95	7.51	7.44	7.99	8.47	6.95	7.51	7.44	7.99	8.47
8H	4H	6.98	7.61	7.45	8.06	8.53	6.98	7.61	7.45	8.06	8.53
	6H	6.89	7.41	7.39	7.90	8.38	6.89	7.41	7.39	7.90	8.38
	8H	6.83	7.30	7.35	7.82	8.31	6.83	7.30	7.35	7.82	8.31
	12H	6.79	7.21	7.30	7.70	8.28	6.79	7.21	7.30	7.70	8.28
12H	4H	6.93	7.49	7.42	7.97	8.45	6.93	7.49	7.42	7.97	8.45
	6H	6.82	7.29	7.34	7.81	8.30	6.82	7.29	7.34	7.81	8.30
	8H	6.78	7.20	7.30	7.70	8.27	6.78	7.20	7.30	7.70	8.27

END OF REPORT