

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979360

Luminaire Tested: PRLX-240-930-23L-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P979360
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-240-930-23L-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 240 SHADE WITH CLEAR LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1798.6 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.39
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 15
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979360

CATALOG NUMBER: PRLX-240-930-23L-C-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P979360

CATALOG NUMBER: PRLX-240-930-23L-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	99		99	97	96		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68
6	79	68	61	56	78	67	60	55	66	60	55		64	59	55		63
7	74	63	55	50	73	62	55	50	61	54	50		59	54	49		58
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		54
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50
10	61	49	42	38	60	49	42	38	48	42	37		47	41	37		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9697
5°	9683
10°	9642
15°	9471
20°	9405
25°	9393
30°	9337
35°	9370
40°	9397
45°	9323
50°	6380
55°	995
60°	246
65°	52
70°	65
75°	86
80°	128
85°	81

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9323 cd/sqm

TEST NUMBER: P979360

CATALOG NUMBER: PRLX-240-930-23L-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.0	5.1
10°-20°	256.9	14.3
20°-30°	389.1	21.6
30°-40°	476.9	26.5
40°-50°	472.2	26.3
50°-60°	105.3	5.9
60°-70°	3.9	0.2
70°-80°	2.3	0.1
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	736.9	41.0
0°-40°	1213.9	67.5
0°-60°	1791.3	99.6
0°-90°	1798.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1798.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	963	
5°	958	91
15°	909	257
25°	846	389
35°	762	477
45°	655	472
55°	57	105
65°	2	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P979360

CATALOG NUMBER: PRLX-240-930-23L-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	963.1
2.5°	963.8
5°	958.0
7.5°	950.9
10°	943.0
12.5°	925.1
15°	908.6
17.5°	894.2
20°	877.7
22.5°	861.9
25°	845.5
27.5°	823.2
30°	803.1
32.5°	782.3
35°	762.3
37.5°	740.0
40°	714.9
42.5°	689.1
45°	654.7
47.5°	550.0
50°	407.3
52.5°	190.0
55°	56.7
57.5°	27.2
60°	12.2
62.5°	4.3
65°	2.2
67.5°	2.2
70°	2.2
72.5°	2.2
75°	2.2
77.5°	2.2
80°	2.2
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

TEST NUMBER: P979360

CATALOG NUMBER: PRLX-240-930-23L-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.70	3.00	2.07	3.31	3.63	1.70	3.00	2.07	3.31	3.63
	3H	1.61	2.75	1.99	3.08	3.45	1.61	2.75	1.99	3.08	3.45
	4H	1.59	2.65	2.00	3.00	3.38	1.59	2.65	2.00	3.00	3.38
	6H	1.62	2.58	2.03	2.95	3.35	1.62	2.58	2.03	2.95	3.35
	8H	1.62	2.53	2.06	2.93	3.33	1.62	2.53	2.06	2.93	3.33
	12H	1.61	2.48	2.04	2.86	3.29	1.61	2.48	2.04	2.86	3.29
4H	2H	1.51	2.56	1.91	2.91	3.29	1.51	2.56	1.91	2.91	3.29
	3H	1.44	2.29	1.86	2.69	3.09	1.44	2.29	1.86	2.69	3.09
	4H	1.44	2.19	1.88	2.61	3.06	1.44	2.19	1.88	2.61	3.06
	6H	1.54	2.19	2.01	2.63	3.10	1.54	2.19	2.01	2.63	3.10
	8H	1.57	2.17	2.04	2.62	3.09	1.57	2.17	2.04	2.62	3.09
	12H	1.57	2.10	2.06	2.58	3.06	1.57	2.10	2.06	2.58	3.06
8H	4H	1.36	1.96	1.83	2.40	2.88	1.36	1.96	1.83	2.40	2.88
	6H	1.51	2.00	2.01	2.50	2.98	1.51	2.00	2.01	2.50	2.98
	8H	1.57	2.02	2.09	2.53	3.03	1.57	2.02	2.09	2.53	3.03
	12H	1.59	2.00	2.11	2.49	3.06	1.59	2.00	2.11	2.49	3.06
12H	4H	1.32	1.85	1.81	2.34	2.81	1.32	1.85	1.81	2.34	2.81
	6H	1.48	1.93	2.00	2.44	2.94	1.48	1.93	2.00	2.44	2.94
	8H	1.57	1.97	2.08	2.47	3.04	1.57	1.97	2.08	2.47	3.04

END OF REPORT