

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980362

Luminaire Tested: PRLX-243-930-62L-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P980362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-37)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-243-930-62L-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 243 SHADE WITH FROSTED LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4247.7 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.31
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P980362

CATALOG NUMBER: PRLX-243-930-62L-F-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P980362

CATALOG NUMBER: PRLX-243-930-62L-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74
5	85	74	67	62	83	73	67	62	71	66	61		70	64	60		68
6	79	68	61	55	77	67	60	55	66	59	55		64	58	54		63
7	74	62	55	50	72	62	55	50	60	54	49		59	53	49		58
8	69	57	50	45	68	57	50	45	56	49	45		54	49	44		53
9	65	53	46	41	64	52	46	41	51	45	41		50	45	40		49
10	61	49	42	37	60	49	42	37	48	41	37		47	41	37		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	11684
5°	11585
10°	11372
15°	11102
20°	10916
25°	10741
30°	10538
35°	10399
40°	10239
45°	10070
50°	8282
55°	1956
60°	114
65°	112
70°	138
75°	147
80°	111
85°	108

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10070 cd/sqm

TEST NUMBER: P980362

CATALOG NUMBER: PRLX-243-930-62L-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.0	5.2
10°-20°	613.8	14.5
20°-30°	908.7	21.4
30°-40°	1080.1	25.4
40°-50°	1084.7	25.5
50°-60°	319.6	7.5
60°-70°	9.8	0.2
70°-80°	7.4	0.2
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1743.5	41.0
0°-40°	2823.6	66.5
0°-60°	4227.9	99.5
0°-90°	4247.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4247.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2368	
5°	2339	221
15°	2174	614
25°	1973	909
35°	1726	1080
45°	1443	1085
55°	227	320
65°	10	10
75°	8	7
85°	2	3
90°	0	

TEST NUMBER: P980362

CATALOG NUMBER: PRLX-243-930-62L-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	2368.1
2.5°	2362.3
5°	2339.2
7.5°	2306.5
10°	2269.8
12.5°	2225.5
15°	2173.5
17.5°	2127.3
20°	2079.1
22.5°	2030.9
25°	1973.1
27.5°	1911.4
30°	1849.8
32.5°	1788.1
35°	1726.5
37.5°	1662.9
40°	1589.7
42.5°	1520.3
45°	1443.2
47.5°	1329.5
50°	1079.0
52.5°	651.3
55°	227.4
57.5°	44.3
60°	11.6
62.5°	9.6
65°	9.6
67.5°	9.6
70°	9.6
72.5°	7.7
75°	7.7
77.5°	5.8
80°	3.9
82.5°	3.9
85°	1.9
87.5°	1.9
90°	0.0

TEST NUMBER: P980362

CATALOG NUMBER: PRLX-243-930-62L-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.82	0.00	1.13	1.45	0.00	0.82	0.00	1.13	1.45
	3H	0.00	0.86	0.09	1.19	1.55	0.00	0.86	0.09	1.19	1.55
	4H	0.00	0.93	0.27	1.28	1.67	0.00	0.93	0.27	1.28	1.67
	6H	0.00	0.95	0.39	1.32	1.71	0.00	0.95	0.39	1.32	1.71
	8H	0.03	0.95	0.46	1.34	1.74	0.03	0.95	0.46	1.34	1.74
	12H	0.05	0.93	0.48	1.31	1.74	0.05	0.93	0.48	1.31	1.74
4H	2H	0.00	0.45	0.00	0.80	1.18	0.00	0.45	0.00	0.80	1.18
	3H	0.00	0.58	0.15	0.99	1.39	0.00	0.58	0.15	0.99	1.39
	4H	0.00	0.76	0.44	1.18	1.63	0.00	0.76	0.44	1.18	1.63
	6H	0.20	0.85	0.67	1.30	1.77	0.20	0.85	0.67	1.30	1.77
	8H	0.30	0.91	0.77	1.36	1.83	0.30	0.91	0.77	1.36	1.83
	12H	0.36	0.90	0.85	1.38	1.86	0.36	0.90	0.85	1.38	1.86
8H	4H	0.03	0.64	0.50	1.09	1.56	0.03	0.64	0.50	1.09	1.56
	6H	0.29	0.79	0.79	1.29	1.77	0.29	0.79	0.79	1.29	1.77
	8H	0.45	0.91	0.98	1.42	1.92	0.45	0.91	0.98	1.42	1.92
	12H	0.57	0.98	1.08	1.47	2.05	0.57	0.98	1.08	1.47	2.05
12H	4H	0.01	0.54	0.49	1.03	1.50	0.01	0.54	0.49	1.03	1.50
	6H	0.28	0.73	0.80	1.25	1.74	0.28	0.73	0.80	1.25	1.74
	8H	0.49	0.90	1.00	1.39	1.97	0.49	0.90	1.00	1.39	1.97

END OF REPORT