

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979370

Luminaire Tested: PRLX-240-930-31L-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P979370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-240-930-31L-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 240 SHADE WITH CLEAR LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2427.8 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.39
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979370

CATALOG NUMBER: PRLX-240-930-31L-C-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P979370

CATALOG NUMBER: PRLX-240-930-31L-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	99		99	97	96		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68
6	79	68	61	56	78	67	60	55	66	60	55		64	59	55		63
7	74	63	55	50	73	62	55	50	61	54	50		59	54	49		58
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		54
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50
10	61	49	42	38	60	49	42	38	48	42	37		47	41	37		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	13089
5°	13071
10°	13014
15°	12784
20°	12694
25°	12679
30°	12604
35°	12647
40°	12684
45°	12584
50°	8612
55°	1343
60°	332
65°	69
70°	85
75°	113
80°	168
85°	116

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12584 cd/sqm

TEST NUMBER: P979370

CATALOG NUMBER: PRLX-240-930-31L-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.8	5.1
10°-20°	346.8	14.3
20°-30°	525.2	21.6
30°-40°	643.8	26.5
40°-50°	637.4	26.3
50°-60°	142.2	5.9
60°-70°	5.2	0.2
70°-80°	3.1	0.1
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	994.7	41.0
0°-40°	1638.5	67.5
0°-60°	2418.0	99.6
0°-90°	2427.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2427.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1300	
5°	1293	123
15°	1226	347
25°	1141	525
35°	1029	644
45°	884	637
55°	76	142
65°	3	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P979370

CATALOG NUMBER: PRLX-240-930-31L-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1299.9
2.5°	1300.9
5°	1293.2
7.5°	1283.5
10°	1272.8
12.5°	1248.6
15°	1226.4
17.5°	1207.0
20°	1184.7
22.5°	1163.5
25°	1141.2
27.5°	1111.2
30°	1084.1
32.5°	1056.0
35°	1028.9
37.5°	998.9
40°	965.0
42.5°	930.2
45°	883.7
47.5°	742.4
50°	549.8
52.5°	256.5
55°	76.5
57.5°	36.8
60°	16.5
62.5°	5.8
65°	2.9
67.5°	2.9
70°	2.9
72.5°	2.9
75°	2.9
77.5°	2.9
80°	2.9
82.5°	1.9
85°	1.0
87.5°	1.0
90°	0.0

TEST NUMBER: P979370

CATALOG NUMBER: PRLX-240-930-31L-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.76	4.06	3.12	4.37	4.69	2.76	4.06	3.12	4.37	4.69
	3H	2.67	3.81	3.05	4.14	4.50	2.67	3.81	3.05	4.14	4.50
	4H	2.65	3.70	3.05	4.05	4.43	2.65	3.70	3.05	4.05	4.43
	6H	2.67	3.63	3.08	4.00	4.39	2.67	3.63	3.08	4.00	4.39
	8H	2.67	3.58	3.10	3.97	4.38	2.67	3.58	3.10	3.97	4.38
	12H	2.66	3.53	3.09	3.91	4.34	2.66	3.53	3.09	3.91	4.34
4H	2H	2.56	3.62	2.97	3.97	4.35	2.56	3.62	2.97	3.97	4.35
	3H	2.50	3.34	2.91	3.74	4.15	2.50	3.34	2.91	3.74	4.15
	4H	2.49	3.24	2.93	3.66	4.10	2.49	3.24	2.93	3.66	4.10
	6H	2.58	3.23	3.05	3.67	4.14	2.58	3.23	3.05	3.67	4.14
	8H	2.61	3.21	3.08	3.66	4.13	2.61	3.21	3.08	3.66	4.13
	12H	2.61	3.14	3.10	3.63	4.10	2.61	3.14	3.10	3.63	4.10
8H	4H	2.40	3.00	2.87	3.45	3.92	2.40	3.00	2.87	3.45	3.92
	6H	2.54	3.04	3.05	3.54	4.02	2.54	3.04	3.05	3.54	4.02
	8H	2.60	3.05	3.12	3.57	4.06	2.60	3.05	3.12	3.57	4.06
	12H	2.63	3.04	3.15	3.53	4.10	2.63	3.04	3.15	3.53	4.10
12H	4H	2.37	2.90	2.86	3.38	3.86	2.37	2.90	2.86	3.38	3.86
	6H	2.51	2.96	3.04	3.48	3.97	2.51	2.96	3.04	3.48	3.97
	8H	2.60	3.01	3.12	3.50	4.07	2.60	3.01	3.12	3.50	4.07

END OF REPORT