

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980302

Luminaire Tested: PRLX-243-930-LL1-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P980302
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-37)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-243-930-LL1-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 243 SHADE WITH FROSTED LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 824.0 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.31
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P980302
CATALOG NUMBER: PRLX-243-930-LL1-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P980302

CATALOG NUMBER: PRLX-243-930-LL1-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91													91															
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81													81															
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73													73															
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65													65															
5	85	74	67	62	83	73	67	62	71	66	61	70	64	60	68	63	60	58													58															
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52													52															
7	74	62	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47													47															
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43													43															
9	65	53	46	41	64	52	46	41	51	45	41	50	45	40	49	44	40	39													39															
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35													35															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2267
5°	2248
10°	2206
15°	2154
20°	2118
25°	2084
30°	2045
35°	2017
40°	1986
45°	1954
50°	1607
55°	379
60°	22
65°	22
70°	27
75°	29
80°	20
85°	23

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1954 cd/sqm

TEST NUMBER: P980302

CATALOG NUMBER: PRLX-243-930-LL1-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.9	5.2
10°-20°	119.1	14.5
20°-30°	176.3	21.4
30°-40°	209.5	25.4
40°-50°	210.4	25.5
50°-60°	62.0	7.5
60°-70°	1.9	0.2
70°-80°	1.4	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.2	41.0
0°-40°	547.8	66.5
0°-60°	820.2	99.5
0°-90°	824.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	824.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	459	
5°	454	43
15°	422	119
25°	383	176
35°	335	210
45°	280	210
55°	44	62
65°	2	2
75°	2	1
85°	0	1
90°	0	



TEST NUMBER: P980302

CATALOG NUMBER: PRLX-243-930-LL1-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	459.4
2.5°	458.3
5°	453.8
7.5°	447.4
10°	440.3
12.5°	431.7
15°	421.7
17.5°	412.7
20°	403.3
22.5°	394.0
25°	382.8
27.5°	370.8
30°	358.9
32.5°	346.9
35°	334.9
37.5°	322.6
40°	308.4
42.5°	294.9
45°	280.0
47.5°	257.9
50°	209.3
52.5°	126.3
55°	44.1
57.5°	8.6
60°	2.2
62.5°	1.9
65°	1.9
67.5°	1.9
70°	1.9
72.5°	1.5
75°	1.5
77.5°	1.1
80°	0.7
82.5°	0.7
85°	0.4
87.5°	0.4
90°	0.0



TEST NUMBER: P980302
 CATALOG NUMBER: PRLX-243-930-LL1-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00