

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980350

Luminaire Tested: PRLX-243-930-LL6-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P980350
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-243-930-LL6-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 243 SHADE WITH CLEAR LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3628.9 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.34
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P980350
CATALOG NUMBER: PRLX-243-930-LL6-C-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P980350

CATALOG NUMBER: PRLX-243-930-LL6-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	105	99	95	91	103	98	93	89	94	91	88	91	88	86	88	86	84	82				82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74				74
4	92	83	76	71	90	81	75	70	79	74	69	77	72	69	75	71	68	66				66
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59				59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53				53
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48				48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44				44
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40				40
10	62	50	43	38	61	50	43	38	49	43	38	48	42	38	47	42	38	36				36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	10408
5°	10170
10°	9850
15°	9627
20°	9523
25°	9479
30°	9423
35°	9418
40°	9405
45°	9404
50°	5450
55°	483
60°	73
65°	86
70°	107
75°	112
80°	85
85°	85

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9404 cd/sqm

TEST NUMBER: P980350

CATALOG NUMBER: PRLX-243-930-LL6-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.2	5.3
10°-20°	532.9	14.7
20°-30°	802.7	22.1
30°-40°	978.5	27.0
40°-50°	983.4	27.1
50°-60°	122.8	3.4
60°-70°	7.3	0.2
70°-80°	6.0	0.2
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1528.8	42.1
0°-40°	2507.3	69.1
0°-60°	3613.4	99.6
0°-90°	3628.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3628.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2110	
5°	2053	193
15°	1885	533
25°	1741	803
35°	1564	978
45°	1348	983
55°	56	123
65°	7	7
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P980350

CATALOG NUMBER: PRLX-243-930-LL6-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	2109.6
2.5°	2100.8
5°	2053.4
7.5°	2004.6
10°	1966.1
12.5°	1929.2
15°	1884.8
17.5°	1847.8
20°	1813.8
22.5°	1782.7
25°	1741.3
27.5°	1698.4
30°	1654.0
32.5°	1609.6
35°	1563.7
37.5°	1514.9
40°	1460.2
42.5°	1404.0
45°	1347.7
47.5°	1272.3
50°	710.1
52.5°	134.6
55°	56.2
57.5°	17.8
60°	7.4
62.5°	7.4
65°	7.4
67.5°	7.4
70°	7.4
72.5°	7.4
75°	5.9
77.5°	4.4
80°	3.0
82.5°	3.0
85°	1.5
87.5°	1.5
90°	0.0



TEST NUMBER: P980350
 CATALOG NUMBER: PRLX-243-930-LL6-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00