

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979382

Luminaire Tested: PRLX-240-930-LL5-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979382
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-240-930-LL5-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 240 SHADE WITH FROSTED LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3029.2 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.33
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 29.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979382
CATALOG NUMBER: PRLX-240-930-LL5-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979382

CATALOG NUMBER: PRLX-240-930-LL5-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	112	109	106	103	110	106	104	101	102	100	98	99	97	95	95	94	92	90													90															
2	105	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	81													81															
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72													72															
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64													64															
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57													57															
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51													51															
7	73	61	54	48	71	61	53	48	59	53	48	58	52	48	57	51	47	46													46															
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41													41															
9	64	52	45	40	63	51	44	40	50	44	39	49	43	39	48	43	39	37													37															
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34													34															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	15935
5°	15889
10°	15774
15°	15529
20°	15337
25°	15119
30°	14851
35°	14656
40°	14432
45°	14029
50°	11958
55°	6107
60°	989
65°	126
70°	118
75°	156
80°	157
85°	150

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14029 cd/sqm

TEST NUMBER: P979382

CATALOG NUMBER: PRLX-240-930-LL5-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.1	4.9
10°-20°	420.4	13.9
20°-30°	626.4	20.7
30°-40°	745.5	24.6
40°-50°	744.2	24.6
50°-60°	326.4	10.8
60°-70°	11.3	0.4
70°-80°	4.1	0.1
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1196.0	39.5
0°-40°	1941.4	64.1
0°-60°	3012.0	99.4
0°-90°	3029.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3029.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1583	
5°	1572	149
15°	1490	420
25°	1361	626
35°	1192	745
45°	985	744
55°	348	326
65°	5	11
75°	4	4
85°	1	2
90°	0	

TEST NUMBER: P979382

CATALOG NUMBER: PRLX-240-930-LL5-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1582.6
2.5°	1581.3
5°	1572.0
7.5°	1558.7
10°	1542.8
12.5°	1520.2
15°	1489.7
17.5°	1459.2
20°	1431.3
22.5°	1398.1
25°	1360.9
27.5°	1318.4
30°	1277.3
32.5°	1234.8
35°	1192.3
37.5°	1145.8
40°	1098.0
42.5°	1047.6
45°	985.2
47.5°	897.5
50°	763.4
52.5°	573.6
55°	347.9
57.5°	156.7
60°	49.1
62.5°	10.6
65°	5.3
67.5°	4.0
70°	4.0
72.5°	4.0
75°	4.0
77.5°	4.0
80°	2.7
82.5°	2.7
85°	1.3
87.5°	1.3
90°	0.0



TEST NUMBER: P979382
 CATALOG NUMBER: PRLX-240-930-LL5-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.92	13.27	12.29	13.58	13.90	11.92	13.27	12.29	13.58	13.90
	3H	11.80	12.98	12.18	13.31	13.67	11.80	12.98	12.18	13.31	13.67
	4H	11.74	12.83	12.14	13.18	13.56	11.74	12.83	12.14	13.18	13.56
	6H	11.67	12.67	12.08	13.04	13.43	11.67	12.67	12.08	13.04	13.43
	8H	11.63	12.57	12.06	12.96	13.37	11.63	12.57	12.06	12.96	13.37
	12H	11.59	12.49	12.02	12.87	13.30	11.59	12.49	12.02	12.87	13.30
4H	2H	11.73	12.82	12.13	13.17	13.55	11.73	12.82	12.13	13.17	13.55
	3H	11.61	12.48	12.02	12.89	13.29	11.61	12.48	12.02	12.89	13.29
	4H	11.53	12.30	11.96	12.72	13.17	11.53	12.30	11.96	12.72	13.17
	6H	11.46	12.13	11.92	12.57	13.04	11.46	12.13	11.92	12.57	13.04
	8H	11.41	12.03	11.88	12.48	12.95	11.41	12.03	11.88	12.48	12.95
	12H	11.36	11.92	11.85	12.40	12.87	11.36	11.92	11.85	12.40	12.87
8H	4H	11.39	12.02	11.86	12.46	12.93	11.39	12.02	11.86	12.46	12.93
	6H	11.30	11.81	11.80	12.31	12.79	11.30	11.81	11.80	12.31	12.79
	8H	11.24	11.71	11.76	12.23	12.72	11.24	11.71	11.76	12.23	12.72
	12H	11.20	11.62	11.71	12.12	12.69	11.20	11.62	11.71	12.12	12.69
12H	4H	11.34	11.89	11.83	12.38	12.85	11.34	11.89	11.83	12.38	12.85
	6H	11.23	11.70	11.75	12.22	12.71	11.23	11.70	11.75	12.22	12.71
	8H	11.19	11.62	11.71	12.11	12.68	11.19	11.62	11.71	12.11	12.68