

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980391

Luminaire Tested: PRLX-243-935-LL2-C-U-S-WHTE-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P980391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-31)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-243-935-LL2-C-U-S-WHTE-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE 243 SHADE WITH CLEAR LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1828.6 lumens
Efficiency: N/A
Efficacy: 166.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.38
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P980391
CATALOG NUMBER: PRLX-243-935-LL2-C-U-S-WHTE-X

Luminous Intensity Polar Plot





TEST NUMBER: P980391

CATALOG NUMBER: PRLX-243-935-LL2-C-U-S-WHTE-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68
4	88	78	71	65	86	77	70	65	75	68	64	72	67	63	70	66	62	60
5	82	71	63	57	80	70	63	57	68	61	56	66	60	56	64	59	55	53
6	76	65	57	51	75	64	56	51	62	55	50	60	55	50	59	54	50	48
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	40	39
9	62	50	43	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4470
5°	4381
10°	4276
15°	4196
20°	4176
25°	4179
30°	4171
35°	4192
40°	4217
45°	4254
50°	2955
55°	962
60°	802
65°	870
70°	952
75°	989
80°	946
85°	957

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4254 cd/sqm

TEST NUMBER: P980391

CATALOG NUMBER: PRLX-243-935-LL2-C-U-S-WHTE-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.5	4.6
10°-20°	232.6	12.7
20°-30°	353.8	19.3
30°-40°	435.9	23.8
40°-50°	447.2	24.5
50°-60°	129.9	7.1
60°-70°	73.5	4.0
70°-80°	53.7	2.9
80°-90°	18.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	669.8	36.6
0°-40°	1105.7	60.5
0°-60°	1682.8	92.0
0°-90°	1828.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1828.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	906	
5°	885	83
15°	821	233
25°	768	354
35°	696	436
45°	610	447
55°	112	130
65°	74	74
75°	52	54
85°	17	18
90°	0	



TEST NUMBER: P980391

CATALOG NUMBER: PRLX-243-935-LL2-C-U-S-WHTE-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	906.0
2.5°	903.2
5°	884.6
7.5°	867.1
10°	853.5
12.5°	838.3
15°	821.4
17.5°	809.5
20°	795.4
22.5°	783.5
25°	767.7
27.5°	749.7
30°	732.2
32.5°	715.2
35°	696.0
37.5°	676.9
40°	654.8
42.5°	634.0
45°	609.7
47.5°	558.3
50°	385.0
52.5°	151.3
55°	111.8
57.5°	92.0
60°	81.3
62.5°	77.9
65°	74.5
67.5°	70.6
70°	66.0
72.5°	59.8
75°	51.9
77.5°	42.3
80°	33.3
82.5°	24.8
85°	16.9
87.5°	9.6
90°	0.0



TEST NUMBER: P980391
 CATALOG NUMBER: PRLX-243-935-LL2-C-U-S-WHTE-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.72	9.14	8.09	9.45	9.77	7.72	9.14	8.09	9.45	9.77
	3H	10.15	11.40	10.53	11.73	12.09	10.15	11.40	10.53	11.73	12.09
	4H	11.20	12.37	11.61	12.72	13.11	11.20	12.37	11.61	12.72	13.11
	6H	11.99	13.07	12.40	13.43	13.83	11.99	13.07	12.40	13.43	13.83
	8H	12.27	13.29	12.69	13.68	14.08	12.27	13.29	12.69	13.68	14.08
	12H	12.48	13.46	12.91	13.84	14.27	12.48	13.46	12.91	13.84	14.27
4H	2H	8.47	9.65	8.88	10.00	10.38	8.47	9.65	8.88	10.00	10.38
	3H	11.17	12.13	11.58	12.53	12.93	11.17	12.13	11.58	12.53	12.93
	4H	12.36	13.22	12.79	13.64	14.08	12.36	13.22	12.79	13.64	14.08
	6H	13.27	14.02	13.73	14.46	14.93	13.27	14.02	13.73	14.46	14.93
	8H	13.60	14.30	14.07	14.74	15.21	13.60	14.30	14.07	14.74	15.21
	12H	13.86	14.49	14.35	14.97	15.44	13.86	14.49	14.35	14.97	15.44
8H	4H	12.78	13.48	13.25	13.92	14.39	12.78	13.48	13.25	13.92	14.39
	6H	13.84	14.41	14.34	14.91	15.39	13.84	14.41	14.34	14.91	15.39
	8H	14.26	14.78	14.78	15.29	15.78	14.26	14.78	14.78	15.29	15.78
	12H	14.63	15.09	15.14	15.59	16.15	14.63	15.09	15.14	15.59	16.15
12H	4H	12.83	13.45	13.31	13.93	14.40	12.83	13.45	13.31	13.93	14.40
	6H	13.92	14.44	14.44	14.96	15.45	13.92	14.44	14.44	14.96	15.45
	8H	14.41	14.88	14.92	15.37	15.94	14.41	14.88	14.92	15.37	15.94