

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P980422

Luminaire Tested: PRLX-243-935-LL5-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P980422
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-37)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-243-935-LL5-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 243 SHADE WITH FROSTED LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3023.9 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.31
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 29.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P980422
CATALOG NUMBER: PRLX-243-935-LL5-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P980422

CATALOG NUMBER: PRLX-243-935-LL5-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65
5	85	74	67	62	83	73	67	62	71	66	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	62	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43
9	65	53	46	41	64	52	46	41	51	45	41	50	45	40	49	44	40	39
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8317
5°	8247
10°	8096
15°	7903
20°	7771
25°	7646
30°	7502
35°	7402
40°	7289
45°	7169
50°	5896
55°	1393
60°	81
65°	81
70°	100
75°	105
80°	77
85°	79

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7169 cd/sqm

TEST NUMBER: P980422

CATALOG NUMBER: PRLX-243-935-LL5-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.4	5.2
10°-20°	437.0	14.5
20°-30°	646.9	21.4
30°-40°	768.9	25.4
40°-50°	772.2	25.5
50°-60°	227.5	7.5
60°-70°	7.0	0.2
70°-80°	5.2	0.2
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1241.2	41.0
0°-40°	2010.1	66.5
0°-60°	3009.8	99.5
0°-90°	3023.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3023.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1686	
5°	1665	157
15°	1547	437
25°	1405	647
35°	1229	769
45°	1027	772
55°	162	228
65°	7	7
75°	6	5
85°	1	2
90°	0	



TEST NUMBER: P980422

CATALOG NUMBER: PRLX-243-935-LL5-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1685.8
2.5°	1681.7
5°	1665.2
7.5°	1641.9
10°	1615.9
12.5°	1584.3
15°	1547.3
17.5°	1514.4
20°	1480.1
22.5°	1445.8
25°	1404.6
27.5°	1360.7
30°	1316.8
32.5°	1272.9
35°	1229.0
37.5°	1183.8
40°	1131.7
42.5°	1082.3
45°	1027.4
47.5°	946.5
50°	768.2
52.5°	463.6
55°	161.9
57.5°	31.5
60°	8.2
62.5°	6.9
65°	6.9
67.5°	6.9
70°	6.9
72.5°	5.5
75°	5.5
77.5°	4.1
80°	2.7
82.5°	2.7
85°	1.4
87.5°	1.4
90°	0.0



TEST NUMBER: P980422
 CATALOG NUMBER: PRLX-243-935-LL5-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.26	0.00	0.00	0.00	0.00	0.26
	3H	0.00	0.00	0.00	0.00	0.37	0.00	0.00	0.00	0.00	0.37
	4H	0.00	0.00	0.00	0.10	0.48	0.00	0.00	0.00	0.10	0.48
	6H	0.00	0.00	0.00	0.13	0.53	0.00	0.00	0.00	0.13	0.53
	8H	0.00	0.00	0.00	0.15	0.55	0.00	0.00	0.00	0.15	0.55
	12H	0.00	0.00	0.00	0.12	0.55	0.00	0.00	0.00	0.12	0.55
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.21	0.00	0.00	0.00	0.00	0.21
	4H	0.00	0.00	0.00	0.00	0.45	0.00	0.00	0.00	0.00	0.45
	6H	0.00	0.00	0.00	0.12	0.58	0.00	0.00	0.00	0.12	0.58
	8H	0.00	0.00	0.00	0.16	0.63	0.00	0.00	0.00	0.16	0.63
	12H	0.00	0.00	0.00	0.19	0.66	0.00	0.00	0.00	0.19	0.66
8H	4H	0.00	0.00	0.00	0.00	0.38	0.00	0.00	0.00	0.00	0.38
	6H	0.00	0.00	0.00	0.10	0.58	0.00	0.00	0.00	0.10	0.58
	8H	0.00	0.00	0.00	0.22	0.72	0.00	0.00	0.00	0.22	0.72
	12H	0.00	0.00	0.00	0.28	0.85	0.00	0.00	0.00	0.28	0.85
12H	4H	0.00	0.00	0.00	0.00	0.32	0.00	0.00	0.00	0.00	0.32
	6H	0.00	0.00	0.00	0.06	0.55	0.00	0.00	0.00	0.06	0.55
	8H	0.00	0.00	0.00	0.19	0.76	0.00	0.00	0.00	0.19	0.76