

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979500

Luminaire Tested: PRLX-240-940-LL1-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-240-940-LL1-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 240 SHADE WITH CLEAR LENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1004.6 lumens
Efficiency: N/A
Efficacy: 133.9 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.39
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979500

CATALOG NUMBER: PRLX-240-940-LL1-C-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P979500

CATALOG NUMBER: PRLX-240-940-LL1-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	99		99	97	96		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68
6	79	68	61	56	78	67	61	55	66	60	55		64	59	55		63
7	74	63	55	50	73	62	55	50	61	54	50		59	54	49		58
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		54
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50
10	61	49	42	38	60	49	42	38	48	42	37		47	41	37		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5416
5°	5409
10°	5385
15°	5290
20°	5254
25°	5246
30°	5216
35°	5234
40°	5248
45°	5207
50°	3564
55°	555
60°	137
65°	29
70°	35
75°	47
80°	70
85°	46

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5207 cd/sqm

TEST NUMBER: P979500

CATALOG NUMBER: PRLX-240-940-LL1-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.8	5.1
10°-20°	143.5	14.3
20°-30°	217.3	21.6
30°-40°	266.4	26.5
40°-50°	263.7	26.3
50°-60°	58.8	5.9
60°-70°	2.2	0.2
70°-80°	1.3	0.1
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	411.6	41.0
0°-40°	678.0	67.5
0°-60°	1000.6	99.6
0°-90°	1004.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1004.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	538	
5°	535	51
15°	508	144
25°	472	217
35°	426	266
45°	366	264
55°	32	59
65°	1	2
75°	1	1
85°	0	1
90°	0	

TEST NUMBER: P979500

CATALOG NUMBER: PRLX-240-940-LL1-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	537.9
2.5°	538.3
5°	535.1
7.5°	531.1
10°	526.7
12.5°	516.7
15°	507.5
17.5°	499.5
20°	490.3
22.5°	481.5
25°	472.2
27.5°	459.8
30°	448.6
32.5°	437.0
35°	425.8
37.5°	413.4
40°	399.3
42.5°	384.9
45°	365.7
47.5°	307.2
50°	227.5
52.5°	106.1
55°	31.6
57.5°	15.2
60°	6.8
62.5°	2.4
65°	1.2
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

TEST NUMBER: P979500

CATALOG NUMBER: PRLX-240-940-LL1-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.98	0.05	1.29	1.61	0.00	0.98	0.05	1.29	1.61
	3H	0.00	0.73	0.00	1.06	1.42	0.00	0.73	0.00	1.06	1.42
	4H	0.00	0.62	0.00	0.97	1.36	0.00	0.62	0.00	0.97	1.36
	6H	0.00	0.55	0.00	0.92	1.32	0.00	0.55	0.00	0.92	1.32
	8H	0.00	0.50	0.03	0.90	1.30	0.00	0.50	0.03	0.90	1.30
	12H	0.00	0.45	0.01	0.83	1.26	0.00	0.45	0.01	0.83	1.26
4H	2H	0.00	0.54	0.00	0.89	1.27	0.00	0.54	0.00	0.89	1.27
	3H	0.00	0.26	0.00	0.67	1.07	0.00	0.26	0.00	0.67	1.07
	4H	0.00	0.16	0.00	0.58	1.03	0.00	0.16	0.00	0.58	1.03
	6H	0.00	0.15	0.00	0.60	1.06	0.00	0.15	0.00	0.60	1.06
	8H	0.00	0.14	0.01	0.58	1.06	0.00	0.14	0.01	0.58	1.06
	12H	0.00	0.07	0.02	0.55	1.02	0.00	0.07	0.02	0.55	1.02
8H	4H	0.00	0.00	0.00	0.37	0.85	0.00	0.00	0.00	0.37	0.85
	6H	0.00	0.00	0.00	0.46	0.94	0.00	0.00	0.00	0.46	0.94
	8H	0.00	0.00	0.05	0.49	0.99	0.00	0.00	0.05	0.49	0.99
	12H	0.00	0.00	0.07	0.46	1.03	0.00	0.00	0.07	0.46	1.03
12H	4H	0.00	0.00	0.00	0.31	0.78	0.00	0.00	0.00	0.31	0.78
	6H	0.00	0.00	0.00	0.40	0.89	0.00	0.00	0.00	0.40	0.89
	8H	0.00	0.00	0.04	0.43	1.00	0.00	0.00	0.04	0.43	1.00

END OF REPORT