

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979650

Luminaire Tested: PRLX-241-927-74L-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P979650
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-927-74L-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 241 SHADE WITH CLEAR LENS
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3341.7 lumens
Efficiency: N/A
Efficacy: 54.3 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.05
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 61.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979650

CATALOG NUMBER: PRLX-241-927-74L-C-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P979650

CATALOG NUMBER: PRLX-241-927-74L-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		93
2	108	103	98	95	105	101	97	94	98	94	92		95	92	90		86
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		80
4	97	89	83	79	95	88	82	78	85	81	77		83	80	76		74
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		69
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		64
7	82	72	66	62	81	72	66	62	70	65	61		69	65	61		59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		55
9	74	64	58	54	73	63	57	53	62	57	53		61	57	53		51
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24232
5°	23107
10°	22007
15°	21508
20°	21366
25°	21217
30°	20996
35°	19742
40°	3037
45°	494
50°	233
55°	231
60°	265
65°	275
70°	243
75°	256
80°	191
85°	195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 494 cd/sqm

TEST NUMBER: P979650

CATALOG NUMBER: PRLX-241-927-74L-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	279.5	8.4
10°-20°	762.5	22.8
20°-30°	1149.1	34.4
30°-40°	1048.0	31.4
40°-50°	61.6	1.8
50°-60°	15.7	0.5
60°-70°	14.1	0.4
70°-80°	8.2	0.2
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2191.1	65.6
0°-40°	3239.1	96.9
0°-60°	3316.4	99.2
0°-90°	3341.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3341.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3143	
5°	2986	279
15°	2695	763
25°	2494	1149
35°	2098	1048
45°	45	62
55°	17	16
65°	15	14
75°	9	8
85°	2	3
90°	0	

TEST NUMBER: P979650

CATALOG NUMBER: PRLX-241-927-74L-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	3143.3
2.5°	3102.4
5°	2986.0
7.5°	2880.3
10°	2811.3
12.5°	2748.8
15°	2694.9
17.5°	2649.6
20°	2604.4
22.5°	2561.2
25°	2494.4
27.5°	2423.3
30°	2358.6
32.5°	2283.1
35°	2097.7
37.5°	1129.7
40°	301.8
42.5°	101.3
45°	45.3
47.5°	23.7
50°	19.4
52.5°	17.2
55°	17.2
57.5°	17.2
60°	17.2
62.5°	15.1
65°	15.1
67.5°	12.9
70°	10.8
72.5°	8.6
75°	8.6
77.5°	6.5
80°	4.3
82.5°	4.3
85°	2.2
87.5°	2.2
90°	0.0

TEST NUMBER: P979650

CATALOG NUMBER: PRLX-241-927-74L-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.17	0.56	0.00	0.00	0.00	0.17	0.56
	6H	0.00	0.25	0.00	0.62	1.02	0.00	0.25	0.00	0.62	1.02
	8H	0.00	0.42	0.22	0.82	1.23	0.00	0.42	0.22	0.82	1.23
	12H	0.00	0.53	0.36	0.92	1.35	0.00	0.53	0.36	0.92	1.35
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.11	0.52	0.00	0.00	0.00	0.11	0.52
	4H	0.02	0.57	0.46	0.99	1.44	0.02	0.57	0.46	0.99	1.44
	6H	0.61	1.08	1.08	1.53	2.00	0.61	1.08	1.08	1.53	2.00
	8H	0.89	1.32	1.37	1.77	2.25	0.89	1.32	1.37	1.77	2.25
	12H	1.07	1.44	1.56	1.93	2.41	1.07	1.44	1.56	1.93	2.41
8H	4H	0.28	0.71	0.76	1.16	1.64	0.28	0.71	0.76	1.16	1.64
	6H	0.99	1.33	1.50	1.83	2.32	0.99	1.33	1.50	1.83	2.32
	8H	1.39	1.69	1.92	2.21	2.71	1.39	1.69	1.92	2.21	2.71
	12H	1.67	1.93	2.20	2.43	3.01	1.67	1.93	2.20	2.43	3.01
12H	4H	0.27	0.64	0.77	1.13	1.61	0.27	0.64	0.77	1.13	1.61
	6H	1.04	1.34	1.57	1.86	2.36	1.04	1.34	1.57	1.86	2.36
	8H	1.51	1.77	2.03	2.27	2.85	1.51	1.77	2.03	2.27	2.85

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7