

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244812

Luminaire Tested: PRLX-MIN-L-930-05L-U-PS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-L-930-05L-U-PS
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, PINSTRIPE SHADE TEXTURE
LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 565.0 lumens
Efficiency: N/A
Efficacy: 38.2 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 14.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244812

CATALOG NUMBER: PRLX-MIN-L-930-05L-U-PS

Luminous Intensity Polar Plot



TEST NUMBER: P1244812

CATALOG NUMBER: PRLX-MIN-L-930-05L-U-PS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56		
1	95	89	83	78	88	82	77	73	70	66	63	59	56	53	48	46	44	39		
2	85	76	68	62	79	70	63	58	60	54	50	50	46	42	41	38	35	30		
3	77	66	57	50	71	61	53	47	52	46	41	43	39	35	36	32	29	25		
4	71	58	49	42	65	54	46	40	46	40	35	39	34	30	32	28	25	21		
5	65	52	43	37	60	48	40	34	41	35	30	35	30	26	29	25	22	18		
6	60	47	38	32	55	44	36	30	38	31	26	32	27	23	27	22	19	16		
7	56	43	34	28	52	40	32	27	35	28	24	29	24	21	25	21	18	15		
8	52	39	31	25	48	37	29	24	32	26	21	27	22	19	23	19	16	14		
9	49	36	28	23	45	34	27	22	30	24	20	26	21	17	22	18	15	13		
10	46	34	26	21	43	32	25	20	28	22	18	24	19	16	21	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25910
5°	11882
10°	2770
15°	1057
20°	682
25°	543
30°	483
35°	452
40°	436
45°	429
50°	426
55°	429
60°	432
65°	438
70°	442
75°	447
80°	447
85°	457

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 90°
Luminance: 467 cd/sqm

TEST NUMBER: P1244812

CATALOG NUMBER: PRLX-MIN-L-930-05L-U-PS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.5	6.1
10°-20°	19.0	3.4
20°-30°	18.5	3.3
30°-40°	24.3	4.3
40°-50°	31.9	5.6
50°-60°	39.7	7.0
60°-70°	46.7	8.3
70°-80°	51.0	9.0
80°-90°	52.8	9.3
90°-100°	52.9	9.4
100°-110°	50.3	8.9
110°-120°	44.5	7.9
120°-130°	36.6	6.5
130°-140°	27.6	4.9
140°-150°	18.7	3.3
150°-160°	10.9	1.9
160°-170°	4.5	0.8
170°-180°	0.4	0.1
0°-30°	72.1	12.8
0°-40°	96.4	17.1
0°-60°	168.0	29.7
0°-90°	318.5	56.4
90°-120°	147.6	26.1
90°-150°	230.5	40.8
90°-180°	246.0	43.5
0°-180°	565.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	819	
5°	482	35
15°	61	19
25°	39	19
35°	39	24
45°	41	32
55°	44	40
65°	47	47
75°	48	51
85°	48	40
90°	48	27
95°	48	40
105°	48	50
115°	45	44
125°	41	37
135°	36	28
145°	30	19
155°	24	11
165°	16	5
175°	2	0
180°	0	

TEST NUMBER: P1244812

CATALOG NUMBER: PRLX-MIN-L-930-05L-U-PS

CANDELA DISTRIBUTION (FULL):

0°	
0°	819.0
2.5°	898.4
5°	481.7
7.5°	196.0
10°	136.2
12.5°	83.4
15°	60.7
17.5°	50.5
20°	44.5
22.5°	41.4
25°	39.4
27.5°	38.6
30°	38.3
32.5°	38.3
35°	38.6
37.5°	38.9
40°	39.7
42.5°	40.3
45°	41.1
47.5°	42.0
50°	42.6
52.5°	43.4
55°	44.3
57.5°	45.1
60°	45.7
62.5°	46.5
65°	47.1
67.5°	47.7
70°	47.9
72.5°	48.2
75°	48.5
77.5°	48.2
80°	48.2
82.5°	48.2
85°	48.5
87.5°	48.5
90°	48.5
92.5°	48.5
95°	48.5
97.5°	48.5
100°	48.2
102.5°	47.9
105°	47.7
107.5°	47.1
110°	46.5

TEST NUMBER: P1244812

CATALOG NUMBER: PRLX-MIN-L-930-05L-U-PS

CANDELA DISTRIBUTION (continued):

	0°
112.5°	45.7
115°	44.8
117.5°	44.0
120°	42.8
122.5°	42.0
125°	40.8
127.5°	39.7
130°	38.3
132.5°	37.2
135°	35.7
137.5°	34.0
140°	32.6
142.5°	31.2
145°	29.5
147.5°	28.1
150°	26.7
152.5°	25.0
155°	23.5
157.5°	21.8
160°	20.1
162.5°	18.2
165°	15.9
167.5°	12.8
170°	8.8
172.5°	5.4
175°	2.3
177.5°	0.6
180°	0.3

TEST NUMBER: P1244812

CATALOG NUMBER: PRLX-MIN-L-930-05L-U-PS

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.7	5.7	5.6	6.6	7.8	4.7	5.7	5.6	6.6	7.8
	3H	7.7	8.6	8.6	9.6	10.8	7.7	8.6	8.6	9.6	10.8
	4H	9.1	10.0	10.0	11.0	12.2	9.1	10.0	10.0	11.0	12.2
	6H	10.5	11.4	11.4	12.3	13.5	10.5	11.4	11.4	12.3	13.5
	8H	11.2	12.0	12.1	12.9	14.2	11.2	12.0	12.1	12.9	14.2
	12H	11.8	12.6	12.8	13.6	14.8	11.8	12.6	12.8	13.6	14.8
4H	2H	5.5	6.4	6.4	7.3	8.5	5.5	6.4	6.4	7.3	8.5
	3H	8.6	9.4	9.5	10.4	11.6	8.6	9.4	9.5	10.4	11.6
	4H	10.2	11.0	11.1	11.9	13.1	10.2	11.0	11.1	11.9	13.1
	6H	11.8	12.4	12.7	13.4	14.6	11.8	12.4	12.7	13.4	14.6
	8H	12.5	13.2	13.5	14.1	15.4	12.5	13.2	13.5	14.1	15.4
	12H	13.3	13.9	14.2	14.8	16.1	13.3	13.9	14.2	14.8	16.1
8H	4H	10.7	11.3	11.7	12.3	13.6	10.7	11.3	11.7	12.3	13.6
	6H	12.5	13.0	13.4	14.0	15.3	12.5	13.0	13.4	14.0	15.3
	8H	13.4	13.9	14.4	14.9	16.1	13.4	13.9	14.4	14.9	16.1
	12H	14.3	14.8	15.3	15.8	17.1	14.3	14.8	15.3	15.8	17.1
12H	4H	10.8	11.4	11.8	12.4	13.6	10.8	11.4	11.8	12.4	13.6
	6H	12.7	13.2	13.6	14.1	15.4	12.7	13.2	13.6	14.1	15.4
	8H	13.6	14.1	14.6	15.1	16.4	13.6	14.1	14.6	15.1	16.4

(END OF REPORT)