

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979592

Luminaire Tested: PRLX-241-927-LL2-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979592
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-927-LL2-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 241 SHADE WITH FROSTED LENS
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 734.1 lumens
Efficiency: N/A
Efficacy: 66.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.07
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979592
CATALOG NUMBER: PRLX-241-927-LL2-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979592

CATALOG NUMBER: PRLX-241-927-LL2-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	98	97	96	95	93	93	86	86																	
	1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	86	86	83	81	79	79	73	73	68																	
	2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86	86	83	81	79	79	73	73	68	68	63																	
	3	102	95	90	86	100	93	89	85	91	87	83	88	85	82	86	83	81	79	79	73	73	68	68	63	63	58	58	54																	
	4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73	73	68	68	63	63	58	58	54	54	50																	
	5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68	68	63	63	58	58	54	54	50	50	47																	
	6	86	77	70	66	84	76	70	65	74	69	65	73	68	65	71	67	64	63	63	58	58	54	54	50	50	47	47	43																	
	7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	54	54	50	50	47	47	43	43	39																	
	8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54	54	50	50	47	47	43	43	39	39	35																	
	9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	47	47	43	43	39	39	35	35	31																	
	10	69	59	53	49	68	58	53	49	58	52	49	57	52	48	56	52	48	47	47	43	43	39	39	35	35	31	31	27																	

AVERAGE LUMINANCE (cd/sqm):

	0°	4888
	5°	4806
	10°	4676
	15°	4558
	20°	4499
	25°	4437
	30°	4359
	35°	3832
	40°	1702
	45°	214
	50°	49
	55°	55
	60°	56
	65°	57
	70°	47
	75°	45
	80°	44
	85°	44

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 214 cd/sqm

TEST NUMBER: P979592

CATALOG NUMBER: PRLX-241-927-LL2-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.5	8.0
10°-20°	161.4	22.0
20°-30°	240.3	32.7
30°-40°	231.9	31.6
40°-50°	33.7	4.6
50°-60°	3.5	0.5
60°-70°	2.9	0.4
70°-80°	1.6	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	460.1	62.7
0°-40°	692.0	94.3
0°-60°	729.2	99.3
0°-90°	734.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	734.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	634	
5°	621	58
15°	571	161
25°	522	240
35°	407	232
45°	20	34
55°	4	4
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P979592

CATALOG NUMBER: PRLX-241-927-LL2-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	634.0
2.5°	630.9
5°	621.1
7.5°	608.2
10°	597.4
12.5°	582.9
15°	571.1
17.5°	559.7
20°	548.4
22.5°	536.6
25°	521.6
27.5°	506.1
30°	489.7
32.5°	463.4
35°	407.2
37.5°	301.5
40°	169.1
42.5°	70.1
45°	19.6
47.5°	6.2
50°	4.1
52.5°	4.1
55°	4.1
57.5°	3.6
60°	3.6
62.5°	3.1
65°	3.1
67.5°	2.6
70°	2.1
72.5°	2.1
75°	1.5
77.5°	1.0
80°	1.0
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0



TEST NUMBER: P979592
 CATALOG NUMBER: PRLX-241-927-LL2-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00