

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244897

Luminaire Tested: PRLX-MIN-M-930-03L-U-NL

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-M-930-03L-U-NL
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, NATURAL LINES SHADE TEXT LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 286.1 lumens
Efficiency: N/A
Efficacy: 25.8 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244897
CATALOG NUMBER: PRLX-MIN-M-930-03L-U-NL

Luminous Intensity Polar Plot





TEST NUMBER: P1244897

CATALOG NUMBER: PRLX-MIN-M-930-03L-U-NL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56			56
1	95	89	84	79	88	82	78	73	70	66	63	59	56	53	48	46	44	39			39
2	86	76	69	62	79	71	64	58	60	55	50	50	46	42	41	38	35	30			30
3	78	67	58	51	71	62	54	48	52	46	41	44	39	35	36	32	29	25			25
4	71	59	50	43	65	55	47	41	47	40	35	39	34	30	32	28	25	22			22
5	66	53	44	37	60	49	41	35	42	36	31	36	31	27	29	26	22	19			19
6	61	48	39	33	56	45	37	31	38	32	27	33	28	24	27	23	20	17			17
7	57	44	35	29	52	41	33	28	35	29	25	30	25	22	25	21	18	16			16
8	53	40	32	27	49	38	30	25	33	27	22	28	23	20	24	20	17	15			15
9	50	37	29	24	46	35	28	23	31	25	21	26	22	18	23	19	16	14			14
10	47	35	27	22	44	33	26	21	29	23	19	25	20	17	21	18	15	13			13

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24906
5°	12591
10°	2255
15°	718
20°	450
25°	364
30°	317
35°	291
40°	282
45°	276
50°	272
55°	272
60°	272
65°	275
70°	280
75°	286
80°	291
85°	299

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 304 cd/sqm

TEST NUMBER: P1244897

CATALOG NUMBER: PRLX-MIN-M-930-03L-U-NL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.4	7.5
10°-20°	9.4	3.3
20°-30°	8.8	3.1
30°-40°	11.6	4.1
40°-50°	15.3	5.3
50°-60°	19.0	6.6
60°-70°	22.4	7.8
70°-80°	25.4	8.9
80°-90°	27.0	9.4
90°-100°	27.0	9.4
100°-110°	25.5	8.9
110°-120°	22.8	8.0
120°-130°	18.7	6.6
130°-140°	14.2	5.0
140°-150°	9.7	3.4
150°-160°	5.5	1.9
160°-170°	2.2	0.8
170°-180°	0.2	0.1
0°-30°	39.6	13.8
0°-40°	51.2	17.9
0°-60°	85.5	29.9
0°-90°	160.3	56.0
90°-120°	75.3	26.3
90°-150°	117.9	41.2
90°-180°	126.0	44.0
0°-180°	286.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	486	
5°	334	21
15°	29	9
25°	19	9
35°	18	12
45°	20	15
55°	21	19
65°	23	22
75°	24	25
85°	25	20
90°	25	14
95°	25	20
105°	24	26
115°	23	23
125°	21	19
135°	18	14
145°	15	10
155°	12	5
165°	8	2
175°	1	0
180°	0	

TEST NUMBER: P1244897

CATALOG NUMBER: PRLX-MIN-M-930-03L-U-NL

CANDELA DISTRIBUTION (FULL):

0°	
0°	486.0
2.5°	537.0
5°	334.3
7.5°	110.8
10°	75.3
12.5°	41.3
15°	28.7
17.5°	23.7
20°	20.8
22.5°	19.7
25°	19.0
27.5°	18.3
30°	18.3
32.5°	18.3
35°	18.3
37.5°	18.7
40°	19.0
42.5°	19.4
45°	19.7
47.5°	20.1
50°	20.4
52.5°	20.8
55°	21.2
57.5°	21.5
60°	21.9
62.5°	22.2
65°	22.6
67.5°	23.0
70°	23.3
72.5°	23.7
75°	24.0
77.5°	24.4
80°	24.4
82.5°	24.8
85°	24.8
87.5°	24.8
90°	24.8
92.5°	24.8
95°	24.8
97.5°	24.8
100°	24.4
102.5°	24.4
105°	24.0
107.5°	24.0
110°	23.7

TEST NUMBER: P1244897

CATALOG NUMBER: PRLX-MIN-M-930-03L-U-NL

CANDELA DISTRIBUTION (continued):

	0°
112.5°	23.3
115°	23.0
117.5°	22.6
120°	21.9
122.5°	21.5
125°	20.8
127.5°	20.4
130°	19.7
132.5°	19.0
135°	18.3
137.5°	17.6
140°	16.9
142.5°	16.1
145°	15.4
147.5°	14.7
150°	13.6
152.5°	12.6
155°	11.8
157.5°	10.8
160°	9.7
162.5°	9.0
165°	7.5
167.5°	6.1
170°	4.3
172.5°	2.5
175°	0.7
177.5°	0.0
180°	0.0



TEST NUMBER: P1244897

CATALOG NUMBER: PRLX-MIN-M-930-03L-U-NL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.8	3.9	3.7	4.8	6.0	2.8	3.9	3.7	4.8	6.0
	3H	5.9	6.8	6.8	7.8	9.0	5.9	6.8	6.8	7.8	9.0
	4H	7.4	8.3	8.3	9.2	10.4	7.4	8.3	8.3	9.2	10.4
	6H	8.9	9.7	9.8	10.6	11.9	8.9	9.7	9.8	10.6	11.9
	8H	9.6	10.4	10.5	11.3	12.6	9.6	10.4	10.5	11.3	12.6
	12H	10.3	11.0	11.2	12.0	13.2	10.3	11.0	11.2	12.0	13.2
4H	2H	3.6	4.5	4.5	5.5	6.7	3.6	4.5	4.5	5.5	6.7
	3H	6.8	7.6	7.8	8.6	9.8	6.8	7.6	7.8	8.6	9.8
	4H	8.5	9.2	9.4	10.2	11.4	8.5	9.2	9.4	10.2	11.4
	6H	10.1	10.8	11.1	11.8	13.0	10.1	10.8	11.1	11.8	13.0
	8H	10.9	11.6	11.9	12.5	13.8	10.9	11.6	11.9	12.5	13.8
	12H	11.7	12.3	12.7	13.3	14.6	11.7	12.3	12.7	13.3	14.6
8H	4H	9.0	9.6	10.0	10.6	11.9	9.0	9.6	10.0	10.6	11.9
	6H	10.9	11.4	11.8	12.4	13.7	10.9	11.4	11.8	12.4	13.7
	8H	11.8	12.3	12.8	13.3	14.6	11.8	12.3	12.8	13.3	14.6
	12H	12.8	13.2	13.8	14.2	15.5	12.8	13.2	13.8	14.2	15.5
12H	4H	9.1	9.7	10.1	10.7	12.0	9.1	9.7	10.1	10.7	12.0
	6H	11.1	11.5	12.0	12.5	13.8	11.1	11.5	12.0	12.5	13.8
	8H	12.1	12.5	13.1	13.5	14.8	12.1	12.5	13.1	13.5	14.8

(END OF REPORT)