

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244960

Luminaire Tested: PRLX-MIN-S-930-07L-U-NL

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244960
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-MIN-S-930-07L-U-NL
Description: 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, NATURAL LINES SHADE TEXTURE
LIGHT LEVEL 3
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 701.0 lumens
Efficiency: N/A
Efficacy: 43.3 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.38
Luminous Opening: Rectangular w/ Sides (W: 0.62' x L: 0.62' x H: 0.87')
CIE Type: Semi-Direct

Input Watts (W): 16.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244960
CATALOG NUMBER: PRLX-MIN-S-930-07L-U-NL

Luminous Intensity Polar Plot





TEST NUMBER: P1244960

CATALOG NUMBER: PRLX-MIN-S-930-07L-U-NL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	113	113	113	113	107	107	107	107	97	97	97		87	87	87		78	78	78	74
1	101	96	91	87	96	91	87	83	82	79	76		74	71	69		66	64	62	58
2	92	84	77	71	87	80	73	68	72	67	63		65	61	57		58	55	52	49
3	85	74	66	60	80	71	63	58	64	58	53		58	53	49		52	48	45	42
4	78	67	58	52	74	63	56	50	58	51	46		52	47	43		47	43	40	37
5	72	60	52	46	68	58	50	44	53	46	41		48	43	38		44	39	36	33
6	67	55	47	41	64	53	45	39	48	42	37		44	39	35		40	36	33	30
7	63	51	42	37	60	49	41	36	45	38	34		41	36	32		38	33	30	28
8	59	47	39	34	56	45	38	33	42	35	31		38	33	29		35	31	28	26
9	56	44	36	31	53	42	35	30	39	33	29		36	31	27		33	29	26	24
10	53	41	34	29	50	39	33	28	37	31	27		34	29	26		32	27	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	16307
5°	16220
10°	14345
15°	3414
20°	2854
25°	2397
30°	1904
35°	1574
40°	1372
45°	1251
50°	1151
55°	1079
60°	1015
65°	957
70°	915
75°	858
80°	785
85°	733

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1251 cd/sqm



TEST NUMBER: P1244960

CATALOG NUMBER: PRLX-MIN-S-930-07L-U-NL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	8.8
10°-20°	64.8	9.2
20°-30°	59.0	8.4
30°-40°	58.4	8.3
40°-50°	59.4	8.5
50°-60°	60.1	8.6
60°-70°	58.2	8.3
70°-80°	52.6	7.5
80°-90°	43.3	6.2
90°-100°	40.7	5.8
100°-110°	38.8	5.5
110°-120°	34.7	4.9
120°-130°	28.7	4.1
130°-140°	20.5	2.9
140°-150°	11.8	1.7
150°-160°	6.1	0.9
160°-170°	2.3	0.3
170°-180°	0.2	0.0
0°-30°	185.1	26.4
0°-40°	243.5	34.7
0°-60°	363.1	51.8
0°-90°	517.3	73.8
90°-120°	114.1	16.3
90°-150°	175.1	25.0
90°-180°	184.0	26.2
0°-180°	701.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	592	
5°	658	61
15°	164	65
25°	130	59
35°	92	58
45°	77	59
55°	67	60
65°	58	58
75°	50	53
85°	39	33
90°	38	21
95°	37	30
105°	36	39
115°	35	35
125°	32	29
135°	26	21
145°	18	12
155°	13	6
165°	8	2
175°	0	0
180°	0	

TEST NUMBER: P1244960

CATALOG NUMBER: PRLX-MIN-S-930-07L-U-NL

CANDELA DISTRIBUTION (FULL):

0°	
0°	591.8
2.5°	613.3
5°	657.8
7.5°	649.8
10°	638.5
12.5°	282.5
15°	164.3
17.5°	155.7
20°	146.6
22.5°	139.1
25°	130.0
27.5°	118.1
30°	107.9
32.5°	98.8
35°	92.4
37.5°	87.0
40°	82.7
42.5°	79.5
45°	76.8
47.5°	74.1
50°	71.4
52.5°	69.3
55°	67.1
57.5°	65.0
60°	62.8
62.5°	60.7
65°	58.5
67.5°	56.9
70°	54.8
72.5°	52.6
75°	49.9
77.5°	47.3
80°	44.0
82.5°	40.8
85°	39.2
87.5°	38.1
90°	37.6
92.5°	37.6
95°	37.1
97.5°	37.1
100°	37.1
102.5°	37.1
105°	36.5
107.5°	36.5
110°	36.0

TEST NUMBER: P1244960

CATALOG NUMBER: PRLX-MIN-S-930-07L-U-NL

CANDELA DISTRIBUTION (continued):

	0°
112.5°	35.4
115°	34.9
117.5°	34.4
120°	33.8
122.5°	32.8
125°	32.2
127.5°	31.1
130°	29.5
132.5°	28.5
135°	26.3
137.5°	24.7
140°	22.6
142.5°	20.4
145°	18.3
147.5°	16.6
150°	15.6
152.5°	14.5
155°	12.9
157.5°	11.8
160°	10.7
162.5°	9.7
165°	8.1
167.5°	6.4
170°	4.3
172.5°	2.1
175°	0.5
177.5°	0.0
180°	0.0



TEST NUMBER: P1244960

CATALOG NUMBER: PRLX-MIN-S-930-07L-U-NL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.9	10.1	9.7	10.8	11.7	8.9	10.1	9.7	10.8	11.7
	3H	11.3	12.3	12.0	13.1	14.0	11.3	12.3	12.0	13.1	14.0
	4H	12.3	13.3	13.1	14.1	15.0	12.3	13.3	13.1	14.1	15.0
	6H	13.3	14.2	14.0	15.0	15.9	13.3	14.2	14.0	15.0	15.9
	8H	13.7	14.6	14.5	15.4	16.3	13.7	14.6	14.5	15.4	16.3
	12H	14.1	14.9	14.9	15.7	16.7	14.1	14.9	14.9	15.7	16.7
4H	2H	9.5	10.5	10.3	11.3	12.2	9.5	10.5	10.3	11.3	12.2
	3H	12.1	12.9	12.8	13.7	14.7	12.1	12.9	12.8	13.7	14.7
	4H	13.3	14.1	14.0	14.9	15.8	13.3	14.1	14.0	14.9	15.8
	6H	14.4	15.1	15.2	15.9	16.9	14.4	15.1	15.2	15.9	16.9
	8H	14.9	15.6	15.7	16.4	17.4	14.9	15.6	15.7	16.4	17.4
	12H	15.4	16.0	16.2	16.8	17.8	15.4	16.0	16.2	16.8	17.8
8H	4H	13.7	14.3	14.5	15.1	16.1	13.7	14.3	14.5	15.1	16.1
	6H	15.0	15.5	15.8	16.4	17.4	15.0	15.5	15.8	16.4	17.4
	8H	15.6	16.1	16.4	16.9	17.9	15.6	16.1	16.4	16.9	17.9
	12H	16.2	16.7	17.1	17.5	18.6	16.2	16.7	17.1	17.5	18.6
12H	4H	13.7	14.3	14.5	15.1	16.1	13.7	14.3	14.5	15.1	16.1
	6H	15.1	15.6	15.9	16.4	17.5	15.1	15.6	15.9	16.4	17.5
	8H	15.8	16.2	16.6	17.1	18.1	15.8	16.2	16.6	17.1	18.1

(END OF REPORT)