

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244964

Luminaire Tested: PRLX-MIN-S-930-09L-U-OW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1244964  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-MIN-S-930-09L-U-OW  
Description: 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, OPEN WEAVE SHADE TEXTURE LIGHT LEVEL 4  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1009.0 lumens  
Efficiency: N/A  
Efficacy: 47.4 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.38  
Luminous Opening: Rectangular w/ Sides (W: 0.62' x L: 0.62' x H: 0.87')  
CIE Type: Semi-Direct

Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P1244964

CATALOG NUMBER: PRLX-MIN-S-930-09L-U-OW

### Luminous Intensity Polar Plot





TEST NUMBER: P1244964

CATALOG NUMBER: PRLX-MIN-S-930-09L-U-OW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74
1	101	96	91	87	96	91	87	83	82	79	76	74	71	69	66	64	62	58
2	92	84	77	71	87	80	73	68	72	67	63	65	61	57	58	55	52	49
3	85	74	66	60	80	71	63	58	64	58	53	58	53	49	52	48	45	42
4	78	67	58	52	74	63	56	50	58	51	46	52	47	43	47	43	40	37
5	72	60	52	46	68	58	50	44	53	46	41	48	43	38	44	39	36	33
6	67	55	47	41	64	53	45	39	48	42	37	44	39	35	40	36	33	30
7	63	51	42	37	60	49	41	36	45	38	34	41	36	32	38	33	30	28
8	59	47	39	34	56	45	38	33	42	35	31	38	33	29	35	31	28	26
9	56	44	36	31	53	42	35	30	39	33	29	36	31	27	33	29	26	24
10	53	41	34	29	50	39	33	28	37	31	27	34	29	26	32	27	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	23472
5°	23349
10°	20648
15°	4914
20°	4107
25°	3450
30°	2742
35°	2264
40°	1975
45°	1800
50°	1658
55°	1553
60°	1461
65°	1379
70°	1316
75°	1236
80°	1131
85°	1055

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1800 cd/sqm

TEST NUMBER: P1244964

CATALOG NUMBER: PRLX-MIN-S-930-09L-U-OW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.3	8.8
10°-20°	93.2	9.2
20°-30°	84.9	8.4
30°-40°	84.0	8.3
40°-50°	85.5	8.5
50°-60°	86.6	8.6
60°-70°	83.8	8.3
70°-80°	75.8	7.5
80°-90°	62.4	6.2
90°-100°	58.5	5.8
100°-110°	55.8	5.5
110°-120°	49.9	4.9
120°-130°	41.3	4.1
130°-140°	29.5	2.9
140°-150°	17.0	1.7
150°-160°	8.8	0.9
160°-170°	3.4	0.3
170°-180°	0.3	0.0
<hr/>		
0°-30°	266.5	26.4
0°-40°	350.5	34.7
0°-60°	522.5	51.8
0°-90°	744.5	73.8
90°-120°	164.2	16.3
90°-150°	252.0	25.0
90°-180°	264.0	26.2
0°-180°	1009.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	852	
5°	947	88
15°	236	93
25°	187	85
35°	133	84
45°	110	86
55°	97	87
65°	84	84
75°	72	76
85°	56	47
90°	54	30
95°	53	44
105°	53	56
115°	50	50
125°	46	41
135°	38	30
145°	26	17
155°	19	9
165°	12	3
175°	1	0
180°	0	

TEST NUMBER: P1244964

CATALOG NUMBER: PRLX-MIN-S-930-09L-U-OW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	851.8
2.5°	882.7
5°	946.9
7.5°	935.3
10°	919.0
12.5°	406.6
15°	236.5
17.5°	224.2
20°	211.0
22.5°	200.2
25°	187.1
27.5°	170.0
30°	155.4
32.5°	142.2
35°	132.9
37.5°	125.2
40°	119.0
42.5°	114.4
45°	110.5
47.5°	106.7
50°	102.8
52.5°	99.7
55°	96.6
57.5°	93.5
60°	90.4
62.5°	87.3
65°	84.3
67.5°	81.9
70°	78.8
72.5°	75.7
75°	71.9
77.5°	68.0
80°	63.4
82.5°	58.7
85°	56.4
87.5°	54.9
90°	54.1
92.5°	54.1
95°	53.3
97.5°	53.3
100°	53.3
102.5°	53.3
105°	52.6
107.5°	52.6
110°	51.8

TEST NUMBER: P1244964

CATALOG NUMBER: PRLX-MIN-S-930-09L-U-OW

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	51.0
115°	50.2
117.5°	49.5
120°	48.7
122.5°	47.1
125°	46.4
127.5°	44.8
130°	42.5
132.5°	41.0
135°	37.9
137.5°	35.6
140°	32.5
142.5°	29.4
145°	26.3
147.5°	24.0
150°	22.4
152.5°	20.9
155°	18.6
157.5°	17.0
160°	15.5
162.5°	13.9
165°	11.6
167.5°	9.3
170°	6.2
172.5°	3.1
175°	0.8
177.5°	0.0
180°	0.0

TEST NUMBER: P1244964

CATALOG NUMBER: PRLX-MIN-S-930-09L-U-OW

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.2	11.4	10.9	12.1	13.0	10.2	11.4	10.9	12.1	13.0
	3H	12.5	13.6	13.2	14.3	15.2	12.5	13.6	13.2	14.3	15.2
	4H	13.6	14.6	14.3	15.3	16.3	13.6	14.6	14.3	15.3	16.3
	6H	14.5	15.5	15.3	16.2	17.2	14.5	15.5	15.3	16.2	17.2
	8H	15.0	15.8	15.7	16.6	17.6	15.0	15.8	15.7	16.6	17.6
	12H	15.4	16.2	16.1	17.0	18.0	15.4	16.2	16.1	17.0	18.0
4H	2H	10.8	11.8	11.6	12.6	13.5	10.8	11.8	11.6	12.6	13.5
	3H	13.3	14.2	14.1	15.0	15.9	13.3	14.2	14.1	15.0	15.9
	4H	14.5	15.3	15.3	16.1	17.1	14.5	15.3	15.3	16.1	17.1
	6H	15.7	16.4	16.5	17.2	18.2	15.7	16.4	16.5	17.2	18.2
	8H	16.2	16.8	17.0	17.6	18.6	16.2	16.8	17.0	17.6	18.6
	12H	16.7	17.3	17.5	18.1	19.1	16.7	17.3	17.5	18.1	19.1
8H	4H	14.9	15.6	15.7	16.4	17.4	14.9	15.6	15.7	16.4	17.4
	6H	16.2	16.8	17.0	17.6	18.6	16.2	16.8	17.0	17.6	18.6
	8H	16.8	17.4	17.7	18.2	19.2	16.8	17.4	17.7	18.2	19.2
	12H	17.5	18.0	18.3	18.8	19.9	17.5	18.0	18.3	18.8	19.9
12H	4H	15.0	15.6	15.8	16.4	17.4	15.0	15.6	15.8	16.4	17.4
	6H	16.3	16.8	17.2	17.7	18.7	16.3	16.8	17.2	17.7	18.7
	8H	17.0	17.5	17.9	18.3	19.4	17.0	17.5	17.9	18.3	19.4

(END OF REPORT)