

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244837

Luminaire Tested: PRLX-MIN-L-935-09L-U-NL

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244837
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-L-935-09L-U-NL
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, NATURAL LINES SHADE TEXTUF
LIGHT LEVEL 3
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 866.9 lumens
Efficiency: N/A
Efficacy: 38.4 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 22.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244837

CATALOG NUMBER: PRLX-MIN-L-935-09L-U-NL

Luminous Intensity Polar Plot





TEST NUMBER: P1244837

CATALOG NUMBER: PRLX-MIN-L-935-09L-U-NL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|--|----|----|----|--|----|----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 109 | 109 | 109 | 109 | 101 | 101 | 101 | 101 | 87 | 87 | 87 | | 74 | 74 | 74 | | 62 | 62 | 62 | 56 |
| 1 | 95 | 89 | 83 | 78 | 88 | 82 | 77 | 73 | 70 | 66 | 63 | | 59 | 56 | 53 | | 48 | 46 | 44 | 39 |
| 2 | 85 | 76 | 68 | 62 | 79 | 70 | 63 | 58 | 60 | 54 | 50 | | 50 | 46 | 42 | | 41 | 38 | 35 | 30 |
| 3 | 77 | 66 | 57 | 50 | 71 | 61 | 53 | 47 | 52 | 46 | 41 | | 43 | 39 | 35 | | 36 | 32 | 29 | 25 |
| 4 | 71 | 58 | 49 | 42 | 65 | 54 | 46 | 40 | 46 | 40 | 35 | | 39 | 34 | 30 | | 32 | 28 | 25 | 21 |
| 5 | 65 | 52 | 43 | 37 | 60 | 48 | 40 | 34 | 41 | 35 | 30 | | 35 | 30 | 26 | | 29 | 25 | 22 | 18 |
| 6 | 60 | 47 | 38 | 32 | 55 | 44 | 36 | 30 | 38 | 31 | 26 | | 32 | 27 | 23 | | 27 | 22 | 19 | 16 |
| 7 | 56 | 43 | 34 | 28 | 52 | 40 | 32 | 27 | 35 | 28 | 24 | | 29 | 24 | 21 | | 25 | 21 | 18 | 15 |
| 8 | 52 | 39 | 31 | 25 | 48 | 37 | 29 | 24 | 32 | 26 | 21 | | 27 | 22 | 19 | | 23 | 19 | 16 | 14 |
| 9 | 49 | 36 | 28 | 23 | 45 | 34 | 27 | 22 | 30 | 24 | 20 | | 26 | 21 | 17 | | 22 | 18 | 15 | 13 |
| 10 | 46 | 34 | 26 | 21 | 43 | 32 | 25 | 20 | 28 | 22 | 18 | | 24 | 19 | 16 | | 21 | 17 | 14 | 12 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 39757 |
| 5° | 18231 |
| 10° | 4249 |
| 15° | 1623 |
| 20° | 1047 |
| 25° | 834 |
| 30° | 741 |
| 35° | 693 |
| 40° | 669 |
| 45° | 659 |
| 50° | 654 |
| 55° | 658 |
| 60° | 663 |
| 65° | 673 |
| 70° | 679 |
| 75° | 686 |
| 80° | 687 |
| 85° | 700 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 716 cd/sqm



TEST NUMBER: P1244837

CATALOG NUMBER: PRLX-MIN-L-935-09L-U-NL

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 53.0 | 6.1 |
| 10°-20° | 29.2 | 3.4 |
| 20°-30° | 28.4 | 3.3 |
| 30°-40° | 37.3 | 4.3 |
| 40°-50° | 48.9 | 5.6 |
| 50°-60° | 60.9 | 7.0 |
| 60°-70° | 71.7 | 8.3 |
| 70°-80° | 78.3 | 9.0 |
| 80°-90° | 81.0 | 9.3 |
| 90°-100° | 81.1 | 9.4 |
| 100°-110° | 77.2 | 8.9 |
| 110°-120° | 68.3 | 7.9 |
| 120°-130° | 56.2 | 6.5 |
| 130°-140° | 42.4 | 4.9 |
| 140°-150° | 28.7 | 3.3 |
| 150°-160° | 16.8 | 1.9 |
| 160°-170° | 6.9 | 0.8 |
| 170°-180° | 0.7 | 0.1 |
| 0°-30° | 110.6 | 12.8 |
| 0°-40° | 147.9 | 17.1 |
| 0°-60° | 257.8 | 29.7 |
| 0°-90° | 488.8 | 56.4 |
| 90°-120° | 226.5 | 26.1 |
| 90°-150° | 353.8 | 40.8 |
| 90°-180° | 378.0 | 43.6 |
| 0°-180° | 866.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|------|------|------|
| 0° | 1257 | |
| 5° | 739 | 53 |
| 15° | 93 | 29 |
| 25° | 60 | 28 |
| 35° | 59 | 37 |
| 45° | 63 | 49 |
| 55° | 68 | 61 |
| 65° | 72 | 72 |
| 75° | 74 | 78 |
| 85° | 74 | 61 |
| 90° | 74 | 41 |
| 95° | 74 | 61 |
| 105° | 73 | 77 |
| 115° | 69 | 68 |
| 125° | 63 | 56 |
| 135° | 55 | 42 |
| 145° | 45 | 29 |
| 155° | 36 | 17 |
| 165° | 24 | 7 |
| 175° | 4 | 1 |
| 180° | 0 | |

TEST NUMBER: P1244837

CATALOG NUMBER: PRLX-MIN-L-935-09L-U-NL

CANDELA DISTRIBUTION (FULL):

| 0° | |
|--------|--------|
| 0° | 1256.7 |
| 2.5° | 1378.6 |
| 5° | 739.1 |
| 7.5° | 300.8 |
| 10° | 208.9 |
| 12.5° | 128.0 |
| 15° | 93.2 |
| 17.5° | 77.5 |
| 20° | 68.3 |
| 22.5° | 63.6 |
| 25° | 60.5 |
| 27.5° | 59.2 |
| 30° | 58.8 |
| 32.5° | 58.8 |
| 35° | 59.2 |
| 37.5° | 59.6 |
| 40° | 60.9 |
| 42.5° | 61.8 |
| 45° | 63.1 |
| 47.5° | 64.4 |
| 50° | 65.3 |
| 52.5° | 66.6 |
| 55° | 67.9 |
| 57.5° | 69.2 |
| 60° | 70.1 |
| 62.5° | 71.4 |
| 65° | 72.3 |
| 67.5° | 73.1 |
| 70° | 73.6 |
| 72.5° | 74.0 |
| 75° | 74.4 |
| 77.5° | 74.0 |
| 80° | 74.0 |
| 82.5° | 74.0 |
| 85° | 74.4 |
| 87.5° | 74.4 |
| 90° | 74.4 |
| 92.5° | 74.4 |
| 95° | 74.4 |
| 97.5° | 74.4 |
| 100° | 74.0 |
| 102.5° | 73.6 |
| 105° | 73.1 |
| 107.5° | 72.3 |
| 110° | 71.4 |

TEST NUMBER: P1244837

CATALOG NUMBER: PRLX-MIN-L-935-09L-U-NL

CANDELA DISTRIBUTION (continued):

| | 0° |
|--------|------|
| 112.5° | 70.1 |
| 115° | 68.8 |
| 117.5° | 67.5 |
| 120° | 65.7 |
| 122.5° | 64.4 |
| 125° | 62.7 |
| 127.5° | 60.9 |
| 130° | 58.8 |
| 132.5° | 57.0 |
| 135° | 54.8 |
| 137.5° | 52.2 |
| 140° | 50.1 |
| 142.5° | 47.9 |
| 145° | 45.3 |
| 147.5° | 43.1 |
| 150° | 40.9 |
| 152.5° | 38.3 |
| 155° | 36.1 |
| 157.5° | 33.5 |
| 160° | 30.9 |
| 162.5° | 27.9 |
| 165° | 24.4 |
| 167.5° | 19.6 |
| 170° | 13.5 |
| 172.5° | 8.3 |
| 175° | 3.5 |
| 177.5° | 0.9 |
| 180° | 0.4 |



TEST NUMBER: P1244837

CATALOG NUMBER: PRLX-MIN-L-935-09L-U-NL

CIE UGR TABLE:

| Reflectances: | | | | | | | | | | | |
|-----------------|------|------------------|------|------|------|------|----------------|------|------|------|------|
| Ceiling | | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 |
| Wall | | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 |
| Reference plane | | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| Room Dimensions | | Viewed crosswise | | | | | Viewed endwise | | | | |
| X=2H | Y=2H | 6.2 | 7.2 | 7.0 | 8.1 | 9.3 | 6.2 | 7.2 | 7.0 | 8.1 | 9.3 |
| | 3H | 9.2 | 10.1 | 10.1 | 11.0 | 12.2 | 9.2 | 10.1 | 10.1 | 11.0 | 12.2 |
| | 4H | 10.6 | 11.5 | 11.5 | 12.4 | 13.6 | 10.6 | 11.5 | 11.5 | 12.4 | 13.6 |
| | 6H | 12.0 | 12.9 | 12.9 | 13.8 | 15.0 | 12.0 | 12.9 | 12.9 | 13.8 | 15.0 |
| | 8H | 12.7 | 13.5 | 13.6 | 14.4 | 15.6 | 12.7 | 13.5 | 13.6 | 14.4 | 15.6 |
| | 12H | 13.3 | 14.1 | 14.2 | 15.1 | 16.3 | 13.3 | 14.1 | 14.2 | 15.1 | 16.3 |
| 4H | 2H | 6.9 | 7.9 | 7.9 | 8.8 | 10.0 | 6.9 | 7.9 | 7.9 | 8.8 | 10.0 |
| | 3H | 10.1 | 10.9 | 11.0 | 11.9 | 13.1 | 10.1 | 10.9 | 11.0 | 11.9 | 13.1 |
| | 4H | 11.7 | 12.4 | 12.6 | 13.4 | 14.6 | 11.7 | 12.4 | 12.6 | 13.4 | 14.6 |
| | 6H | 13.3 | 13.9 | 14.2 | 14.9 | 16.1 | 13.3 | 13.9 | 14.2 | 14.9 | 16.1 |
| | 8H | 14.0 | 14.6 | 15.0 | 15.6 | 16.9 | 14.0 | 14.6 | 15.0 | 15.6 | 16.9 |
| | 12H | 14.8 | 15.4 | 15.7 | 16.3 | 17.6 | 14.8 | 15.4 | 15.7 | 16.3 | 17.6 |
| 8H | 4H | 12.2 | 12.8 | 13.1 | 13.8 | 15.1 | 12.2 | 12.8 | 13.1 | 13.8 | 15.1 |
| | 6H | 14.0 | 14.5 | 14.9 | 15.5 | 16.8 | 14.0 | 14.5 | 14.9 | 15.5 | 16.8 |
| | 8H | 14.9 | 15.4 | 15.8 | 16.4 | 17.6 | 14.9 | 15.4 | 15.8 | 16.4 | 17.6 |
| | 12H | 15.8 | 16.3 | 16.8 | 17.2 | 18.5 | 15.8 | 16.3 | 16.8 | 17.2 | 18.5 |
| 12H | 4H | 12.3 | 12.9 | 13.3 | 13.9 | 15.1 | 12.3 | 12.9 | 13.3 | 13.9 | 15.1 |
| | 6H | 14.2 | 14.6 | 15.1 | 15.6 | 16.9 | 14.2 | 14.6 | 15.1 | 15.6 | 16.9 |
| | 8H | 15.1 | 15.6 | 16.1 | 16.6 | 17.9 | 15.1 | 15.6 | 16.1 | 16.6 | 17.9 |

(END OF REPORT)