

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244849

Luminaire Tested: PRLX-MIN-L-935-23L-U-NL

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244849
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-L-935-23L-U-NL
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, NATURAL LINES SHADE TEXTUF
LIGHT LEVEL 7
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2235.0 lumens
Efficiency: N/A
Efficacy: 38.4 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244849

CATALOG NUMBER: PRLX-MIN-L-935-23L-U-NL

Luminous Intensity Polar Plot





TEST NUMBER: P1244849

CATALOG NUMBER: PRLX-MIN-L-935-23L-U-NL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|--|----|----|----|--|----|----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 109 | 109 | 109 | 109 | 101 | 101 | 101 | 101 | 87 | 87 | 87 | | 74 | 74 | 74 | | 62 | 62 | 62 | 56 |
| 1 | 95 | 89 | 83 | 78 | 88 | 82 | 77 | 73 | 70 | 66 | 63 | | 59 | 56 | 53 | | 48 | 46 | 44 | 39 |
| 2 | 85 | 76 | 68 | 62 | 79 | 70 | 63 | 58 | 60 | 54 | 50 | | 50 | 46 | 42 | | 41 | 38 | 35 | 30 |
| 3 | 77 | 66 | 57 | 50 | 71 | 61 | 53 | 47 | 52 | 46 | 41 | | 43 | 39 | 35 | | 36 | 32 | 29 | 25 |
| 4 | 71 | 58 | 49 | 42 | 65 | 54 | 46 | 40 | 46 | 40 | 35 | | 39 | 34 | 30 | | 32 | 28 | 25 | 21 |
| 5 | 65 | 52 | 43 | 36 | 60 | 48 | 40 | 34 | 41 | 35 | 30 | | 35 | 30 | 26 | | 29 | 25 | 22 | 18 |
| 6 | 60 | 47 | 38 | 32 | 55 | 44 | 36 | 30 | 38 | 31 | 26 | | 32 | 27 | 23 | | 27 | 22 | 19 | 16 |
| 7 | 56 | 43 | 34 | 28 | 52 | 40 | 32 | 27 | 35 | 28 | 24 | | 29 | 24 | 21 | | 25 | 21 | 18 | 15 |
| 8 | 52 | 39 | 31 | 25 | 48 | 37 | 29 | 24 | 32 | 26 | 21 | | 27 | 22 | 19 | | 23 | 19 | 16 | 14 |
| 9 | 49 | 36 | 28 | 23 | 45 | 34 | 27 | 22 | 30 | 24 | 20 | | 26 | 21 | 17 | | 22 | 18 | 15 | 13 |
| 10 | 46 | 34 | 26 | 21 | 43 | 32 | 25 | 20 | 28 | 22 | 18 | | 24 | 19 | 16 | | 21 | 17 | 14 | 12 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 102492 |
| 5° | 46999 |
| 10° | 10955 |
| 15° | 4182 |
| 20° | 2701 |
| 25° | 2150 |
| 30° | 1910 |
| 35° | 1785 |
| 40° | 1727 |
| 45° | 1698 |
| 50° | 1685 |
| 55° | 1696 |
| 60° | 1709 |
| 65° | 1733 |
| 70° | 1749 |
| 75° | 1769 |
| 80° | 1770 |
| 85° | 1807 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 1848 cd/sqm



TEST NUMBER: P1244849

CATALOG NUMBER: PRLX-MIN-L-935-23L-U-NL

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 136.7 | 6.1 |
| 10°-20° | 75.2 | 3.4 |
| 20°-30° | 73.3 | 3.3 |
| 30°-40° | 96.2 | 4.3 |
| 40°-50° | 126.1 | 5.6 |
| 50°-60° | 157.0 | 7.0 |
| 60°-70° | 184.7 | 8.3 |
| 70°-80° | 202.0 | 9.0 |
| 80°-90° | 208.9 | 9.3 |
| 90°-100° | 209.2 | 9.4 |
| 100°-110° | 198.9 | 8.9 |
| 110°-120° | 175.9 | 7.9 |
| 120°-130° | 144.9 | 6.5 |
| 130°-140° | 109.3 | 4.9 |
| 140°-150° | 73.9 | 3.3 |
| 150°-160° | 43.3 | 1.9 |
| 160°-170° | 17.8 | 0.8 |
| 170°-180° | 1.7 | 0.1 |
| 0°-30° | 285.2 | 12.8 |
| 0°-40° | 381.4 | 17.1 |
| 0°-60° | 664.6 | 29.7 |
| 0°-90° | 1260.1 | 56.4 |
| 90°-120° | 584.0 | 26.1 |
| 90°-150° | 912.1 | 40.8 |
| 90°-180° | 975.0 | 43.6 |
| 0°-180° | 2235.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|------|------|------|
| 0° | 3240 | |
| 5° | 1905 | 137 |
| 15° | 240 | 75 |
| 25° | 156 | 73 |
| 35° | 153 | 96 |
| 45° | 163 | 126 |
| 55° | 175 | 157 |
| 65° | 186 | 185 |
| 75° | 192 | 202 |
| 85° | 192 | 156 |
| 90° | 192 | 105 |
| 95° | 192 | 157 |
| 105° | 188 | 199 |
| 115° | 177 | 176 |
| 125° | 162 | 145 |
| 135° | 141 | 109 |
| 145° | 117 | 74 |
| 155° | 93 | 43 |
| 165° | 63 | 18 |
| 175° | 9 | 2 |
| 180° | 1 | |

TEST NUMBER: P1244849

CATALOG NUMBER: PRLX-MIN-L-935-23L-U-NL

CANDELA DISTRIBUTION (FULL):

| 0° | |
|--------|--------|
| 0° | 3239.7 |
| 2.5° | 3553.9 |
| 5° | 1905.4 |
| 7.5° | 775.4 |
| 10° | 538.6 |
| 12.5° | 329.9 |
| 15° | 240.1 |
| 17.5° | 199.7 |
| 20° | 176.2 |
| 22.5° | 163.8 |
| 25° | 156.0 |
| 27.5° | 152.6 |
| 30° | 151.5 |
| 32.5° | 151.5 |
| 35° | 152.6 |
| 37.5° | 153.7 |
| 40° | 157.1 |
| 42.5° | 159.3 |
| 45° | 162.7 |
| 47.5° | 166.1 |
| 50° | 168.3 |
| 52.5° | 171.7 |
| 55° | 175.1 |
| 57.5° | 178.4 |
| 60° | 180.7 |
| 62.5° | 184.0 |
| 65° | 186.3 |
| 67.5° | 188.5 |
| 70° | 189.6 |
| 72.5° | 190.8 |
| 75° | 191.9 |
| 77.5° | 190.8 |
| 80° | 190.8 |
| 82.5° | 190.8 |
| 85° | 191.9 |
| 87.5° | 191.9 |
| 90° | 191.9 |
| 92.5° | 191.9 |
| 95° | 191.9 |
| 97.5° | 191.9 |
| 100° | 190.8 |
| 102.5° | 189.6 |
| 105° | 188.5 |
| 107.5° | 186.3 |
| 110° | 184.0 |

TEST NUMBER: P1244849

CATALOG NUMBER: PRLX-MIN-L-935-23L-U-NL

CANDELA DISTRIBUTION (continued):

| | 0° |
|--------|-------|
| 112.5° | 180.7 |
| 115° | 177.3 |
| 117.5° | 173.9 |
| 120° | 169.4 |
| 122.5° | 166.1 |
| 125° | 161.6 |
| 127.5° | 157.1 |
| 130° | 151.5 |
| 132.5° | 147.0 |
| 135° | 141.4 |
| 137.5° | 134.7 |
| 140° | 129.0 |
| 142.5° | 123.4 |
| 145° | 116.7 |
| 147.5° | 111.1 |
| 150° | 105.5 |
| 152.5° | 98.7 |
| 155° | 93.1 |
| 157.5° | 86.4 |
| 160° | 79.7 |
| 162.5° | 71.8 |
| 165° | 62.8 |
| 167.5° | 50.5 |
| 170° | 34.8 |
| 172.5° | 21.3 |
| 175° | 9.0 |
| 177.5° | 2.2 |
| 180° | 1.1 |



TEST NUMBER: P1244849

CATALOG NUMBER: PRLX-MIN-L-935-23L-U-NL

CIE UGR TABLE:

| Reflectances: | | | | | | | | | | | |
|-----------------|------|------------------|------|------|------|------|----------------|------|------|------|------|
| Ceiling | | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 |
| Wall | | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 |
| Reference plane | | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| Room Dimensions | | Viewed crosswise | | | | | Viewed endwise | | | | |
| X=2H | Y=2H | 9.5 | 10.5 | 10.3 | 11.4 | 12.6 | 9.5 | 10.5 | 10.3 | 11.4 | 12.6 |
| | 3H | 12.5 | 13.4 | 13.3 | 14.3 | 15.5 | 12.5 | 13.4 | 13.3 | 14.3 | 15.5 |
| | 4H | 13.9 | 14.8 | 14.8 | 15.7 | 16.9 | 13.9 | 14.8 | 14.8 | 15.7 | 16.9 |
| | 6H | 15.3 | 16.1 | 16.2 | 17.1 | 18.3 | 15.3 | 16.1 | 16.2 | 17.1 | 18.3 |
| | 8H | 16.0 | 16.8 | 16.9 | 17.7 | 18.9 | 16.0 | 16.8 | 16.9 | 17.7 | 18.9 |
| | 12H | 16.6 | 17.4 | 17.5 | 18.3 | 19.6 | 16.6 | 17.4 | 17.5 | 18.3 | 19.6 |
| 4H | 2H | 10.2 | 11.2 | 11.1 | 12.1 | 13.3 | 10.2 | 11.2 | 11.1 | 12.1 | 13.3 |
| | 3H | 13.4 | 14.2 | 14.3 | 15.2 | 16.4 | 13.4 | 14.2 | 14.3 | 15.2 | 16.4 |
| | 4H | 15.0 | 15.7 | 15.9 | 16.7 | 17.9 | 15.0 | 15.7 | 15.9 | 16.7 | 17.9 |
| | 6H | 16.6 | 17.2 | 17.5 | 18.2 | 19.4 | 16.6 | 17.2 | 17.5 | 18.2 | 19.4 |
| | 8H | 17.3 | 17.9 | 18.2 | 18.9 | 20.2 | 17.3 | 17.9 | 18.2 | 18.9 | 20.2 |
| | 12H | 18.1 | 18.6 | 19.0 | 19.6 | 20.9 | 18.1 | 18.6 | 19.0 | 19.6 | 20.9 |
| 8H | 4H | 15.5 | 16.1 | 16.4 | 17.1 | 18.3 | 15.5 | 16.1 | 16.4 | 17.1 | 18.3 |
| | 6H | 17.3 | 17.8 | 18.2 | 18.8 | 20.1 | 17.3 | 17.8 | 18.2 | 18.8 | 20.1 |
| | 8H | 18.2 | 18.7 | 19.1 | 19.7 | 20.9 | 18.2 | 18.7 | 19.1 | 19.7 | 20.9 |
| | 12H | 19.1 | 19.5 | 20.1 | 20.5 | 21.8 | 19.1 | 19.5 | 20.1 | 20.5 | 21.8 |
| 12H | 4H | 15.6 | 16.2 | 16.6 | 17.2 | 18.4 | 15.6 | 16.2 | 16.6 | 17.2 | 18.4 |
| | 6H | 17.4 | 17.9 | 18.4 | 18.9 | 20.2 | 17.4 | 17.9 | 18.4 | 18.9 | 20.2 |
| | 8H | 18.4 | 18.9 | 19.4 | 19.9 | 21.2 | 18.4 | 18.9 | 19.4 | 19.9 | 21.2 |

(END OF REPORT)