

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244916

Luminaire Tested: PRLX-MIN-M-935-04L-U-OW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244916
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-M-935-04L-U-OW
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, OPEN WEAVE SHADE TEXTU
LIGHT LEVEL 3
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 482.0 lumens
Efficiency: N/A
Efficacy: 29.8 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 16.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244916

CATALOG NUMBER: PRLX-MIN-M-935-04L-U-OW

Luminous Intensity Polar Plot



TEST NUMBER: P1244916

CATALOG NUMBER: PRLX-MIN-M-935-04L-U-OW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62			56
1	95	89	84	79	88	82	78	73	70	66	63	59	56	53	48	46	44			39
2	86	76	69	62	79	71	64	58	60	55	50	50	46	42	41	38	35			30
3	78	67	58	51	71	62	54	48	52	46	41	44	39	35	36	32	29			25
4	71	59	50	43	65	55	47	41	47	40	35	39	34	30	32	28	25			22
5	66	53	44	37	60	49	41	35	42	36	31	36	31	27	29	26	22			19
6	61	48	39	33	56	45	37	31	38	32	27	33	28	24	27	23	20			17
7	57	44	35	29	52	41	33	28	35	29	25	30	25	22	25	21	18			16
8	53	40	32	27	49	38	30	25	33	27	22	28	23	20	24	20	17			15
9	50	37	29	24	46	35	28	23	31	25	21	26	22	18	23	19	16			14
10	47	35	27	22	44	33	26	21	29	23	19	25	20	17	21	18	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41977
5°	21219
10°	3801
15°	1211
20°	759
25°	613
30°	534
35°	491
40°	475
45°	464
50°	460
55°	457
60°	459
65°	463
70°	471
75°	483
80°	491
85°	502

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 90°
Luminance: 511 cd/sqm

TEST NUMBER: P1244916

CATALOG NUMBER: PRLX-MIN-M-935-04L-U-OW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.1	7.5
10°-20°	15.8	3.3
20°-30°	14.9	3.1
30°-40°	19.6	4.1
40°-50°	25.8	5.3
50°-60°	32.0	6.6
60°-70°	37.8	7.8
70°-80°	42.8	8.9
80°-90°	45.4	9.4
90°-100°	45.4	9.4
100°-110°	43.0	8.9
110°-120°	38.4	8.0
120°-130°	31.6	6.6
130°-140°	23.9	5.0
140°-150°	16.3	3.4
150°-160°	9.2	1.9
160°-170°	3.7	0.8
170°-180°	0.3	0.1
0°-30°	66.7	13.8
0°-40°	86.3	17.9
0°-60°	144.1	29.9
0°-90°	270.1	56.0
90°-120°	126.8	26.3
90°-150°	198.7	41.2
90°-180°	212.0	44.0
0°-180°	482.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	819	
5°	563	36
15°	48	16
25°	32	15
35°	31	20
45°	33	26
55°	36	32
65°	38	38
75°	40	43
85°	42	34
90°	42	23
95°	42	34
105°	40	43
115°	39	38
125°	35	32
135°	31	24
145°	26	16
155°	20	9
165°	13	4
175°	1	0
180°	0	

TEST NUMBER: P1244916

CATALOG NUMBER: PRLX-MIN-M-935-04L-U-OW

CANDELA DISTRIBUTION (FULL):

0°	
0°	819.1
2.5°	905.0
5°	563.4
7.5°	186.8
10°	126.9
12.5°	69.5
15°	48.4
17.5°	39.9
20°	35.1
22.5°	33.2
25°	32.0
27.5°	30.8
30°	30.8
32.5°	30.8
35°	30.8
37.5°	31.4
40°	32.0
42.5°	32.6
45°	33.2
47.5°	33.9
50°	34.5
52.5°	35.1
55°	35.7
57.5°	36.3
60°	36.9
62.5°	37.5
65°	38.1
67.5°	38.7
70°	39.3
72.5°	39.9
75°	40.5
77.5°	41.1
80°	41.1
82.5°	41.7
85°	41.7
87.5°	41.7
90°	41.7
92.5°	41.7
95°	41.7
97.5°	41.7
100°	41.1
102.5°	41.1
105°	40.5
107.5°	40.5
110°	39.9

TEST NUMBER: P1244916

CATALOG NUMBER: PRLX-MIN-M-935-04L-U-OW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	39.3
115°	38.7
117.5°	38.1
120°	36.9
122.5°	36.3
125°	35.1
127.5°	34.5
130°	33.2
132.5°	32.0
135°	30.8
137.5°	29.6
140°	28.4
142.5°	27.2
145°	26.0
147.5°	24.8
150°	23.0
152.5°	21.2
155°	19.9
157.5°	18.1
160°	16.3
162.5°	15.1
165°	12.7
167.5°	10.3
170°	7.3
172.5°	4.2
175°	1.2
177.5°	0.0
180°	0.0

TEST NUMBER: P1244916

CATALOG NUMBER: PRLX-MIN-M-935-04L-U-OW

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.7	5.7	5.6	6.6	7.8	4.7	5.7	5.6	6.6	7.8
	3H	7.7	8.6	8.6	9.6	10.8	7.7	8.6	8.6	9.6	10.8
	4H	9.2	10.1	10.1	11.0	12.2	9.2	10.1	10.1	11.0	12.2
	6H	10.7	11.5	11.6	12.5	13.7	10.7	11.5	11.6	12.5	13.7
	8H	11.4	12.2	12.3	13.1	14.4	11.4	12.2	12.3	13.1	14.4
	12H	12.1	12.8	13.0	13.8	15.0	12.1	12.8	13.0	13.8	15.0
4H	2H	5.4	6.3	6.4	7.3	8.5	5.4	6.3	6.4	7.3	8.5
	3H	8.7	9.4	9.6	10.4	11.6	8.7	9.4	9.6	10.4	11.6
	4H	10.3	11.0	11.2	12.0	13.2	10.3	11.0	11.2	12.0	13.2
	6H	11.9	12.6	12.9	13.6	14.8	11.9	12.6	12.9	13.6	14.8
	8H	12.7	13.4	13.7	14.3	15.6	12.7	13.4	13.7	14.3	15.6
	12H	13.5	14.1	14.5	15.1	16.4	13.5	14.1	14.5	15.1	16.4
8H	4H	10.8	11.5	11.8	12.4	13.7	10.8	11.5	11.8	12.4	13.7
	6H	12.7	13.2	13.6	14.2	15.5	12.7	13.2	13.6	14.2	15.5
	8H	13.6	14.1	14.6	15.1	16.4	13.6	14.1	14.6	15.1	16.4
	12H	14.6	15.0	15.6	16.0	17.3	14.6	15.0	15.6	16.0	17.3
12H	4H	10.9	11.5	11.9	12.5	13.8	10.9	11.5	11.9	12.5	13.8
	6H	12.9	13.4	13.8	14.3	15.6	12.9	13.4	13.8	14.3	15.6
	8H	13.9	14.3	14.9	15.3	16.6	13.9	14.3	14.9	15.3	16.6

(END OF REPORT)