

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244923

Luminaire Tested: PRLX-MIN-M-935-07L-U-PS

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1244923  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-MIN-M-935-07L-U-PS  
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, PINSTRIPE SHADE TEXTURE LIGHT LEVEL 5  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 775.1 lumens  
Efficiency: N/A  
Efficacy: 26.8 lumens/watt  
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.18  
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')  
CIE Type: General Diffuse

Input Watts (W): 28.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P1244923

CATALOG NUMBER: PRLX-MIN-M-935-07L-U-PS

### Luminous Intensity Polar Plot





TEST NUMBER: P1244923

CATALOG NUMBER: PRLX-MIN-M-935-07L-U-PS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87		74	74	74		62	62	62	56
1	95	89	84	79	88	82	78	73	70	66	63		59	56	53		48	46	44	39
2	86	76	69	62	79	71	64	58	60	55	50		50	46	42		41	38	35	30
3	78	67	58	51	71	62	54	48	52	46	41		44	39	35		36	32	29	25
4	71	59	50	43	65	55	47	41	47	40	35		39	34	30		32	28	25	22
5	66	53	44	37	60	49	41	35	42	36	31		36	31	27		29	26	22	19
6	61	48	39	33	56	45	37	31	38	32	27		33	28	24		27	23	20	17
7	57	44	35	29	52	41	33	28	35	29	25		30	25	22		25	21	19	16
8	53	40	32	27	49	38	30	25	33	27	22		28	23	20		24	20	17	15
9	50	37	29	24	46	35	28	23	31	25	21		26	22	18		23	19	16	14
10	47	35	27	22	44	33	26	21	29	23	19		25	20	17		21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	67498
5°	34118
10°	6113
15°	1946
20°	1220
25°	987
30°	860
35°	790
40°	764
45°	748
50°	738
55°	734
60°	737
65°	744
70°	758
75°	776
80°	789
85°	808

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 90°  
 Luminance: 822 cd/sqm

TEST NUMBER: P1244923

CATALOG NUMBER: PRLX-MIN-M-935-07L-U-PS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.0	7.5
10°-20°	25.4	3.3
20°-30°	23.9	3.1
30°-40°	31.5	4.1
40°-50°	41.4	5.3
50°-60°	51.5	6.6
60°-70°	60.8	7.8
70°-80°	68.8	8.9
80°-90°	73.1	9.4
90°-100°	73.1	9.4
100°-110°	69.2	8.9
110°-120°	61.7	8.0
120°-130°	50.9	6.6
130°-140°	38.5	5.0
140°-150°	26.3	3.4
150°-160°	14.8	1.9
160°-170°	5.9	0.8
170°-180°	0.5	0.1
0°-30°	107.3	13.8
0°-40°	138.8	17.9
0°-60°	231.7	29.9
0°-90°	434.3	56.0
90°-120°	203.9	26.3
90°-150°	319.5	41.2
90°-180°	341.0	44.0
0°-180°	775.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1317	
5°	906	58
15°	78	25
25°	52	24
35°	50	31
45°	54	41
55°	57	51
65°	61	61
75°	65	69
85°	67	55
90°	67	37
95°	67	55
105°	65	69
115°	62	62
125°	56	51
135°	50	38
145°	42	26
155°	32	15
165°	20	6
175°	2	1
180°	0	

TEST NUMBER: P1244923

CATALOG NUMBER: PRLX-MIN-M-935-07L-U-PS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1317.1
2.5°	1455.1
5°	905.9
7.5°	300.3
10°	204.1
12.5°	111.8
15°	77.8
17.5°	64.2
20°	56.4
22.5°	53.5
25°	51.5
27.5°	49.6
30°	49.6
32.5°	49.6
35°	49.6
37.5°	50.5
40°	51.5
42.5°	52.5
45°	53.5
47.5°	54.4
50°	55.4
52.5°	56.4
55°	57.3
57.5°	58.3
60°	59.3
62.5°	60.3
65°	61.2
67.5°	62.2
70°	63.2
72.5°	64.2
75°	65.1
77.5°	66.1
80°	66.1
82.5°	67.1
85°	67.1
87.5°	67.1
90°	67.1
92.5°	67.1
95°	67.1
97.5°	67.1
100°	66.1
102.5°	66.1
105°	65.1
107.5°	65.1
110°	64.2

TEST NUMBER: P1244923

CATALOG NUMBER: PRLX-MIN-M-935-07L-U-PS

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	63.2
115°	62.2
117.5°	61.2
120°	59.3
122.5°	58.3
125°	56.4
127.5°	55.4
130°	53.5
132.5°	51.5
135°	49.6
137.5°	47.6
140°	45.7
142.5°	43.7
145°	41.8
147.5°	39.9
150°	36.9
152.5°	34.0
155°	32.1
157.5°	29.2
160°	26.2
162.5°	24.3
165°	20.4
167.5°	16.5
170°	11.7
172.5°	6.8
175°	1.9
177.5°	0.0
180°	0.0



TEST NUMBER: P1244923

CATALOG NUMBER: PRLX-MIN-M-935-07L-U-PS

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.3	7.3	7.2	8.3	9.4	6.3	7.3	7.2	8.3	9.4
	3H	9.3	10.3	10.2	11.2	12.4	9.3	10.3	10.2	11.2	12.4
	4H	10.8	11.7	11.7	12.7	13.9	10.8	11.7	11.7	12.7	13.9
	6H	12.3	13.2	13.2	14.1	15.3	12.3	13.2	13.2	14.1	15.3
	8H	13.0	13.8	14.0	14.8	16.0	13.0	13.8	14.0	14.8	16.0
	12H	13.7	14.5	14.6	15.4	16.7	13.7	14.5	14.6	15.4	16.7
4H	2H	7.1	8.0	8.0	8.9	10.1	7.1	8.0	8.0	8.9	10.1
	3H	10.3	11.1	11.2	12.1	13.3	10.3	11.1	11.2	12.1	13.3
	4H	11.9	12.7	12.9	13.6	14.9	11.9	12.7	12.9	13.6	14.9
	6H	13.6	14.2	14.5	15.2	16.5	13.6	14.2	14.5	15.2	16.5
	8H	14.4	15.0	15.3	16.0	17.2	14.4	15.0	15.3	16.0	17.2
	12H	15.2	15.8	16.2	16.7	18.0	15.2	15.8	16.2	16.7	18.0
8H	4H	12.5	13.1	13.4	14.1	15.3	12.5	13.1	13.4	14.1	15.3
	6H	14.3	14.9	15.3	15.9	17.1	14.3	14.9	15.3	15.9	17.1
	8H	15.3	15.8	16.3	16.8	18.0	15.3	15.8	16.3	16.8	18.0
	12H	16.2	16.7	17.2	17.7	19.0	16.2	16.7	17.2	17.7	19.0
12H	4H	12.6	13.2	13.6	14.2	15.4	12.6	13.2	13.6	14.2	15.4
	6H	14.5	15.0	15.5	16.0	17.3	14.5	15.0	15.5	16.0	17.3
	8H	15.6	16.0	16.5	17.0	18.3	15.6	16.0	16.5	17.0	18.3

(END OF REPORT)