

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244972

Luminaire Tested: PRLX-MIN-S-935-05L-U-NL

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244972
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-S-935-05L-U-NL
Description: 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, NATURAL LINES SHADE TEXTURE
LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 495.0 lumens
Efficiency: N/A
Efficacy: 44.6 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.38
Luminous Opening: Rectangular w/ Sides (W: 0.62' x L: 0.62' x H: 0.87')
CIE Type: Semi-Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244972
CATALOG NUMBER: PRLX-MIN-S-935-05L-U-NL

Luminous Intensity Polar Plot





TEST NUMBER: P1244972

CATALOG NUMBER: PRLX-MIN-S-935-05L-U-NL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	113	113	113	113	107	107	107	107	97	97	97		87	87	87		78	78	78	74
1	101	96	91	87	96	91	87	83	82	79	76		74	71	69		66	64	62	58
2	92	84	77	71	87	80	73	68	72	67	63		65	61	57		58	55	52	49
3	85	74	66	60	80	71	63	58	64	58	53		58	53	49		52	48	45	42
4	78	67	58	52	74	63	56	50	58	51	46		52	47	43		47	43	40	37
5	72	60	52	46	68	58	50	44	53	46	41		48	43	38		44	39	36	33
6	67	55	47	41	64	53	45	39	48	42	37		44	39	35		40	36	33	30
7	63	51	42	37	60	49	41	36	45	38	34		41	36	32		38	33	30	28
8	59	47	39	34	56	45	38	33	42	35	31		38	33	29		35	31	28	26
9	56	44	36	31	53	42	35	30	39	33	29		36	31	27		33	29	26	24
10	53	41	34	29	50	39	33	28	37	31	27		34	29	26		32	27	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	11515
5°	11454
10°	10131
15°	2410
20°	2015
25°	1693
30°	1344
35°	1111
40°	969
45°	883
50°	813
55°	762
60°	717
65°	676
70°	646
75°	607
80°	555
85°	518

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 883 cd/sqm

TEST NUMBER: P1244972

CATALOG NUMBER: PRLX-MIN-S-935-05L-U-NL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.3	8.8
10°-20°	45.7	9.2
20°-30°	41.7	8.4
30°-40°	41.2	8.3
40°-50°	41.9	8.5
50°-60°	42.5	8.6
60°-70°	41.1	8.3
70°-80°	37.2	7.5
80°-90°	30.6	6.2
90°-100°	28.7	5.8
100°-110°	27.4	5.5
110°-120°	24.5	4.9
120°-130°	20.3	4.1
130°-140°	14.5	2.9
140°-150°	8.3	1.7
150°-160°	4.3	0.9
160°-170°	1.7	0.3
170°-180°	0.1	0.0
0°-30°	130.7	26.4
0°-40°	171.9	34.7
0°-60°	256.3	51.8
0°-90°	365.3	73.8
90°-120°	80.6	16.3
90°-150°	123.6	25.0
90°-180°	130.0	26.3
0°-180°	495.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	418	
5°	464	43
15°	116	46
25°	92	42
35°	65	41
45°	54	42
55°	47	42
65°	41	41
75°	35	37
85°	28	23
90°	26	15
95°	26	21
105°	26	27
115°	25	24
125°	23	20
135°	19	14
145°	13	8
155°	9	4
165°	6	2
175°	0	0
180°	0	

TEST NUMBER: P1244972

CATALOG NUMBER: PRLX-MIN-S-935-05L-U-NL

CANDELA DISTRIBUTION (FULL):

0°	
0°	417.9
2.5°	433.0
5°	464.5
7.5°	458.8
10°	450.9
12.5°	199.5
15°	116.0
17.5°	110.0
20°	103.5
22.5°	98.2
25°	91.8
27.5°	83.4
30°	76.2
32.5°	69.8
35°	65.2
37.5°	61.4
40°	58.4
42.5°	56.1
45°	54.2
47.5°	52.3
50°	50.4
52.5°	48.9
55°	47.4
57.5°	45.9
60°	44.4
62.5°	42.8
65°	41.3
67.5°	40.2
70°	38.7
72.5°	37.2
75°	35.3
77.5°	33.4
80°	31.1
82.5°	28.8
85°	27.7
87.5°	26.9
90°	26.5
92.5°	26.5
95°	26.2
97.5°	26.2
100°	26.2
102.5°	26.2
105°	25.8
107.5°	25.8
110°	25.4

TEST NUMBER: P1244972

CATALOG NUMBER: PRLX-MIN-S-935-05L-U-NL

CANDELA DISTRIBUTION (continued):

	0°
112.5°	25.0
115°	24.6
117.5°	24.3
120°	23.9
122.5°	23.1
125°	22.8
127.5°	22.0
130°	20.9
132.5°	20.1
135°	18.6
137.5°	17.4
140°	15.9
142.5°	14.4
145°	12.9
147.5°	11.8
150°	11.0
152.5°	10.2
155°	9.1
157.5°	8.3
160°	7.6
162.5°	6.8
165°	5.7
167.5°	4.6
170°	3.0
172.5°	1.5
175°	0.4
177.5°	0.0
180°	0.0



TEST NUMBER: P1244972

CATALOG NUMBER: PRLX-MIN-S-935-05L-U-NL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.7	8.9	8.5	9.6	10.5	7.7	8.9	8.5	9.6	10.5
	3H	10.0	11.1	10.8	11.8	12.8	10.0	11.1	10.8	11.8	12.8
	4H	11.1	12.1	11.8	12.9	13.8	11.1	12.1	11.8	12.9	13.8
	6H	12.1	13.0	12.8	13.8	14.7	12.1	13.0	12.8	13.8	14.7
	8H	12.5	13.4	13.3	14.2	15.1	12.5	13.4	13.3	14.2	15.1
	12H	12.9	13.7	13.7	14.5	15.5	12.9	13.7	13.7	14.5	15.5
4H	2H	8.3	9.3	9.1	10.1	11.0	8.3	9.3	9.1	10.1	11.0
	3H	10.9	11.7	11.6	12.5	13.5	10.9	11.7	11.6	12.5	13.5
	4H	12.1	12.9	12.8	13.6	14.6	12.1	12.9	12.8	13.6	14.6
	6H	13.2	13.9	14.0	14.7	15.7	13.2	13.9	14.0	14.7	15.7
	8H	13.7	14.3	14.5	15.2	16.2	13.7	14.3	14.5	15.2	16.2
	12H	14.2	14.8	15.0	15.6	16.6	14.2	14.8	15.0	15.6	16.6
8H	4H	12.5	13.1	13.2	13.9	14.9	12.5	13.1	13.2	13.9	14.9
	6H	13.8	14.3	14.6	15.2	16.2	13.8	14.3	14.6	15.2	16.2
	8H	14.4	14.9	15.2	15.7	16.7	14.4	14.9	15.2	15.7	16.7
	12H	15.0	15.5	15.9	16.3	17.4	15.0	15.5	15.9	16.3	17.4
12H	4H	12.5	13.1	13.3	13.9	14.9	12.5	13.1	13.3	13.9	14.9
	6H	13.9	14.4	14.7	15.2	16.2	13.9	14.4	14.7	15.2	16.2
	8H	14.6	15.0	15.4	15.9	16.9	14.6	15.0	15.4	15.9	16.9

(END OF REPORT)