

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244859

Luminaire Tested: PRLX-MIN-L-940-05L-U-OW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1244859
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-MIN-L-940-05L-U-OW
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, OPEN WEAVE SHADE TEXTURE LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 603.1 lumens
Efficiency: N/A
Efficacy: 40.8 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 14.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1244859

CATALOG NUMBER: PRLX-MIN-L-940-05L-U-OW

Luminous Intensity Polar Plot





TEST NUMBER: P1244859

CATALOG NUMBER: PRLX-MIN-L-940-05L-U-OW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87		74	74	74		62	62	62	56
1	95	89	83	78	88	82	77	73	70	66	63		59	56	53		48	46	44	39
2	85	76	68	62	79	70	63	58	60	54	50		50	46	42		41	38	35	30
3	77	66	57	50	71	61	53	47	52	46	41		43	39	35		36	32	29	25
4	71	58	49	42	65	54	46	40	46	40	35		39	34	30		32	28	25	21
5	65	52	43	36	60	48	40	34	41	35	30		35	30	26		29	25	22	18
6	60	47	38	32	55	44	36	30	38	31	26		32	27	23		27	22	19	16
7	56	43	34	28	52	40	32	27	35	28	24		29	24	21		25	21	18	15
8	52	39	31	25	48	37	29	24	32	26	21		27	22	19		23	19	16	14
9	49	36	28	23	45	34	27	22	30	24	20		26	21	17		22	18	15	13
10	46	34	26	21	43	32	25	20	28	22	18		24	19	16		21	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27653
5°	12681
10°	2955
15°	1129
20°	728
25°	580
30°	516
35°	482
40°	466
45°	458
50°	455
55°	457
60°	460
65°	468
70°	472
75°	477
80°	478
85°	488

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 499 cd/sqm



TEST NUMBER: P1244859

CATALOG NUMBER: PRLX-MIN-L-940-05L-U-OW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.9	6.1
10°-20°	20.3	3.4
20°-30°	19.8	3.3
30°-40°	26.0	4.3
40°-50°	34.0	5.6
50°-60°	42.3	7.0
60°-70°	49.9	8.3
70°-80°	54.5	9.0
80°-90°	56.4	9.4
90°-100°	56.5	9.4
100°-110°	53.7	8.9
110°-120°	47.4	7.9
120°-130°	39.1	6.5
130°-140°	29.5	4.9
140°-150°	19.9	3.3
150°-160°	11.7	1.9
160°-170°	4.8	0.8
170°-180°	0.5	0.1
0°-30°	76.9	12.8
0°-40°	102.9	17.1
0°-60°	179.3	29.7
0°-90°	340.1	56.4
90°-120°	157.6	26.1
90°-150°	246.1	40.8
90°-180°	263.0	43.6
0°-180°	603.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	874	
5°	514	37
15°	65	20
25°	42	20
35°	41	26
45°	44	34
55°	47	42
65°	50	50
75°	52	55
85°	52	42
90°	52	28
95°	52	42
105°	51	54
115°	48	47
125°	44	39
135°	38	29
145°	32	20
155°	25	12
165°	17	5
175°	2	0
180°	0	

TEST NUMBER: P1244859

CATALOG NUMBER: PRLX-MIN-L-940-05L-U-OW

CANDELA DISTRIBUTION (FULL):

0°	
0°	874.1
2.5°	958.8
5°	514.1
7.5°	209.2
10°	145.3
12.5°	89.0
15°	64.8
17.5°	53.9
20°	47.5
22.5°	44.2
25°	42.1
27.5°	41.2
30°	40.9
32.5°	40.9
35°	41.2
37.5°	41.5
40°	42.4
42.5°	43.0
45°	43.9
47.5°	44.8
50°	45.4
52.5°	46.3
55°	47.2
57.5°	48.1
60°	48.7
62.5°	49.7
65°	50.3
67.5°	50.9
70°	51.2
72.5°	51.5
75°	51.8
77.5°	51.5
80°	51.5
82.5°	51.5
85°	51.8
87.5°	51.8
90°	51.8
92.5°	51.8
95°	51.8
97.5°	51.8
100°	51.5
102.5°	51.2
105°	50.9
107.5°	50.3
110°	49.7

TEST NUMBER: P1244859

CATALOG NUMBER: PRLX-MIN-L-940-05L-U-OW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	48.7
115°	47.8
117.5°	46.9
120°	45.7
122.5°	44.8
125°	43.6
127.5°	42.4
130°	40.9
132.5°	39.7
135°	38.1
137.5°	36.3
140°	34.8
142.5°	33.3
145°	31.5
147.5°	30.0
150°	28.5
152.5°	26.6
155°	25.1
157.5°	23.3
160°	21.5
162.5°	19.4
165°	17.0
167.5°	13.6
170°	9.4
172.5°	5.8
175°	2.4
177.5°	0.6
180°	0.3



TEST NUMBER: P1244859

CATALOG NUMBER: PRLX-MIN-L-940-05L-U-OW

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.9	5.9	5.8	6.9	8.0	4.9	5.9	5.8	6.9	8.0
	3H	7.9	8.9	8.8	9.8	11.0	7.9	8.9	8.8	9.8	11.0
	4H	9.3	10.3	10.2	11.2	12.4	9.3	10.3	10.2	11.2	12.4
	6H	10.7	11.6	11.7	12.5	13.7	10.7	11.6	11.7	12.5	13.7
	8H	11.4	12.2	12.3	13.2	14.4	11.4	12.2	12.3	13.2	14.4
	12H	12.1	12.8	13.0	13.8	15.0	12.1	12.8	13.0	13.8	15.0
4H	2H	5.7	6.6	6.6	7.5	8.7	5.7	6.6	6.6	7.5	8.7
	3H	8.9	9.7	9.8	10.6	11.8	8.9	9.7	9.8	10.6	11.8
	4H	10.4	11.2	11.4	12.1	13.4	10.4	11.2	11.4	12.1	13.4
	6H	12.0	12.7	12.9	13.6	14.9	12.0	12.7	12.9	13.6	14.9
	8H	12.8	13.4	13.7	14.4	15.6	12.8	13.4	13.7	14.4	15.6
	12H	13.5	14.1	14.5	15.1	16.3	13.5	14.1	14.5	15.1	16.3
8H	4H	11.0	11.6	11.9	12.5	13.8	11.0	11.6	11.9	12.5	13.8
	6H	12.7	13.3	13.7	14.3	15.5	12.7	13.3	13.7	14.3	15.5
	8H	13.6	14.1	14.6	15.1	16.4	13.6	14.1	14.6	15.1	16.4
	12H	14.6	15.0	15.5	16.0	17.3	14.6	15.0	15.5	16.0	17.3
12H	4H	11.1	11.6	12.0	12.6	13.9	11.1	11.6	12.0	12.6	13.9
	6H	12.9	13.4	13.9	14.4	15.7	12.9	13.4	13.9	14.4	15.7
	8H	13.9	14.3	14.9	15.3	16.6	13.9	14.3	14.9	15.3	16.6

(END OF REPORT)