

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1244863

Luminaire Tested: PRLX-MIN-L-940-09L-U-PS

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1244863  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-MIN-L-940-09L-U-PS  
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, PINSTRIPE SHADE TEXTURE LIGHT LEVEL 3  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1013.1 lumens  
Efficiency: N/A  
Efficacy: 44.8 lumens/watt  
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.18  
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')  
CIE Type: General Diffuse  
  
Input Watts (W): 22.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P1244863

CATALOG NUMBER: PRLX-MIN-L-940-09L-U-PS

### Luminous Intensity Polar Plot





TEST NUMBER: P1244863

CATALOG NUMBER: PRLX-MIN-L-940-09L-U-PS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |    |    |    |  |    |    |    |  |    |    |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|--|----|----|----|--|----|----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20 |    |    |  | 20 |    |    |  | 20 |    |    |    |
| RC  | 80  |     |     |     | 70  |     |     |     | 50 |    |    |  | 30 |    |    |  | 10 | 0  |    |    |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50 | 30 | 10 |  | 50 | 30 | 10 |  | 50 | 30 | 10 | 0  |
| RCR |     |     |     |     |     |     |     |     |    |    |    |  |    |    |    |  |    |    |    |    |
| 0   | 109 | 109 | 109 | 109 | 101 | 101 | 101 | 101 | 87 | 87 | 87 |  | 74 | 74 | 74 |  | 62 | 62 | 62 | 56 |
| 1   | 95  | 89  | 83  | 78  | 88  | 82  | 77  | 73  | 70 | 66 | 63 |  | 59 | 56 | 53 |  | 48 | 46 | 44 | 39 |
| 2   | 85  | 76  | 68  | 62  | 79  | 70  | 63  | 58  | 60 | 54 | 50 |  | 50 | 46 | 42 |  | 41 | 38 | 35 | 30 |
| 3   | 77  | 66  | 57  | 50  | 71  | 61  | 53  | 47  | 52 | 46 | 41 |  | 43 | 39 | 35 |  | 36 | 32 | 29 | 25 |
| 4   | 71  | 58  | 49  | 42  | 65  | 54  | 46  | 40  | 46 | 40 | 35 |  | 39 | 34 | 30 |  | 32 | 28 | 25 | 21 |
| 5   | 65  | 52  | 43  | 36  | 60  | 48  | 40  | 34  | 41 | 35 | 30 |  | 35 | 30 | 26 |  | 29 | 25 | 22 | 18 |
| 6   | 60  | 47  | 38  | 32  | 55  | 44  | 36  | 30  | 38 | 31 | 26 |  | 32 | 27 | 23 |  | 27 | 22 | 19 | 16 |
| 7   | 56  | 43  | 34  | 28  | 52  | 40  | 32  | 27  | 35 | 28 | 24 |  | 29 | 24 | 21 |  | 25 | 21 | 18 | 15 |
| 8   | 52  | 39  | 31  | 25  | 48  | 37  | 29  | 24  | 32 | 26 | 21 |  | 27 | 22 | 19 |  | 23 | 19 | 16 | 14 |
| 9   | 49  | 36  | 28  | 23  | 45  | 34  | 27  | 22  | 30 | 24 | 20 |  | 26 | 21 | 17 |  | 22 | 18 | 15 | 13 |
| 10  | 46  | 34  | 26  | 21  | 43  | 32  | 25  | 20  | 28 | 22 | 18 |  | 24 | 19 | 16 |  | 21 | 17 | 14 | 12 |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 46455 |
| 5°  | 21302 |
| 10° | 4965  |
| 15° | 1895  |
| 20° | 1225  |
| 25° | 975   |
| 30° | 866   |
| 35° | 810   |
| 40° | 783   |
| 45° | 769   |
| 50° | 764   |
| 55° | 768   |
| 60° | 774   |
| 65° | 785   |
| 70° | 793   |
| 75° | 802   |
| 80° | 803   |
| 85° | 819   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 90°  
 Luminance: 838 cd/sqm



TEST NUMBER: P1244863

CATALOG NUMBER: PRLX-MIN-L-940-09L-U-PS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 61.9   | 6.1       |
| 10°-20°   | 34.1   | 3.4       |
| 20°-30°   | 33.2   | 3.3       |
| 30°-40°   | 43.6   | 4.3       |
| 40°-50°   | 57.2   | 5.6       |
| 50°-60°   | 71.2   | 7.0       |
| 60°-70°   | 83.7   | 8.3       |
| 70°-80°   | 91.6   | 9.0       |
| 80°-90°   | 94.7   | 9.3       |
| 90°-100°  | 94.9   | 9.4       |
| 100°-110° | 90.1   | 8.9       |
| 110°-120° | 79.7   | 7.9       |
| 120°-130° | 65.7   | 6.5       |
| 130°-140° | 49.5   | 4.9       |
| 140°-150° | 33.5   | 3.3       |
| 150°-160° | 19.6   | 1.9       |
| 160°-170° | 8.1    | 0.8       |
| 170°-180° | 0.8    | 0.1       |
| 0°-30°    | 129.3  | 12.8      |
| 0°-40°    | 172.9  | 17.1      |
| 0°-60°    | 301.2  | 29.7      |
| 0°-90°    | 571.2  | 56.4      |
| 90°-120°  | 264.7  | 26.1      |
| 90°-150°  | 413.4  | 40.8      |
| 90°-180°  | 442.0  | 43.6      |
| 0°-180°   | 1013.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | Flux |
|------|------|------|
| 0°   | 1468 |      |
| 5°   | 864  | 62   |
| 15°  | 109  | 34   |
| 25°  | 71   | 33   |
| 35°  | 69   | 44   |
| 45°  | 74   | 57   |
| 55°  | 79   | 71   |
| 65°  | 84   | 84   |
| 75°  | 87   | 92   |
| 85°  | 87   | 71   |
| 90°  | 87   | 48   |
| 95°  | 87   | 71   |
| 105° | 85   | 90   |
| 115° | 80   | 80   |
| 125° | 73   | 66   |
| 135° | 64   | 50   |
| 145° | 53   | 33   |
| 155° | 42   | 20   |
| 165° | 28   | 8    |
| 175° | 4    | 1    |
| 180° | 0    |      |

TEST NUMBER: P1244863

CATALOG NUMBER: PRLX-MIN-L-940-09L-U-PS

**CANDELA DISTRIBUTION (FULL):**

| 0°     |        |
|--------|--------|
| 0°     | 1468.4 |
| 2.5°   | 1610.8 |
| 5°     | 863.6  |
| 7.5°   | 351.4  |
| 10°    | 244.1  |
| 12.5°  | 149.5  |
| 15°    | 108.8  |
| 17.5°  | 90.5   |
| 20°    | 79.9   |
| 22.5°  | 74.3   |
| 25°    | 70.7   |
| 27.5°  | 69.2   |
| 30°    | 68.7   |
| 32.5°  | 68.7   |
| 35°    | 69.2   |
| 37.5°  | 69.7   |
| 40°    | 71.2   |
| 42.5°  | 72.2   |
| 45°    | 73.7   |
| 47.5°  | 75.3   |
| 50°    | 76.3   |
| 52.5°  | 77.8   |
| 55°    | 79.3   |
| 57.5°  | 80.9   |
| 60°    | 81.9   |
| 62.5°  | 83.4   |
| 65°    | 84.4   |
| 67.5°  | 85.4   |
| 70°    | 86.0   |
| 72.5°  | 86.5   |
| 75°    | 87.0   |
| 77.5°  | 86.5   |
| 80°    | 86.5   |
| 82.5°  | 86.5   |
| 85°    | 87.0   |
| 87.5°  | 87.0   |
| 90°    | 87.0   |
| 92.5°  | 87.0   |
| 95°    | 87.0   |
| 97.5°  | 87.0   |
| 100°   | 86.5   |
| 102.5° | 86.0   |
| 105°   | 85.4   |
| 107.5° | 84.4   |
| 110°   | 83.4   |

TEST NUMBER: P1244863

CATALOG NUMBER: PRLX-MIN-L-940-09L-U-PS

**CANDELA DISTRIBUTION (continued):**

|        | 0°   |
|--------|------|
| 112.5° | 81.9 |
| 115°   | 80.4 |
| 117.5° | 78.8 |
| 120°   | 76.8 |
| 122.5° | 75.3 |
| 125°   | 73.2 |
| 127.5° | 71.2 |
| 130°   | 68.7 |
| 132.5° | 66.6 |
| 135°   | 64.1 |
| 137.5° | 61.0 |
| 140°   | 58.5 |
| 142.5° | 55.9 |
| 145°   | 52.9 |
| 147.5° | 50.4 |
| 150°   | 47.8 |
| 152.5° | 44.8 |
| 155°   | 42.2 |
| 157.5° | 39.2 |
| 160°   | 36.1 |
| 162.5° | 32.6 |
| 165°   | 28.5 |
| 167.5° | 22.9 |
| 170°   | 15.8 |
| 172.5° | 9.7  |
| 175°   | 4.1  |
| 177.5° | 1.0  |
| 180°   | 0.5  |



TEST NUMBER: P1244863

CATALOG NUMBER: PRLX-MIN-L-940-09L-U-PS

**CIE UGR TABLE:**

| Reflectances:   |      |                  |      |      |      |      |                |      |      |      |      |
|-----------------|------|------------------|------|------|------|------|----------------|------|------|------|------|
| Ceiling         |      | 0.7              | 0.7  | 0.5  | 0.5  | 0.3  | 0.7            | 0.7  | 0.5  | 0.5  | 0.3  |
| Wall            |      | 0.5              | 0.3  | 0.5  | 0.3  | 0.3  | 0.5            | 0.3  | 0.5  | 0.3  | 0.3  |
| Reference plane |      | 0.2              | 0.2  | 0.2  | 0.2  | 0.2  | 0.2            | 0.2  | 0.2  | 0.2  | 0.2  |
| Room Dimensions |      | Viewed crosswise |      |      |      |      | Viewed endwise |      |      |      |      |
| X=2H            | Y=2H | 6.7              | 7.8  | 7.6  | 8.7  | 9.8  | 6.7            | 7.8  | 7.6  | 8.7  | 9.8  |
|                 | 3H   | 9.7              | 10.7 | 10.6 | 11.6 | 12.8 | 9.7            | 10.7 | 10.6 | 11.6 | 12.8 |
|                 | 4H   | 11.1             | 12.1 | 12.0 | 13.0 | 14.2 | 11.1           | 12.1 | 12.0 | 13.0 | 14.2 |
|                 | 6H   | 12.5             | 13.4 | 13.5 | 14.3 | 15.5 | 12.5           | 13.4 | 13.5 | 14.3 | 15.5 |
|                 | 8H   | 13.2             | 14.0 | 14.1 | 15.0 | 16.2 | 13.2           | 14.0 | 14.1 | 15.0 | 16.2 |
|                 | 12H  | 13.9             | 14.7 | 14.8 | 15.6 | 16.8 | 13.9           | 14.7 | 14.8 | 15.6 | 16.8 |
| 4H              | 2H   | 7.5              | 8.4  | 8.4  | 9.3  | 10.5 | 7.5            | 8.4  | 8.4  | 9.3  | 10.5 |
|                 | 3H   | 10.7             | 11.5 | 11.6 | 12.4 | 13.6 | 10.7           | 11.5 | 11.6 | 12.4 | 13.6 |
|                 | 4H   | 12.2             | 13.0 | 13.2 | 13.9 | 15.2 | 12.2           | 13.0 | 13.2 | 13.9 | 15.2 |
|                 | 6H   | 13.8             | 14.5 | 14.7 | 15.4 | 16.7 | 13.8           | 14.5 | 14.7 | 15.4 | 16.7 |
|                 | 8H   | 14.6             | 15.2 | 15.5 | 16.2 | 17.4 | 14.6           | 15.2 | 15.5 | 16.2 | 17.4 |
|                 | 12H  | 15.3             | 15.9 | 16.3 | 16.9 | 18.1 | 15.3           | 15.9 | 16.3 | 16.9 | 18.1 |
| 8H              | 4H   | 12.8             | 13.4 | 13.7 | 14.3 | 15.6 | 12.8           | 13.4 | 13.7 | 14.3 | 15.6 |
|                 | 6H   | 14.5             | 15.1 | 15.5 | 16.1 | 17.3 | 14.5           | 15.1 | 15.5 | 16.1 | 17.3 |
|                 | 8H   | 15.4             | 15.9 | 16.4 | 16.9 | 18.2 | 15.4           | 15.9 | 16.4 | 16.9 | 18.2 |
|                 | 12H  | 16.4             | 16.8 | 17.3 | 17.8 | 19.1 | 16.4           | 16.8 | 17.3 | 17.8 | 19.1 |
| 12H             | 4H   | 12.9             | 13.4 | 13.8 | 14.4 | 15.7 | 12.9           | 13.4 | 13.8 | 14.4 | 15.7 |
|                 | 6H   | 14.7             | 15.2 | 15.7 | 16.2 | 17.5 | 14.7           | 15.2 | 15.7 | 16.2 | 17.5 |
|                 | 8H   | 15.7             | 16.1 | 16.7 | 17.1 | 18.4 | 15.7           | 16.1 | 16.7 | 17.1 | 18.4 |

(END OF REPORT)