

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979722

Luminaire Tested: PRLX-241-930-LL7-F-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-930-LL7-F-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 241 SHADE WITH FROSTED LENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2744.6 lumens
Efficiency: N/A
Efficacy: 57.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.07
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979722
CATALOG NUMBER: PRLX-241-930-LL7-F-U-S-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P979722

CATALOG NUMBER: PRLX-241-930-LL7-F-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86
3	102	95	90	86	100	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68
6	86	77	70	66	84	76	70	65	74	69	65	73	68	65	71	67	64	63
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50
10	69	59	53	49	68	58	53	49	58	52	49	57	52	48	56	52	48	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18271
5°	17968
10°	17482
15°	17040
20°	16820
25°	16587
30°	16295
35°	14326
40°	6360
45°	798
50°	185
55°	207
60°	208
65°	212
70°	174
75°	173
80°	173
85°	168

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 798 cd/sqm

TEST NUMBER: P979722

CATALOG NUMBER: PRLX-241-930-LL7-F-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.6	8.0
10°-20°	603.2	22.0
20°-30°	898.2	32.7
30°-40°	866.8	31.6
40°-50°	126.1	4.6
50°-60°	13.2	0.5
60°-70°	10.7	0.4
70°-80°	6.1	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1720.1	62.7
0°-40°	2586.9	94.3
0°-60°	2726.2	99.3
0°-90°	2744.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2744.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2370	
5°	2322	219
15°	2135	603
25°	1950	898
35°	1522	867
45°	73	126
55°	15	13
65°	12	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P979722

CATALOG NUMBER: PRLX-241-930-LL7-F-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	2370.0
2.5°	2358.5
5°	2321.9
7.5°	2273.7
10°	2233.2
12.5°	2179.3
15°	2135.0
17.5°	2092.6
20°	2050.2
22.5°	2005.9
25°	1950.0
27.5°	1892.2
30°	1830.5
32.5°	1732.2
35°	1522.2
37.5°	1127.2
40°	632.0
42.5°	262.1
45°	73.2
47.5°	23.1
50°	15.4
52.5°	15.4
55°	15.4
57.5°	13.5
60°	13.5
62.5°	11.6
65°	11.6
67.5°	9.6
70°	7.7
72.5°	7.7
75°	5.8
77.5°	3.9
80°	3.9
82.5°	1.9
85°	1.9
87.5°	0.0
90°	0.0



TEST NUMBER: P979722
 CATALOG NUMBER: PRLX-241-930-LL7-F-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.13	0.00	0.00	0.00	0.00	0.13
	6H	0.00	0.00	0.00	0.16	0.64	0.00	0.00	0.00	0.16	0.64
	8H	0.00	0.00	0.00	0.26	0.74	0.00	0.00	0.00	0.26	0.74
	12H	0.00	0.00	0.00	0.37	0.85	0.00	0.00	0.00	0.37	0.85
8H	4H	0.00	0.00	0.00	0.00	0.27	0.00	0.00	0.00	0.00	0.27
	6H	0.00	0.00	0.10	0.44	0.93	0.00	0.00	0.10	0.44	0.93
	8H	0.00	0.09	0.31	0.61	1.11	0.00	0.09	0.31	0.61	1.11
	12H	0.01	0.28	0.53	0.78	1.36	0.01	0.28	0.53	0.78	1.36
12H	4H	0.00	0.00	0.00	0.00	0.24	0.00	0.00	0.00	0.00	0.24
	6H	0.00	0.00	0.14	0.44	0.94	0.00	0.00	0.14	0.44	0.94
	8H	0.00	0.11	0.37	0.61	1.19	0.00	0.11	0.37	0.61	1.19