

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979741

Luminaire Tested: PRLX-241-935-LL1-C-U-S-WHTE-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979741
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-935-LL1-C-U-S-WHTE-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE 241 SHADE WITH CLEAR LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1077.4 lumens
Efficiency: N/A
Efficacy: 143.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.09
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979741
CATALOG NUMBER: PRLX-241-935-LL1-C-U-S-WHTE-X

Luminous Intensity Polar Plot





TEST NUMBER: P979741

CATALOG NUMBER: PRLX-241-935-LL1-C-U-S-WHTE-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	98	100	98	95		97	94	92		93	91	90	88
2	103	96	90	85	100	94	89	84	91	86	83		87	84	81		85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	73		80	75	71		77	73	70	68
4	89	79	71	66	87	78	71	65	75	69	65		73	68	64		71	67	63	61
5	83	72	64	59	81	71	64	59	69	63	58		67	62	57		65	61	57	55
6	78	66	59	53	76	65	58	53	64	57	52		62	56	52		61	56	52	50
7	73	61	54	48	71	60	53	48	59	53	48		58	52	48		56	51	47	45
8	69	57	49	44	67	56	49	44	55	48	44		54	48	44		53	47	43	42
9	65	53	46	41	63	52	45	41	51	45	40		50	44	40		49	44	40	38
10	61	49	42	38	60	49	42	37	48	42	37		47	41	37		46	41	37	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5147
5°	5027
10°	4846
15°	4784
20°	4800
25°	4822
30°	4837
35°	4671
40°	1803
45°	1267
50°	1241
55°	1313
60°	1381
65°	1423
70°	1375
75°	1299
80°	1216
85°	1123

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 65°
 Luminance: 1423 cd/sqm

TEST NUMBER: P979741

CATALOG NUMBER: PRLX-241-935-LL1-C-U-S-WHTE-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.0	5.7
10°-20°	169.9	15.8
20°-30°	261.4	24.3
30°-40°	265.9	24.7
40°-50°	95.2	8.8
50°-60°	87.1	8.1
60°-70°	76.1	7.1
70°-80°	46.3	4.3
80°-90°	14.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	492.2	45.7
0°-40°	758.1	70.4
0°-60°	940.4	87.3
0°-90°	1077.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1077.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	668	
5°	650	61
15°	599	170
25°	567	261
35°	496	266
45°	116	95
55°	98	87
65°	78	76
75°	44	46
85°	13	15
90°	0	

TEST NUMBER: P979741

CATALOG NUMBER: PRLX-241-935-LL1-C-U-S-WHTE-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	667.7
2.5°	665.4
5°	649.6
7.5°	631.8
10°	619.1
12.5°	609.4
15°	599.4
17.5°	592.8
20°	585.1
22.5°	577.4
25°	566.9
27.5°	555.3
30°	543.4
32.5°	528.3
35°	496.3
37.5°	336.0
40°	179.2
42.5°	130.5
45°	116.2
47.5°	107.4
50°	103.5
52.5°	100.8
55°	97.7
57.5°	93.8
60°	89.6
62.5°	84.6
65°	78.0
67.5°	69.5
70°	61.0
72.5°	52.1
75°	43.6
77.5°	35.5
80°	27.4
82.5°	20.1
85°	12.7
87.5°	7.0
90°	0.0



TEST NUMBER: P979741
 CATALOG NUMBER: PRLX-241-935-LL1-C-U-S-WHTE-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.40	12.72	11.77	13.04	13.35	11.40	12.72	11.77	13.04	13.35
	3H	13.56	14.75	13.94	15.08	15.44	13.56	14.75	13.94	15.08	15.44
	4H	14.34	15.45	14.74	15.80	16.19	14.34	15.45	14.74	15.80	16.19
	6H	14.93	15.95	15.34	16.32	16.72	14.93	15.95	15.34	16.32	16.72
	8H	15.13	16.11	15.56	16.50	16.90	15.13	16.11	15.56	16.50	16.90
	12H	15.27	16.20	15.70	16.59	17.02	15.27	16.20	15.70	16.59	17.02
4H	2H	12.15	13.26	12.55	13.61	13.99	12.15	13.26	12.55	13.61	13.99
	3H	14.47	15.39	14.88	15.80	16.20	14.47	15.39	14.88	15.80	16.20
	4H	15.36	16.20	15.80	16.62	17.06	15.36	16.20	15.80	16.62	17.06
	6H	16.08	16.80	16.54	17.25	17.71	16.08	16.80	16.54	17.25	17.71
	8H	16.33	17.00	16.79	17.45	17.92	16.33	17.00	16.79	17.45	17.92
	12H	16.51	17.11	17.00	17.60	18.07	16.51	17.11	17.00	17.60	18.07
8H	4H	15.68	16.36	16.15	16.81	17.28	15.68	16.36	16.15	16.81	17.28
	6H	16.54	17.09	17.04	17.59	18.07	16.54	17.09	17.04	17.59	18.07
	8H	16.88	17.37	17.40	17.89	18.38	16.88	17.37	17.40	17.89	18.38
	12H	17.16	17.59	17.67	18.09	18.66	17.16	17.59	17.67	18.09	18.66
12H	4H	15.71	16.31	16.20	16.79	17.27	15.71	16.31	16.20	16.79	17.27
	6H	16.60	17.10	17.12	17.61	18.10	16.60	17.10	17.12	17.61	18.10
	8H	17.01	17.44	17.52	17.93	18.51	17.01	17.44	17.52	17.93	18.51