

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979761

Luminaire Tested: PRLX-241-935-LL3-C-U-S-WHTE-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979761
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-241-935-LL3-C-U-S-WHTE-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE 241 SHADE WITH CLEAR LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2066.8 lumens
Efficiency: N/A
Efficacy: 137.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.09
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979761
CATALOG NUMBER: PRLX-241-935-LL3-C-U-S-WHTE-X

Luminous Intensity Polar Plot





TEST NUMBER: P979761

CATALOG NUMBER: PRLX-241-935-LL3-C-U-S-WHTE-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68
4	89	79	71	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61
5	83	72	64	59	81	71	64	59	69	63	58	67	62	57	65	61	57	55
6	78	66	59	53	76	65	58	53	64	57	52	62	56	52	61	56	52	50
7	73	61	54	48	71	60	53	48	59	53	48	58	52	48	56	51	47	45
8	69	57	49	44	67	56	49	44	55	48	44	54	48	44	53	47	43	42
9	65	53	46	41	63	52	45	41	51	45	40	50	44	40	49	44	40	38
10	61	49	42	38	60	49	42	37	48	42	37	47	41	37	46	41	37	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9875
5°	9643
10°	9297
15°	9177
20°	9208
25°	9251
30°	9279
35°	8959
40°	3460
45°	2431
50°	2381
55°	2519
60°	2650
65°	2731
70°	2639
75°	2493
80°	2335
85°	2158

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 65°
 Luminance: 2731 cd/sqm

TEST NUMBER: P979761

CATALOG NUMBER: PRLX-241-935-LL3-C-U-S-WHTE-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.0	5.7
10°-20°	325.8	15.8
20°-30°	501.4	24.3
30°-40°	510.0	24.7
40°-50°	182.7	8.8
50°-60°	167.1	8.1
60°-70°	146.0	7.1
70°-80°	88.8	4.3
80°-90°	27.9	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	944.3	45.7
0°-40°	1454.3	70.4
0°-60°	1804.1	87.3
0°-90°	2066.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2066.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1281	
5°	1246	117
15°	1150	326
25°	1088	501
35°	952	510
45°	223	183
55°	187	167
65°	150	146
75°	84	89
85°	24	28
90°	0	

TEST NUMBER: P979761

CATALOG NUMBER: PRLX-241-935-LL3-C-U-S-WHTE-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1280.9
2.5°	1276.5
5°	1246.1
7.5°	1212.0
10°	1187.6
12.5°	1169.1
15°	1149.8
17.5°	1137.2
20°	1122.4
22.5°	1107.6
25°	1087.6
27.5°	1065.3
30°	1042.4
32.5°	1013.5
35°	952.0
37.5°	644.5
40°	343.8
42.5°	250.4
45°	223.0
47.5°	206.0
50°	198.5
52.5°	193.4
55°	187.4
57.5°	180.0
60°	171.9
62.5°	162.2
65°	149.7
67.5°	133.4
70°	117.1
72.5°	100.0
75°	83.7
77.5°	68.2
80°	52.6
82.5°	38.5
85°	24.4
87.5°	13.3
90°	0.0



TEST NUMBER: P979761
 CATALOG NUMBER: PRLX-241-935-LL3-C-U-S-WHTE-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.67	14.99	14.03	15.30	15.62	13.67	14.99	14.03	15.30	15.62
	3H	15.83	17.01	16.21	17.34	17.71	15.83	17.01	16.21	17.34	17.71
	4H	16.61	17.72	17.01	18.07	18.45	16.61	17.72	17.01	18.07	18.45
	6H	17.20	18.22	17.61	18.59	18.99	17.20	18.22	17.61	18.59	18.99
	8H	17.40	18.37	17.83	18.76	19.17	17.40	18.37	17.83	18.76	19.17
	12H	17.54	18.47	17.97	18.85	19.28	17.54	18.47	17.97	18.85	19.28
4H	2H	14.41	15.53	14.82	15.88	16.26	14.41	15.53	14.82	15.88	16.26
	3H	16.73	17.66	17.15	18.06	18.47	16.73	17.66	17.15	18.06	18.47
	4H	17.63	18.47	18.06	18.88	19.33	17.63	18.47	18.06	18.88	19.33
	6H	18.34	19.07	18.81	19.51	19.98	18.34	19.07	18.81	19.51	19.98
	8H	18.59	19.27	19.06	19.72	20.19	18.59	19.27	19.06	19.72	20.19
	12H	18.78	19.38	19.27	19.86	20.34	18.78	19.38	19.27	19.86	20.34
8H	4H	17.95	18.63	18.42	19.08	19.55	17.95	18.63	18.42	19.08	19.55
	6H	18.81	19.36	19.31	19.86	20.34	18.81	19.36	19.31	19.86	20.34
	8H	19.15	19.64	19.67	20.15	20.65	19.15	19.64	19.67	20.15	20.65
	12H	19.43	19.86	19.94	20.35	20.92	19.43	19.86	19.94	20.35	20.92
12H	4H	17.98	18.58	18.47	19.06	19.54	17.98	18.58	18.47	19.06	19.54
	6H	18.87	19.37	19.39	19.88	20.37	18.87	19.37	19.39	19.88	20.37
	8H	19.28	19.71	19.79	20.20	20.77	19.28	19.71	19.79	20.20	20.77